



WELCOME TO
ACCURATE SCREW MACHINE
A Division of MW Industries

[Login / Register](#)
[ENTER](#)
[HOME](#) [ABOUT ASM](#) [QUALITY](#) [TECH TIPS](#) [CREDIT](#) [CHAT](#) [E-SERVICES](#) [RFQ](#)

CALL US TOLL-FREE: 1.877.285.2181

[CONTACT ASM](#)


Product Search

 By Part No.:

 By

 Keyword:
[ENTER](#)



View Products



- ▶ Bushings
- ▶ Captive Screws & Assemblies
- ▶ Handles / Ferrules
- ▶ Locking Fasteners
- ▶ Nuts
- ▶ Panel Screw Retainers
- ▶ Screws - Standard, Set, Stud
- ▶ Spacers
- ▶ Springs
- ▶ Standoffs / Adapters
- ▶ Thumb Screws
- ▶ Tools
- ▶ Washers
- ▶ Custom Parts
- ▶ Optional Product Features



CAPTIVE SOCKET HEAD CAP SCREW ASSEMBLY


 $D=0.365-0.375$ $H=0.244-0.250$ $K=1/4$ $B=0.175$

Complete ASM Part No.: 114121 .500 SS G 1
[Material Specifications](#)
[Thread Length Info](#)
[Metric Size Info](#)
[Help](#)
[Get .DXF File](#)
[Back to Product Index](#)

Printed catalog page(s): 130

 Tolerance(s): K: ± 0.010 B: ± 0.005

Step 3 of 3: Click here to add part & download CAD Drawings or
Edit values below and click [Up-date](#) again

Length	Material	Lock Washer Type	Finish	Options	Point Full Thrd. Self-Seal Opt 'Prefix'
Please enter value in the box below: .500	Steel Stainless Steel	Split Internal Tooth External Tooth	No finish Anodized (Dk. Gray) Anodized (Clear) Anodized (Blue) Anodized (Red) Anodized (YellowGreen) Anodized (Dichromate) Anodized (Dyed Gold) Anodized (Black) Cadmium Clear Plate	Full thread Unselect	Lead Point Self Sealing Self Seal, Lead Pt. Unselect

© Monday, July 09, 2012, MW Industries, Inc. All rights reserved.

[Terms of use](#) | [Product Sitemap](#) | [Services Sitemap](#) | [Site Optimization](#)