



LOC	DIST	P	F	REVISIONS						
				ZONE	LTR	DESCRIPTION			DATE	APPD
AJ	16				0	RLSE -2 PER 98-3137-043 & 0630-0373-98			9-22-98	JL



- 1 ZINC PER QQ-Z-363.
- 2 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3 PHOSPHOR BRONZE PER QQ-B-750.
- 4 NICKEL PLATE PER QQ-N-290, 3.81 μm [.000150] MINIMUM THICK.
- 5 GOLD PLATE PER MIL-G-45204, 0.76 μm [.000030] MINIMUM THICK.



SUGGESTED PCB CONFIGURATION

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

1274127-1		
PART NO		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± - ANGLES ± 5°		
MATERIAL		
SEE NOTES 1 THRU 3		
FINISH		
SEE NOTES 4 & 5		
DR 9-3-98 J. LIPPERT		
CHK 9-22-98 J. LIPPERT		
APPD 9-22-98 J. LIPPERT		
APPD 9-22-98 J. LIPPERT		
PRODUCT SPEC -		
APPLICATION SPEC -		
WEIGHT -		
AMP Incorporated Harrisburg, PA 17105-3608		
NAME		
JACK, RIGHT ANGLE, PCB, 75 OHM, BNC		
SIZE		
CAGE CODE		
DRAWING NO		
SCALE		
SHEET		
1 OF 1		