


VICOR CONFIDENTIAL



THIS DOCUMENT AND THE DATA DISCLOSED
HEREIN OR HEREWITH IS NOT TO BE REPRODUCED,
USED, OR DISCLOSED IN WHOLE OR IN PART
TO ANYONE WITHOUT PERMISSION OF VICOR CORP.

REV.	DESCRIPTION	DATE	APPROVED
1	RELEASED PER E050355 LEK	11/17/05	EF
2	REVISED PER E064280 PEI	02/23/06	ECF
3	REVISED PER E064291 PEI	03/20/06	MH



NOTES:

1. MATERIAL: BRASS QQ-B-626 ALLOY 360 1/2 HARD;
ELECTRO-TIN PER ASTM B 545, OVER .0001 NICKEL
PLATING, WITH BERYLLIUM COPPER SPRING INSERT
CAPTIVATED.
2. CONCORD P/N 09-9002-1-06 OR APPROVED EQUIV.
3. PARTS SHALL MEET SOLDERABILITY REQUIREMENTS
PER MIL-STD-202, METHOD 208 AFTER EXPOSURE TO
8 HRS STEAM AGING PER MIL-STD-883, METHOD 2003.
4. RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST
REVISION.

DRAWN BY	DATE				
P.E.IENI	05/18/05				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES- TOLERANCES ARE:		SOCKET, PIN .040 DIA. PC			
FRACTIONS	DECIMALS				
±1/64	.XX= ±.01	±1°			
	.XXX=±.005				
THIRD ANGLE PROJECTION		SIZE	FSCM NO.	DWG NO	REV
		B	67131	30074	3
DO NOT SCALE DRAWING		SCALE NONE		SHEET 1 OF 1	

SOCKET, PIN
.040 DIA. PC

REV
3