




4

3

2

1



NOTES:

1. Unless otherwise noted, all dimensions are in inches.
2. Foil Material: .002 thick 1145 aluminum
3. Interface Material: .0005 thick phase-change thermal compound, both sides.
Maximum shipping & storage temperature - 40°C
Reflow temperature - 60°C
Maximum recommended service temperature - 200°C
4. Thermal impedance: .030 °C/W-in² (.194 °C/W-cm²) @ 20psi
5. Thermal washers shall be packaged in quantities of 10 with oversize separators between them.
6. Used with 12-pin PSIP packages (Apex designators: DP, ED, EE & EQ).
7. Power Devices part no. AL-123-077-APX
8. Supplier is to label each plastic box with the Apex Microtechnology part number.

TOLERANCES - UNLESS
OTHERWISE SPECIFIED
.XX = ±.05 [.002]
.XXX = ±.005 [.0002]
ANG. = ±2°



TITLE: THERMAL WASHER, PSIP
SUBJECT: MECHANICAL DRAWING
ENGINEER: D-M
DRAWN BY: P.ECK
DCAL: 12437
SPL: 1 OF 1

MODEL: TW07
FILENAME: TW07
REV: G
DATE: 14NOV12

4

3

2

1