


## ENERGIZER NO. E95

D



Industry Standard Dimensions in mm (inches)






Negative cover detail referenced on page 2.

<b>Chemical System:</b>	Alkaline Zinc-Manganese Dioxide (Zn/MnO <sub>2</sub> ) ( <i>No Added Mercury or Cadmium</i> )
<b>Designation:</b>	ANSI-13A, IEC-LR20
<b>Battery Voltage:</b>	1.5 Volts
<b>Internal Resistance:</b>	173 Milliohms (Fresh)
<b>Operating Temp:</b>	-18°C to 55°C (0°F to 130°F)
<b>Average Capacity:</b>	18,000 mAh (to 0.8 volts) (Rated capacity at 25 mA continuous drain.)
<b>Average Weight:</b>	141.9 grams (5.03 oz.)
<b>Volume:</b>	55.9 cubic centimeters (3.4 cubic inch)
<b>Cell:</b>	One No. 3-350 (size 'D')
<b>Jacket:</b>	Plastic Label
<b>Shelf Life:</b>	7 years (80% of rated capacity)

## TEMPERATURE EFFECTS


Typical Service to 0.8 Volts

Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.


Copyright © Eveready Battery Co. - All rights reserved

**ENERGIZER NO. E95****NEGATIVE COVER VIEW****ANSI - IEC Industry Standard Tests @ 20° C****PORABLE LIGHTING**

1.5 ohm - 4 min/15 min 8 hr/day

**TOY**

2.2 ohm - 1 hr/day

**PORABLE STEREO**

3.9 ohm - 1 hr/day

**PORABLE LIGHTING**

2.2 ohm - 4 min/hr 8 hr/day

**Radio**

10 ohm - 4 hr/day

**Important Notice**

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved