

Pneufit C composite and Pneufit M fittings Inch Ø 1/8" ... 1/2" O/D tube

Norgren Pneufit® C fittings are ready to use, offering fast assembly with no need for tools providing optimum flow. Pneufit® C offers a broad range of over 1,000 composite push-in pneumatic fittings to complement our established all brass Pneufit® series.

Releasable stainless-steel grab-ring to grip nylon or polyurethane tube (85 or 95 durometer).

Nickel plated brass components provide corrosion and contamination resistance and an extended life.

Pre applied thread sealant on all taper threads and recessed captive O-ring on parallel threads provides optimum rapid sealing.

Internal and external hexagons on straight fittings.

Immediate quality sealing using silicone free U-packing.

Mounting holes on all union fittings.

Also introducing Miniature Pneufit M an ultra compact alternative where space is at a premium.



Technical data

Medium: Compressed air

Operating pressure: 29.5" Hg vacuum up to 150 psi

Temperature: 32°F to 140°F

Materials

Body: PBT

Seals: NBR (silicone free) u-packaging and O-rings

Threaded bodies: nickel plated brass

Release sleeve and backing ring: POM

Grab-ring: stainless steel

Collar: nickel plated brass

Thread sealant: threebond 2350B

Tube sizes

Standard sizes: 5/32", 3/16", 1/4", 5/16", 3/8" and 1/2"

Miniature sizes: 1/8", 5/32" (1/4" from Dec 2003)

Thread sizes

Standard sizes: 10-32 UNF, 1/8", 1/4", 3/8" and 1/2" NPT and ISO R

Miniature sizes: 10-32 UNF, 1/16" and 1/8" NPT

Tube types

Nylon 11 or 12

Polyurethane 85 or 95 durometer



Pneufit C

Straight Adaptors and Connectors

Straight Union C2020  Page 9.1.002.04	Straight Union (unequal) C2020  Page 9.1.002.04	Straight Adaptor (external + internal hex) C2425  Page 9.1.002.04	Straight Adaptor (internal hex) C242A  Page 9.1.002.05	Straight Adaptor (female thread) C2426  Page 9.1.002.05	Stem Reducer (stem/tube) C2023  Page 9.1.002.05	Stem Expander (stem/tube) C2023  Page 9.1.002.05
Bulkhead Union C2029  Page 9.1.002.05	Female Bulkhead C2432  Page 9.1.002.05	Stem Union C2022  Page 9.1.002.05	Plug C2004  Page 9.1.002.06	Cap (female plug) C2012  Page 9.1.002.06		

Elbow Connectors and Adaptors

Union Elbow C2040  Page 9.1.002.06	90° Swivel Elbow Adaptor C2447  Page 9.1.002.06	Stem Elbow C2043  Page 9.1.002.06	90° Swivel Elbow Adaptor (extended) C2454  Page 9.1.002.06	90° Swivel Elbow Adaptor (female) C2448  Page 9.1.002.07	
Banjo Flow Control (regulating out) C2VA0  Page 9.1.002.07	Banjo Flow Control (regulating in) C2WA0  Page 9.1.002.07	Banjo C2R51  Page 9.1.002.07	Banjo with Top Port C2D51  Page 9.1.002.07	Shrouded Banjo C2VB0  Page 9.1.002.08	In line flow control C24GE  Page 9.1.002.08

Tee Connectors and Adaptors

Union Tee C2060  Page 9.1.002.08	Swivel Tee Adaptor C2467  Page 9.1.002.08	Swivel Side Tee Adaptor C2468  Page 9.1.002.08	Union Tee (unequal) C206A  Page 9.1.002.08	Stem Tee C2063  Page 9.1.002.09	Stem Side Tee C2064  Page 9.1.002.09	Swivel Tee Adaptor (female) C246C  Page 9.1.002.09
--	---	--	--	---	--	--

Y Connectors



Union Y (equal +unequal) C2082  Page 9.1.002.09	Swivel Y Adaptor C2488  Page 9.1.002.10	Stem Y (equal +unequal) C2084  Page 9.1.002.10
---	---	--



Cross and Manifolds



Union Cross C2090  Page 9.1.002.10	Manifold Union C20D3  Page 9.1.002.10	Male Manifold C24D3  Page 9.1.002.10	Stem Manifold C20J3  Page 9.1.002.10
--	---	--	--

Hand Valves

Tube to Tube C20GF  Page 9.1.002.11	Thread to Thread C24GG  Page 9.1.002.11	Tube to Thread C24GH  Page 9.1.002.11	Thread to Tube C24GJ  Page 9.1.002.11
---	---	---	---

Pneufit M




Straight Adaptors and Connectors

Straight Union M2020  Page 9.1.002.12	Straight Union (unequal) M2020  Page 9.1.002.12	Straight Adaptor (external + internal hex) M2425  Page 9.1.002.12	Straight Adaptor (internal hex only) M242A  Page 9.1.002.12	Straight Adaptor (female thread) M2426  Page 9.1.002.12
---	---	---	---	---

Elbow Connectors and Adaptors

Union Elbow M2040  Page 9.1.002.13	90° Swivel Elbow Adaptor M2447  Page 9.1.002.13
--	---

Tee Connectors and Adaptors

Union Tee M2060  Page 9.1.002.13	Swivel Tee Adaptor M2467  Page 9.1.002.13	Swivel Side Tee Adaptor M2468  Page 9.1.002.13
--	---	--





Pneufit C & Pneufit M composite fittings Inch

Method of assembly





1. Ensure that the end tube is cut square and is free from burrs.

2. Push the tube through the release ring button and grab ring into the fitting.



3. Push the tube firmly through the 'O' ring until it bottoms on the tube stop, then pull back.


4. To disconnect, push the tube into the fitting, hold down the release button and withdraw the tube.



- 1 Impact resistant PBT body in black for Pneufit® C and light gray for Pneufit® M.
- 2 Release buttons are red for metric, grey for inch, and light grey oval for Pneufit® M.
- 3 Stainless steel grab ring with special design to retain softer tube and provide easy releasability.
- 4 Silicon free U-packing provides leak tight tube seal under side loading.
- 5 Stem seal provides leak tight 360° swivel connection.
- 6 Nickel plated brass threads and notches on hex to signify NPT.
- 7 Pre-applied thread sealant on tapered threads and recessed captive O-ring on parallel threads.

C2020

Straight Union




ØD	H	L	C	B	D	
5/32	1.36 (34.6)	0.50 (12.75)	0.13 (3.3)	0.64 (16.3)	0.41 (10.5)	C20200200
3/16	1.40 (35.5)	0.59 (15.1)	0.14 (3.5)	0.66 (16.8)	0.45 (11.5)	C20200300
1/4	1.45 (36.8)	0.64 (16.3)	0.14 (3.5)	0.69 (17.4)	0.51 (13.0)	C20200400
5/16	1.55 (39.4)	0.78 (19.85)	0.17 (4.3)	0.74 (18.7)	0.57 (14.5)	C20200500
3/8	1.68 (42.6)	0.85 (21.5)	0.18 (4.5)	0.80 (20.2)	0.69 (17.5)	C20200600
1/2	1.93 (48.9)	0.96 (24.5)	0.18 (4.5)	0.87 (22.0)	0.83 (21.0)	C20200700

C2020

Straight Union


(Unequal)



ØA	ØB	H	B1	B2	ØE	ØF	
3/16	5/32	1.38 (35.0)	0.66 (16.8)	0.64 (16.3)	0.45 (11.5)	0.41 (10.5)	C20200302
1/4	5/32	1.40 (35.6)	0.69 (17.4)	0.64 (16.3)	0.51 (13.0)	0.41 (10.5)	C20200402
1/4	3/16	1.43 (36.2)	0.69 (17.4)	0.66 (16.8)	0.51 (13.0)	0.45 (11.5)	C20200403
5/16	1/4	1.50 (38.1)	0.74 (18.7)	0.69 (17.4)	0.57 (14.5)	0.51 (13.0)	C20200504
3/8	1/4	1.56 (39.7)	0.80 (20.2)	0.69 (17.4)	0.69 (17.5)	0.51 (13.0)	C20200604
3/8	5/16	1.61 (41.0)	0.80 (20.2)	0.74 (18.7)	0.69 (17.5)	0.57 (14.5)	C20200605
1/2	3/8	1.78 (45.3)	0.87 (22.0)	0.80 (20.2)	0.83 (21.0)	0.69 (17.5)	C20200706

C2425

Straight adaptor (external + internal hex)




ØD	T	L	A	B	Hex
5/32	UNF 10/32	0.84 (21.4)	0.14 (3.6)	0.64 (16.2)	7/16 C24250210
	NPT 1/8	0.77 (19.5)	0.33 (8.5)		7/16 C24250218
	NPT 1/4	0.87 (22.0)	0.41 (10.5)		9/16 C24250228
	NPT 3/8	0.90 (22.95)	0.45 (11.5)		11/16 C24250238
3/16	UNF 10/32	0.87 (22.0)	0.14 (3.6)	0.66 (16.8)	7/16 C24250310
	NPT 1/8	0.91 (23.1)	0.33 (8.5)		7/16 C24250318
	NPT 1/4	0.91 (23.1)	0.41 (10.5)		9/16 C24250328
	NPT 3/8	0.95 (24.1)	0.45 (11.5)		11/16 C24250338
1/4	UNF 10/32	0.91 (23.2)	0.14 (3.6)	0.68 (17.3)	1/2 C24250410
	NPT 1/8	0.94 (23.8)	0.33 (8.5)		1/2 C24250418
	NPT 1/4	0.91 (23.2)	0.41 (10.5)		9/16 C24250428
	NPT 3/8	0.95 (24.2)	0.45 (11.5)		11/16 C24250438
5/16	NPT 1/2	1.07 (27.3)	0.57 (14.5)	0.72 (18.2)	7/8 C24250448
	NPT 1/8	1.11 (28.2)	0.33 (8.5)		9/16 C24250518
	NPT 1/4	1.02 (26.0)	0.41 (10.5)		9/16 C24250528
	NPT 3/8	1.04 (26.5)	0.45 (11.5)		11/16 C24250538
3/8	NPT 1/2	0.96 (24.5)	0.57 (14.5)	0.78 (19.9)	7/8 C24250548
	NTP 1/8	1.19 (30.1)	0.33 (8.5)		11/16 C24250618
	NTP 1/4	1.22 (31.1)	0.41 (10.5)		11/16 C24250628
	NPT 3/8	0.98 (24.8)	0.45 (11.5)		11/16 C24250638
1/2	NPT 1/2	0.94 (24.0)	0.57 (14.5)	0.91 (23.0)	7/8 C24250648
	NPT 1/8	1.31 (33.4)	0.33 (8.5)		7/8 C24250718
	NPT 1/4	1.39 (35.4)	0.41 (10.5)		7/8 C24250728
	NPT 3/8	1.26 (31.9)	0.45 (11.5)		7/8 C24250738
	NPT 1/2	1.24 (31.4)	0.57 (14.5)		7/8 C24250748

Pneufit C & Pneufit M composite fittings Inch



C242A


Straight Adaptor (Internal hex)



ØD	T	L	A	B	Hex	
5/32	UNF 10/32	0.82 (20.8)	0.14 (3.5)	0.60 (15.3)	0.09 (2.38)	C242A0210
5/32	NPT 1/8	0.83 (21.0)	0.33 (8.5)	0.60 (15.3)	0.13 (3.18)	C242A0218
5/32	NPT 1/4	0.87 (22.0)	0.41 (10.5)	0.60 (15.3)	0.13 (3.18)	C242A0228
3/16	UNF 10/32	0.88 (22.4)	0.14 (3.5)	0.67 (16.9)	0.09 (2.38)	C242A0310
3/16	NPT 1/8	0.89 (22.7)	0.33 (8.5)	0.67 (16.9)	0.13 (3.18)	C242A0318
3/16	NPT 1/4	0.93 (23.7)	0.41 (10.5)	0.67 (16.9)	0.13 (3.18)	C242A0328
1/4	UNF 10/32	0.90 (22.9)	0.14 (3.5)	0.69 (17.4)	0.09 (2.38)	C242A0410
1/4	NPT 1/8	0.93 (23.6)	0.33 (8.5)	0.69 (17.4)	0.19 (4.76)	C242A0418
1/4	NPT 1/4	0.94 (23.8)	0.41 (10.5)	0.69 (17.4)	0.19 (4.76)	C242A0428
5/16	NPT 1/8	1.08 (27.5)	0.33 (8.5)	0.74 (18.7)	0.16 (4.00)	C242A0518
5/16	NPT 1/4	1.00 (25.5)	0.41 (10.5)	0.74 (18.7)	0.24 (6.00)	C242A0528
5/16	NPT 3/8	1.00 (25.4)	0.45 (11.5)	0.74 (18.7)	0.24 (6.00)	C242A0538
3/8	NPT 1/8	1.13 (28.7)	0.33 (8.5)	0.80 (20.2)	0.25 (6.35)	C242A0618
3/8	NPT 1/4	1.11 (28.2)	0.41 (10.5)	0.80 (20.2)	0.25 (6.35)	C242A0628
3/8	NPT 3/8	1.11 (28.2)	0.45 (11.5)	0.80 (20.2)	0.31 (8.00)	C242A0638
3/8	NPT 1/2	1.15 (29.2)	0.57 (14.5)	0.80 (20.2)	0.31 (8.00)	C242A0648
1/2	NPT 1/4	1.39 (35.4)	0.41 (10.5)	0.87 (22.0)	0.37 (9.5)	C242A0728
1/2	NPT 3/8	1.30 (32.9)	0.45 (11.5)	0.87 (22.0)	0.37 (9.5)	C242A0738
1.2	NPT 1/2	1.30 (33.0)	0.57 (14.5)	0.87 (22.0)	0.37 (9.5)	C242A0748

C2426


Straight Adaptor (Female thread)



ØD	T	L	A	B	Hex	
5/32	NPT 1/8	1.09 (27.6)	0.37 (9.5)	0.60 (15.3)	0.55 (14.00)	C24260218
5/32	NPT 1/4	1.17 (29.6)	0.45 (11.5)	0.60 (15.3)	0.69 (17.46)	C24260228
3/16	NPT 1/8	1.11 (28.2)	0.37 (9.5)	0.66 (16.8)	0.55 (14.00)	C24260318
3/16	NPT 1/4	1.19 (30.2)	0.45 (11.5)	0.66 (16.8)	0.69 (17.46)	C24260328
1/4	NPT 1/8	1.13 (28.7)	0.37 (9.5)	0.69 (17.4)	0.55 (14.00)	C24260418
1/4	NPT 1/4	1.21 (30.7)	0.45 (11.5)	0.69 (17.4)	0.67 (17.00)	C24260428
1/4	NPT 3/8	1.29 (32.7)	0.49 (12.5)	0.69 (17.4)	0.87 (22.00)	C24260438
5/16	NPT 1/8	1.14 (29.0)	0.37 (9.5)	0.74 (18.7)	0.55 (14.00)	C24260518
5/16	NPT 1/4	1.22 (31.0)	0.45 (11.5)	0.74 (18.7)	0.67 (17.00)	C24260528
5/16	NPT 3/8	1.26 (32.0)	0.49 (12.5)	0.74 (18.7)	0.87 (22.00)	C24260538
5/16	NPT 1/2	1.41 (35.9)	0.57 (14.5)	0.74 (18.7)	1.00 (25.4)	C24260548
3/8	NPT 1/8	1.25 (31.8)	0.37 (9.5)	0.80 (20.2)	0.69 (17.46)	C24260618
3/8	NPT 1/4	1.28 (32.6)	0.45 (11.5)	0.80 (20.2)	0.67 (17.00)	C24260628
3/8	NPT 3/8	1.34 (34.1)	0.49 (12.5)	0.80 (20.2)	0.87 (22.00)	C24260638
3/8	NPT 1/2	1.49 (37.8)	0.57 (14.5)	0.80 (20.2)	1.00 (25.4)	C24260648
1/2	NPT 1/4	1.43 (36.2)	0.45 (11.5)	0.87 (22.0)	0.67 (17.00)	C24260728
1/2	NPT 3/8	1.48 (37.6)	0.49 (12.5)	0.87 (22.0)	0.87 (22.0)	C24260738

C2023


Stem Reducer (Stem/tube)



ØD2	ØD1	A	L	B	
5/32	1/8	0.73 (18.5)	1.25 (31.7)	0.44 (11.3)	C20230201
1/4	1/8	0.82 (20.9)	1.25 (31.7)	0.44 (11.3)	C20230401
1/4	5/32	0.93 (23.5)	1.59 (40.4)	0.64 (16.3)	C20230402
5/16	5/32	1.02 (26.0)	1.69 (42.9)	0.64 (16.3)	C20230502
5/16	1/4	1.17 (29.7)	1.89 (48.0)	0.69 (17.4)	C20230504
3/8	1/4	1.23 (31.3)	1.89 (48.0)	0.69 (17.4)	C20230604
3/8	5/16	0.98 (25.0)	1.76 (44.7)	0.74 (18.7)	C20230605
1/2	1/4	1.22 (30.9)	1.90 (48.3)	0.69 (17.4)	C20230704
1/2	5/16	1.31 (33.2)	1.91 (48.5)	0.74 (18.7)	C20230705
1/2	3/8	1.25 (31.8)	2.04 (51.8)	0.80 (20.2)	C20230706

C2029


Bulkhead Union



ØD	H	B	T	Hex	
5/32	1.40 (35.5)	0.64 (16.3)	M12*1.0p	5(14*16.1)	C20290200
3/16	1.44 (36.5)	0.66 (16.8)	M14*1.0p	5(17*19.6)	C20290300
1/4	1.53 (38.8)	0.69 (17.4)	M14*1.0p	5(17*19.6)	C20290400
5/16	1.66 (42.2)	0.74 (18.7)	M16*1.0p	5(19*21.9)	C20290500
3/8	1.70 (43.2)	0.80 (20.2)	M20*1.0p	5(24*27.7)	C20290600
1/2	1.95 (49.5)	0.87 (22.0)	M22*1.0p	5(26*30.0)	C20290700

C2432


Female Bulkhead



ØD	T1	L	E	T2	A	Hex1	B	Hex2	
5/32	NPT 1/8	1.07 (27.1)	0.20 (5)	M12*1.0p	0.35 (9)	14*16.1	0.64 (16.3)	14*16.1	C24320218
3/16	NPT 1/8	1.11 (28.3)	0.20 (5)	M12*1.0p	0.37 (9.5)	14*16.1	0.66 (16.8)	14*16.1	C24320318
3/16	NPT 1/4	1.19 (30.3)	0.20 (5)	M12*1.0p	0.45 (11.5)	14*16.1	0.66 (16.8)	14*16.1	C24320328
1/4	NPT 1/8	1.22 (30.9)	0.20 (5)	M14*1.0p	0.37 (9.5)	17*19.6	0.69 (17.4)	17*19.6	C24320418
1/4	NPT 1/4	1.22 (30.9)	0.20 (5)	M14*1.0p	0.45 (11.5)	17*19.6	0.69 (17.4)	17*19.6	C24320428
5/16	NPT 1/8	1.16 (29.5)	0.20 (5)	M16*1.0p	0.35 (9)	19*21.9	0.74 (18.7)	19*21.9	C24320518
5/16	NPT 1/4	1.24 (31.5)	0.20 (5)	M16*1.0p	0.43 (11)	19*21.9	0.74 (18.7)	19*21.9	C24320528
5/16	NPT 3/8	1.28 (32.5)	0.20 (5)	M16*1.0p	0.47 (12)	19*21.9	0.74 (18.7)	22*25.4	C24320538
3/8	NPT 1/4	1.31 (33.3)	0.20 (5)	M20*1.0p	0.45 (11.5)	24*27.7	0.80 (20.2)	24*27.7	C24320628
3/8	NPT 3/8	1.35 (34.3)	0.20 (5)	M20*1.0p	0.49 (12.5)	24*27.7	0.80 (20.2)	24*27.7	C24320638
1/2	NPT 1/4	1.54 (39.0)	0.20 (5)	M22*1.0p	0.49 (12.5)	26*30.0	0.87 (22.0)	24*27.7	C24320728
1/2	NPT 3/8	1.54 (39.0)	0.20 (5)	M22*1.0p	0.49 (12.5)	26*30.0	0.87 (22.0)	24*27.7	C24320738
1/2	NPT 1/2	1.61 (41.0)	0.20 (5)	M22*1.0p	0.57 (14.5)	26*30.0	0.87 (22.0)	24*27.7	C24320748

C2023


Stem Expander (Stem/tube)



ØD2	ØD1	A	L	B	
1/8	1/4	0.65 (16.5)	1.41 (35.8)	0.69 (17.4)	C20230104
5/32	1/4	0.73 (18.5)	1.49 (37.8)	0.69 (17.4)	C20230204

C2022


Stem Union



ØA	L	
5/32	1.42 (36.0)	C20220200
3/16	1.50 (38.0)	C20220300
1/4	1.57 (40.0)	C20220400
5/16	1.65 (42.0)	C20220500
3/8	1.77 (45.0)	C20220600
1/2	1.97 (50.0)	C20220700

C2022

Stem Union (Unequal)




ØA	ØB	C	D	L	
3/16	5/32	0.79 (20.0)	0.79 (20.0)	1.57 (40.0)	C20220302
1/4	5/32	0.83 (21.0)	0.79 (20.0)	1.61 (41.0)	C20220402
1/4	3/16	0.83 (21.0)	0.79 (20.0)	1.61 (41.0)	C20220403
5/16	1/4	0.87 (22.0)	0.83 (21.0)	1.69 (43.0)	C20220504
3/8	1/4	0.91 (23.0)	0.83 (21.0)	1.73 (44.0)	C20220604
3/8	5/16	0.91 (23.0)	0.87 (22.0)	1.77 (45.0)	C20220605
1/2	3/8	0.98 (25.0)	0.91 (23.0)	1.89 (48.0)	C20220706



Pneufit C & Pneufit M composite fittings Inch

C2004


Plug



ØD	D	A	L	
5/32	5/32	0.71 (18.0)	1.18 (30.0)	C00040400
3/16	3/16	0.75 (19.0)	1.30 (33.0)	C20040300
1/4	1/4	0.79 (20.0)	1.34 (34.0)	C20040400
5/16	5/16	0.87 (22.0)	1.50 (38.0)	C20040500
3/8	3/8	1.02 (26.0)	1.65 (42.0)	C20040600
1/2	1/2	1.10 (28.0)	1.81 (46.0)	C20040700

C2012


Cap (Female Plug)



ØD	B	ØC	L	
5/32	0.64 (16.3)	0.41 (10.5)	0.74 (18.9)	C20120200
3/16	0.66 (16.8)	0.45 (11.5)	0.74 (18.8)	C20120300
1/4	0.69 (17.4)	0.51 (13.0)	0.78 (19.9)	C20120400
5/16	0.74 (18.7)	0.57 (14.5)	0.85 (21.5)	C20120500
3/8	0.80 (20.2)	0.69 (17.5)	0.90 (22.8)	C20120600
1/2	0.87 (22.0)	0.83 (21.0)	1.02 (26.0)	C20120700

C2040


Union Elbow



ØD	H	L	C	B	D	
5/32	0.95 (24.2)	0.95 (24.2)	0.13 (3.3)	0.64 (16.3)	0.41 (10.5)	C020400200
3/16	1.00 (25.5)	1.00 (25.5)	0.14 (3.5)	0.66 (16.8)	0.45 (11.5)	C020400300
1/4	1.09 (27.8)	1.09 (27.8)	0.14 (3.5)	0.69 (17.4)	0.51 (13.0)	C020400400
5/16	1.21 (30.65)	1.21 (30.65)	0.17 (4.3)	0.74 (18.7)	0.57 (14.5)	C020400500
3/8	1.36 (34.6)	1.36 (34.6)	0.18 (4.5)	0.80 (20.2)	0.69 (17.5)	C020400600
1/2	1.61 (40.8)	1.61 (40.8)	0.18 (4.5)	0.87 (22.0)	0.83 (21.0)	C020400700

C2043


Stem Elbow



ØA	ØB	H	B	L	A	
5/32	5/32	0.74 (18.7)	0.64 (16.3)	1.48 (37.5)	0.94 (24.0)	C20430200
3/16	3/16	0.75 (19.1)	0.66 (16.8)	1.48 (37.5)	0.94 (24.0)	C20430300
1/4	1/4	0.81 (20.5)	0.69 (17.4)	1.61 (41.0)	0.98 (25.0)	C20430400
5/16	5/16	0.89 (22.7)	0.74 (18.7)	1.69 (42.9)	1.02 (26.0)	C20430500
3/8	3/8	0.94 (23.8)	0.80 (20.2)	1.80 (45.8)	1.10 (28.0)	C20430600
1/2	1/2	1.11 (28.3)	0.87 (22.0)	2.03 (51.5)	1.18 (30.0)	C20430700

C2447


90° Swivel Elbow Adaptor



ØD	T	D	L	H	A	B	Hex	
5/32	UNF 10/32	0.41 (10.5)	0.84 (21.4)	0.73 (18.6)	0.14 (3.6)	0.64 (16.2)	3/8	C24470210
	NPT 1/8		0.98 (25.0)		0.33 (8.5)		7/16	C24470218
	NPT 1/4		1.10 (28.0)		0.41 (10.5)		9/16	C24470228
3/16	UNF 10/32	0.45 (11.5)	0.92 (23.4)	0.75 (19.1)	0.14 (3.6)	0.66 (16.8)	7/16	C24470310
	NPT 1/8		0.98 (25.0)		0.33 (8.5)		7/16	C24470318
	NPT 1/4		1.10 (28.0)		0.41 (10.5)		9/16	C24470328
1/4	NPT 3/8	0.51 (13.0)	1.14 (29.0)	0.80 (20.4)	0.45 (11.5)	0.68 (17.3)	11/16	C24470338
	UNF 10/32		1.02 (25.9)		0.14 (3.6)		1/2	C24470410
	NPT 1/8		1.09 (27.8)		0.33 (8.5)		1/2	C24470418
5/16	NPT 1/4	0.57 (14.5)	1.20 (30.5)	0.88 (22.3)	0.41 (10.5)	0.72 (18.2)	9/16	C24470428
	NPT 3/8		1.24 (31.5)		0.45 (11.5)		11/16	C24470438
	NPT 1/2		1.16 (29.4)		0.33 (8.5)		9/16	C24470518
3/8	NPT 1/4	0.69 (17.5)	1.24 (31.4)	0.94 (23.9)	0.41 (10.5)	0.78 (19.9)	9/16	C24470528
	NPT 3/8		1.28 (32.4)		0.45 (11.5)		11/16	C24470538
	NPT 1/2		1.39 (35.4)		0.57 (14.5)		7/8	C24470548
1/2	NPT 1/8	0.83 (21.0)	1.18 (30.0)	1.12 (28.5)	0.33 (8.5)	0.91 (23.0)	11/16	C24470618
	NPT 1/4		1.26 (32.0)		0.41 (10.5)		11/16	C24470628
	NPT 3/8		1.30 (33.0)		0.45 (11.5)		11/16	C24470638
1/2	NPT 1/2	0.83 (21.0)	1.42 (36.0)	1.12 (28.5)	0.57 (14.5)	0.91 (23.0)	7/8	C24470648
	NPT 1/4		1.40 (35.5)		0.41 (10.5)		3/4	C24470728
	NPT 3/8		1.44 (36.5)		0.45 (11.5)		3/4	C24470738
1/2	NPT 1/2	0.83 (21.0)	1.56 (39.5)	1.12 (28.5)	0.57 (14.5)	0.91 (23.0)	7/8	C24470748

C2454

90° Swivel Elbow Adaptor (Extended)



ØD	T	D	L	H	A	B	Hex	
5/32	UNF 10/32	0.41 (10.5)	1.28 (32.5)	0.73 (18.6)	0.14 (3.6)	0.64 (16.2)	3/8	C24540210
	NPT 1/8		1.40 (35.5)		0.33 (8.5)		7/16	C24540218
	NPT 1/4		1.52 (38.5)		0.41 (10.5)		9/16	C24540228
3/16	NPT 1/8	0.45 (11.5)	1.38 (35.0)	0.75 (19.1)	0.33 (8.5)	0.66 (16.8)	7/16	C24540318
	NPT 1/4		1.52 (38.5)		0.41 (10.5)		9/16	C24540328
	NPT 3/8		1.52 (38.5)		0.45 (11.5)		11/16	C24540338
1/4	UNF 10/32	0.51 (13.0)	1.48 (37.5)	0.80 (20.4)	0.14 (3.6)	0.68 (17.3)	1/2	C24540410
	NPT 1/8		1.63 (41.3)		0.33 (8.5)		1/2	C24540418
	NPT 1/4		1.73 (44.0)		0.41 (10.5)		9/16	C24540428
5/16	NPT 3/8	0.57 (14.5)	1.77 (45.0)	0.88 (22.3)	0.45 (11.5)	0.72 (18.2)	11/16	C24540438
	UNF 10/32		1.48 (37.5)		0.14 (3.6)		1/2	C24540410
	NPT 1/8		1.63 (41.3)		0.33 (8.5)		1/2	C24540418
3/8	NPT 1/4	0.69 (17.5)	1.83 (46.4)	0.94 (23.9)	0.41 (10.5)	0.78 (19.9)	9/16	C24540428
	NPT 3/8		1.98 (50.4)		0.45 (11.5)		11/16	C24540438
	NPT 1/2		1.89 (48.0)		0.33 (8.5)		9/16	C24540518
1/2	NPT 1/4	0.83 (21.0)	2.01 (51.0)	1.12 (28.5)	0.41 (10.5)	0.91 (23.0)	11/16	C24540528
	NPT 3/8		2.13 (54.0)		0.45 (11.5)		11/16	C24540538
	NPT 1/2		2.26 (57.5)		0.57 (14.5)		7/8	C24540648
1/2	NPT 1/4	0.83 (21.0)	2.26 (57.5)	1.12 (28.5)	0.41 (10.5)	0.91 (23.0)	3/4	C24540728
	NPT 3/8		2.30 (58.5)		0.45 (11.5)		3/4	C24540738
	NPT 1/2		2.42 (61.5)		0.57 (14.5)		7/8	C24540748


Pneufit C & Pneufit M composite fittings Inch




C2448

90° Swivel Elbow Adaptor

(Female)




ØD	T	D	L	H	A	B	Hex
5/32	UNF 10/32	0.41 (10.5)	0.85 (21.5)	0.73 (18.6)	0.28 (7.0)	0.64 (16.2)	0.39 (10) C24480210
	NPT 1/8		0.89 (22.5)		0.35 (9.0)		0.55 (14) C24480218
	NPT 1/4		0.89 (22.5)		0.35 (9.0)		0.69 (17.46) C24480228
3/16	UNF 10/32	0.45 (11.5)	0.81 (20.5)	0.75 (19.1)	0.28 (7.0)	0.66 (16.8)	0.43 (11) C24480310
	NPT 1/8		0.89 (22.5)		0.35 (9.0)		0.69 (17.46) C24480328
	NPT 1/4		0.89 (22.5)		0.35 (9.0)		0.69 (17.46) C24480338
1/4	UNF 10/32	0.51 (13.0)	0.83 (21.0)	0.80 (20.4)	0.20 (5.0)	0.68 (17.3)	0.50 (12.7) C24480410
	NPT 1/8		0.98 (25.0)		0.35 (9.0)		0.55 (14) C24480418
	NPT 1/4		1.06 (27.0)		0.43 (11.0)		0.69 (17.46) C24480428
5/16	NPT 3/8	0.57 (14.5)	1.10 (28.0)	0.88 (22.3)	0.47 (12.0)	0.72 (18.2)	0.87 (22) C24480438
	NPT 1/8		1.02 (25.9)		0.35 (9.0)		0.55 (14) C24480518
	NPT 1/4		1.10 (27.9)		0.43 (11.0)		0.69 (17.46) C24480528
3/8	NPT 3/8	0.69 (17.5)	1.14 (28.9)	0.94 (23.9)	0.47 (12.0)	0.78 (19.9)	0.87 (22) C24480538
	NPT 1/4		1.12 (28.5)		0.43 (11.0)		0.69 (17.46) C24480628
	NPT 1/2		1.16 (29.5)		0.47 (12.0)		0.87 (22) C24480638
1/2	NPT 3/8	0.83 (21.0)	1.30 (33.0)	1.12 (28.5)	0.57 (14.5)	0.91 (23.0)	0.96 (24.5) C24480648
	NPT 1/2		1.44 (36.5)		0.47 (12.0)		0.87 (22) C24480738



C2R51

Banjo

L	T	H	ØD	B	A	Hex
0.72 (18.2)	UNF 10/32	0.99 (25.1)	5/32	0.64 (16.3)	0.14 (3.6)	0.31 (8.0) C2R510210
0.72 (18.2)	UNF 10/32	1.05 (26.6)	3/16	0.66 (16.8)	0.14 (3.6)	0.31 (8.0) C2R510310
0.72 (18.2)	UNF 10/32	1.13 (28.7)	1/4	0.69 (17.4)	0.14 (3.6)	0.31 (8.0) C2R510410
0.98 (25.0)	NPT 1/8	1.20 (30.5)	5/32	0.64 (16.3)	0.31 (8.0)	0.43 (11.0) C2R510218
0.98 (25.0)	NPT 1/8	1.24 (31.4)	3/16	0.66 (16.8)	0.31 (8.0)	0.43 (11.0) C2R510318
0.98 (25.0)	NPT 1/8	1.26 (32.0)	1/4	0.69 (17.4)	0.31 (8.0)	0.43 (11.0) C2R510418
0.98 (25.0)	NPT 1/8	1.30 (33.0)	5/16	0.74 (18.7)	0.31 (8.0)	0.43 (11.0) C2R510518
1.13 (28.8)	NPT 1/4	1.39 (35.3)	3/16	0.66 (16.8)	0.39 (10.0)	0.59 (15.0) C2R510328
1.13 (28.8)	NPT 1/4	1.41 (35.9)	1/4	0.69 (17.4)	0.39 (10.0)	0.59 (15.0) C2R510428
1.13 (28.8)	NPT 1/4	1.45 (36.8)	5/16	0.74 (18.7)	0.39 (10.0)	0.59 (15.0) C2R510528
1.13 (28.8)	NPT 1/4	1.48 (37.5)	3/8	0.80 (20.2)	0.39 (10.0)	0.59 (15.0) C2R510628
1.33 (33.7)	NPT 3/8	1.58 (40.1)	5/16	0.74 (18.7)	0.43 (11.0)	0.75 (19.0) C2R510538
1.33 (33.7)	NPT 3/8	1.66 (42.1)	3/8	0.80 (20.2)	0.43 (11.0)	0.75 (19.0) C2R510638
1.33 (33.7)	NPT 3/8	1.78 (45.1)	1/2	0.87 (22.0)	0.43 (11.0)	0.75 (19.0) C2R510738
1.55 (39.4)	NPT 1/2	1.86 (47.3)	3/8	0.80 (20.2)	0.55 (14.0)	0.94 (24.0) C2R510648
1.55 (39.4)	NPT 1/2	1.99 (50.5)	1/2	0.87 (22.0)	0.55 (14.0)	0.94 (24.0) C2R510748



C2D51


Banjo with Top Port

L	T	H	ØD	B	A1	A2	Hex
0.79 (20.0)	UNF 10/32	1.13 (28.7)	1/4	0.52 (13.1)	0.14 (3.6)	0.24 (6.0)	5/16 C2D510410
1.22 (30.9)	NPT 1/8	1.21 (30.8)	5/32	0.64 (16.2)	0.33 (8.5)	0.33 (8.5)	9/16 C2E510218
1.22 (30.9)	NPT 1/8	1.26 (32.0)	1/4	0.69 (17.4)	0.33 (8.5)	0.33 (8.5)	9/16 C2E510418
1.22 (30.9)	NPT 1/8	1.33 (33.7)	5/16	0.75 (19.1)	0.33 (8.5)	0.33 (8.5)	9/16 C2E510518
1.41 (35.8)	NPT 1/4	1.41 (35.9)	1/4	0.69 (17.4)	0.41 (10.5)	0.43 (11.0)	11/16 C2F510428
1.41 (35.8)	NPT 1/4	1.48 (37.6)	5/16	0.75 (19.1)	0.41 (10.5)	0.43 (11.0)	11/16 C2F510528
1.41 (35.8)	NPT 1/4	1.58 (40.1)	3/8	0.80 (20.2)	0.41 (10.5)	0.43 (11.0)	11/16 C2F510628
1.61 (41.0)	NPT 3/8	1.66 (42.1)	3/8	0.78 (19.8)	0.45 (11.5)	0.51 (13.0)	7/8 C2G510638
1.61 (41.0)	NPT 3/8	1.78 (45.2)	1/2	0.87 (22.0)	0.45 (11.5)	0.51 (13.0)	7/8 C2G510738

C2VA0

Banjo Flow Control

(Regulating out)




MI	L	MA	T	H	ØD	B	A	HEX
1.07 (27.2)	1.19 (30.2)	UNF 10/32	0.85 (21.5)	1/8	0.44 (11.1)	0.14 (3.6)	0.31 (8.0)	C2VA00110
1.07 (27.2)	1.19 (30.2)	UNF 10/32	0.99 (25.1)	5/32	0.64 (16.3)	0.14 (3.6)	0.31 (8.0)	C2VA00210
1.07 (27.2)	1.19 (30.2)	UNF 10/32	1.05 (26.6)	3/16	0.66 (16.8)	0.14 (3.6)	0.31 (8.0)	C2VA00310
1.07 (27.2)	1.19 (30.2)	UNF 10/32	1.13 (28.7)	1/4	0.69 (17.4)	0.14 (3.6)	0.31 (8.0)	C2VA00410
1.37 (34.9)	1.58 (40.1)	NPT 1/8	1.20 (30.5)	5/32	0.64 (16.3)	0.31 (8.0)	0.43 (11.0)	C2VA00218
1.37 (34.9)	1.58 (40.1)	NPT 1/8	1.24 (31.4)	3/16	0.66 (16.8)	0.31 (8.0)	0.43 (11.0)	C2VA00318
1.37 (34.9)	1.58 (40.1)	NPT 1/8	1.26 (32.0)	1/4	0.69 (17.4)	0.31 (8.0)	0.43 (11.0)	C2VA00418
1.37 (34.9)	1.58 (40.1)	NPT 1/8	1.30 (33.0)	5/16	0.74 (18.7)	0.31 (8.0)	0.43 (11.0)	C2VA00518
1.57 (40.0)	1.80 (45.7)	NPT 1/4	1.36 (34.5)	5/32	0.64 (16.3)	0.39 (10.0)	0.59 (15.0)	C2VA00228
1.57 (40.0)	1.80 (45.7)	NPT 1/4	1.39 (35.3)	3/16	0.66 (16.8)	0.39 (10.0)	0.59 (15.0)	C2VA00328
1.57 (40.0)	1.80 (45.7)	NPT 1/4	1.41 (35.9)	1/4	0.69 (17.4)	0.39 (10.0)	0.59 (15.0)	C2VA00428
1.57 (40.0)	1.80 (45.7)	NPT 1/4	1.45 (36.8)	5/16	0.74 (18.7)	0.39 (10.0)	0.59 (15.0)	C2VA00528
1.57 (40.0)	1.80 (45.7)	NPT 1/4	1.48 (37.5)	3/8	0.80 (20.2)	0.39 (10.0)	0.59 (15.0)	C2VA00628
1.84 (46.7)	2.17 (55.0)	NPT 3/8	1.54 (39.1)	3/16	0.66 (16.8)	0.43 (11.0)	0.75 (19.0)	C2VA00338
1.84 (46.7)	2.17 (55.0)	NPT 3/8	1.56 (39.7)	1/4	0.69 (17.4)	0.43 (11.0)	0.75 (19.0)	C2VA00438
1.84 (46.7)	2.17 (55.0)	NPT 3/8	1.58 (40.1)	5/16	0.74 (18.7)	0.43 (11.0)	0.75 (19.0)	C2VA00538
1.84 (46.7)	2.17 (55.0)	NPT 3/8	1.66 (42.1)	3/8	0.80 (20.2)	0.43 (11.0)	0.75 (19.0)	C2VA00638
1.84 (46.7)	2.17 (55.0)	NPT 3/8	1.78 (45.1)	1/2	0.87 (22.0)	0.43 (11.0)	0.75 (19.0)	C2VA00738
2.09 (53.0)	2.37 (60.2)	NPT 1/2	1.80 (45.8)	5/16	0.74 (18.7)	0.55 (14.0)	0.94 (24.0)	C2VA00548
2.09 (53.0)	2.37 (60.2)	NPT 1/2	1.86 (47.3)	3/8	0.80 (20.2)	0.55 (14.0)	0.94 (24.0)	C2VA00648
2.09 (53.0)	2.37 (60.2)	NPT 1/2	1.99 (50.5)	1/2	0.87 (22.0)	0.55 (14.0)	0.94 (24.0)	C2VA00748

Please see Speed Controllers Flowrate on page 14

C2WA0

Banjo Flow Control

(Regulating in)



MI	L	MA	T	H	ØD	B	A	HEX
1.07 (27.2)	1.19 (30.2)	UNF 10/32	0.85 (21.5)	1/8	0.44 (11.1)	0.14 (3.6)	0.31 (8.0)	C2WA00110
1.07 (27.2)	1.19 (30.2)	UNF 10/32	0.99 (25.1)	5/32	0.64 (16.3)	0.14 (3.6)	0.31 (8.0)	C2WA00210
1.07 (27.2)	1.19 (30.2)	UNF 10/32	1.03 (26.2)	3/16	0.66 (16.8)	0.14 (3.6)	0.31 (8.0)	C2WA00310
1.07 (27.2)	1.19 (30.2)	UNF 10/32	1.13 (28.7)	1/4	0.69 (17.4)	0.14 (3.6)	0.31 (8.0)	C2WA00410
1.37 (34.9)	1.58 (40.1)	NPT 1/8	1.20 (30.5)	5/32	0.64 (16.3)	0.31 (8.0)	0.43 (11.0)	C2WA00218
1.37 (34.9)	1.58 (40.1)	NPT 1/8	1.24 (31.4)	3/16	0.66 (16.8)	0.31 (8.0)	0.43 (11.0)	C2WA00318
1.37 (34.9)	1.58 (40.1)	NPT 1/8	1.26 (32.0)	1/4	0.69 (17.4)	0.31 (8.0)	0.43 (11.0)	C2WA00418
1.37 (34.9)	1.58 (40.1)	NPT 1/8	1.30 (33.0)	5/16	0.74 (18.7)	0.31 (8.0)	0.43 (11.0)	C2WA00518
1.57 (40.0)	1.80 (45.7)	NPT 1/4	1.36 (34.5)	5/32	0.64 (16.3)	0.39 (10.0)	0.59 (15.0)	C2WA00228
1.57 (40.0)	1.80 (45.7)	NPT 1/4	1.39 (35.3)	3/16	0.66 (16.8)	0.39 (10.0)	0.59 (15.0)	C2WA00328
1.57 (40.0)	1.80 (45.7)	NPT 1/4	1.41 (35.9)	1/4	0.69 (17.4)	0.39 (10.0)	0.59 (15.0)	C2WA00428
1.57 (40.0)	1.80 (45.7)	NPT 1/4	1.45 (36.8)	5/16	0.74 (18.7)	0.39 (10.0)	0.59 (15.0)	C2WA00528
1.57 (40.0)	1.80 (45.7)	NPT 1/4	1.48 (37.5)	3/8	0.80 (20.2)	0.39 (10.0)	0.59 (15.0)	C2WA00628
1.84 (46.7)	2.17 (55.0)	NPT 3/8	1.54 (39.1)	3/16	0.66 (16.8)	0.43 (11.0)	0.75 (19.0)	C2WA00338
1.84 (46.7)	2.17 (55.0)	NPT 3/8	1.56 (39.7)	1/4	0.69 (17.4)	0.43 (11.0)	0.75 (19.0)	C2WA00438
1.84 (46.7)	2.17 (55.0)	NPT 3/8	1.58 (40.1)	5/16	0.74 (18.7)	0.43 (11.0)	0.75 (19.0)	C2WA00538
1.84 (46.7)	2.17 (55.0)	NPT 3/8	1.66 (42.1)	3/8	0.80 (20.2)	0.43 (11.0)	0.75 (19.0)	C2WA00638
1.84 (46.7)	2.17 (55.0)	NPT 1/2	1.78 (45.1)	1/2	0.87 (22.0)	0.43 (11.0)	0.75 (19.0)	C2WA00738
2.09 (53.0)	2.37 (60.2)	NPT 1/2	1.80 (45.8)	5/16	0.74 (18.7)	0.55 (14.0)	0.94 (24.0)	C2WA00548
2.09 (53.0)	2.37 (60.2)	NPT 1/2	1.86 (47.3)	3/8	0.80 (20.2)	0.55 (14.0)	0.94 (24.0)	C2WA00648
2.09 (53.0)	2.37 (60.2)	NPT 1/2	1.99 (50.5)	1/2	0.87 (22.0)	0.55 (14.0)	0.94 (24.0)	C2WA00748


Please see Speed Controllers Flowrate on page 14



Pneufit C & Pneufit M composite fittings Inch

C2VB0


Shrouded Banjo



L	T	H	ØD	B	A	Hex	
0.91 (23.2)	UNF 10/32	0.85 (21.5)	1/8	0.44 (11.1)	0.14 (3.6)	0.31 (8.0)	C2VB00110
0.91 (23.2)	UNF 10/32	0.99 (25.1)	5/32	0.64 (16.3)	0.14 (3.6)	0.31 (8.0)	C2VB00210
0.91 (23.2)	UNF 10/32	1.13 (28.7)	1/4	0.69 (17.4)	0.14 (3.6)	0.31 (8.0)	C2VB00410
1.24 (31.6)	NPT 1/8	1.20 (30.5)	5/32	0.64 (16.3)	0.31 (8.0)	0.43 (11.0)	C2VB00218
1.24 (31.6)	NPT 1/8	1.26 (32.0)	1/4	0.69 (17.4)	0.31 (8.0)	0.43 (11.0)	C2VB00418
1.24 (31.6)	NPT 1/8	1.30 (33.0)	5/16	0.74 (18.7)	0.31 (8.0)	0.43 (11.0)	C2VB00518
1.46 (37.0)	NPT 1/4	1.36 (34.5)	5/32	0.64 (16.3)	0.39 (10.0)	0.59 (15.0)	C2VB00228
1.46 (37.0)	NPT 1/4	1.41 (35.9)	1/4	0.69 (17.4)	0.39 (10.0)	0.59 (15.0)	C2VB00428
1.46 (37.0)	NPT 1/4	1.45 (36.8)	5/16	0.74 (18.7)	0.39 (10.0)	0.59 (15.0)	C2VB00528
1.46 (37.0)	NPT 1/4	1.48 (37.5)	3/8	0.80 (20.2)	0.39 (10.0)	0.59 (15.0)	C2VB00628
1.70 (43.3)	NPT 3/8	1.56 (39.7)	1/4	0.69 (17.4)	0.43 (11.0)	0.75 (19.0)	C2VB00438
1.70 (43.3)	NPT 3/8	1.58 (40.1)	5/16	0.74 (18.7)	0.43 (11.0)	0.75 (19.0)	C2VB00538
1.70 (43.3)	NPT 3/8	1.66 (42.1)	3/8	0.80 (20.2)	0.43 (11.0)	0.75 (19.0)	C2VB00638
1.70 (43.3)	NPT 3/8	1.78 (45.1)	1/2	0.87 (22.0)	0.43 (11.0)	0.75 (19.0)	C2VB00738
1.98 (50.2)	NPT 1/2	1.80 (45.8)	5/16	0.74 (18.7)	0.55 (14.0)	0.94 (24.0)	C2VB00548
1.98 (50.2)	NPT 1/2	1.86 (47.3)	3/8	0.80 (20.2)	0.55 (14.0)	0.94 (24.0)	C2VB00648
1.98 (50.2)	NPT 1/2	1.99 (50.5)	1/2	0.87 (22.0)	0.55 (14.0)	0.94 (24.0)	C2VB00748

C24GE

In-Line Flow Control




L						
MIN	MAX	C	H	ØD	B	
1.18 (29.9)	1.31 (33.3)	0.13 (3.3)	1.78 (45.1)	5/32	0.64 (16.3)	C24GE0200
1.38 (35.0)	1.56 (39.5)	0.17 (4.3)	1.98 (50.3)	3/16	0.66 (16.8)	C24GE0300
1.38 (35.0)	1.56 (39.5)	0.17 (4.3)	1.98 (50.3)	1/4	0.69 (17.4)	C24GE0400
1.47 (37.4)	1.66 (42.1)	0.17 (4.4)	2.19 (55.7)	5/16	0.74 (18.7)	C24GE0500
1.72 (43.8)	1.93 (49.0)	0.17 (4.4)	2.41 (61.2)	3/8	0.80 (20.2)	C24GE0600
1.87 (47.4)	2.11 (53.6)	0.17 (4.4)	2.75 (69.8)	1/2	0.87 (22.0)	C24GE0700

Please see Speed Controllers Flowrate on page 15

C2060

Union Tee




ØD	H	L	C	B	
5/32	1.44 (36.6)	0.95 (24.2)	0.13 (3.3)	0.64 (16.3)	C20600200
3/16	1.56 (39.5)	1.00 (25.5)	0.14 (3.5)	0.66 (16.8)	C20600300
1/4	1.68 (42.6)	1.09 (27.8)	0.14 (3.5)	0.69 (17.4)	C20600400
5/16	1.77 (44.9)	1.21 (30.6)	0.17 (4.3)	0.74 (18.7)	C20600500
3/8	2.03 (51.6)	1.36 (34.6)	0.18 (4.5)	0.80 (20.2)	C20600600
1/2	2.38 (60.5)	1.61 (40.8)	0.18 (4.5)	0.87 (22.0)	C20600700

C206A

Union Tee


(unequal)



ØA	ØB	B1	B2	C	L	H	
1/4	5/32	0.69 (17.4)	0.64 (16.3)	0.14 (3.5)	1.05 (26.6)	1.60 (40.6)	C206A0402
5/16	1/4	0.74 (18.7)	0.69 (17.4)	0.14 (3.5)	1.12 (28.4)	1.70 (43.2)	C206A0504
3/8	1/4	0.80 (20.2)	0.69 (17.4)	0.18 (4.5)	1.27 (32.2)	1.91 (48.6)	C206A0604
3/8	5/16	0.80 (20.2)	0.74 (18.7)	0.18 (4.5)	1.32 (33.5)	1.99 (50.6)	C206A0605
1/2	1/4	0.87 (22.0)	0.69 (17.4)	0.18 (4.5)	1.68 (42.7)	2.38 (60.5)	C206A0704
1/2	3/8	0.87 (22.0)	0.80 (20.2)	0.18 (4.5)	1.45 (36.8)	2.30 (58.5)	C206A0706

C2467


Swivel Tee Adaptor



ØD	T	D	L	H	A	B	Hex	
5/32	UNF 10/32	0.41 (10.5)	0.84 (21.4)	1.46 (37.0)	0.14 (3.6)	0.64 (16.2)	3/8	C24670210
	NPT 1/8		0.98 (25.0)		0.33 (8.5)		7/16	C24670218
	NPT 1/4		1.10 (28.0)		0.41 (10.5)		9/16	C24670228
3/16	UNF 10/32	0.45 (11.5)	0.92 (23.4)	1.50 (38.2)	0.14 (3.6)	0.66 (16.8)	7/16	C24670310
	NPT 1/8		0.98 (25.0)		0.33 (8.5)		7/16	C24670318
	NPT 1/4		1.10 (28.0)		0.41 (10.5)		9/16	C24670328
1/4	NPT 3/8	0.51 (13.0)	1.14 (29.0)	1.61 (40.8)	0.45 (11.5)	0.68 (17.3)	11/16	C24670338
	UNF 10/32		1.02 (25.9)		0.14 (3.6)		1/2	C24670410
	NPT 1/8		1.09 (27.8)		0.33 (8.5)		1/2	C24670418
5/16	NPT 1/4	0.57 (14.5)	1.20 (30.5)	1.72 (43.7)	0.41 (10.5)	0.72 (18.2)	9/16	C24670428
	NPT 3/8		1.24 (31.5)		0.45 (11.5)		11/16	C24670438
	NPT 1/2		1.39 (35.4)		0.57 (14.5)		7/8	C24670548
3/8	NPT 1/8	0.69 (17.5)	1.18 (30.0)	1.88 (47.7)	0.33 (8.5)	0.78 (19.9)	11/16	C24670618
	NPT 1/4		1.26 (32.0)		0.41 (10.5)		11/16	C24670628
	NPT 3/8		1.30 (33.0)		0.45 (11.5)		11/16	C24670638
1/2	NPT 1/2	0.83 (21.0)	1.42 (36.0)	2.22 (56.5)	0.57 (14.5)	0.91 (23.0)	7/8	C24670648
	NPT 1/4		1.40 (35.5)		0.41 (10.5)		3/4	C24670728
	NPT 3/8		1.44 (36.5)		0.45 (11.5)		3/4	C24670738
	NPT 1/2		1.56 (39.5)		0.57 (14.5)		7/8	C24670748

C2468

Swivel Side Tee Adaptor



ØD	T	D	L	H	A	B	Hex	
5/32	UNF 10/32	0.41 (10.5)	1.66 (42.1)	0.98 (25.0)	0.14 (3.6)	0.64 (16.2)	3/8	C24680210
	NPT 1/8		1.80 (45.7)		0.33 (8.5)		7/16	C24680218
	NPT 1/4		1.92 (48.7)		0.41 (10.5)		9/16	C24680228
3/16	UNF 10/32	0.45 (11.5)	1.63 (41.5)	0.99 (25.1)	0.14 (3.6)	0.66 (16.8)	7/16	C24680310
	NPT 1/8		1.78 (45.1)		0.33 (8.5)		7/16	C24680318
	NPT 1/4		1.89 (48.1)		0.41 (10.5)		9/16	C24680328
1/4	NPT 3/8	0.51 (13.0)	1.93 (49.1)	1.10 (28.0)	0.45 (11.5)	0.68 (17.3)	11/16	C24680338
	UNF 10/32		1.87 (47.4)		0.14 (3.6)		1/2	C24680410
	NPT 1/8		1.94 (49.3)		0.33 (8.5)		1/2	C24680418
5/16	NPT 1/4	0.57 (14.5)	2.05 (52.0)	1.22 (30.9)	0.41 (10.5)	0.72 (18.2)	9/16	C24680428
	NPT 3/8		2.09 (53.0)		0.45 (11.5)		11/16	C24680438
	NPT 1/2		2.11 (53.7)		0.57 (14.5)		7/8	C24680518
3/8	NPT 1/8	0.69 (17.5)	2.19 (55.7)	1.37 (34.7)	0.41 (10.5)	0.78 (19.9)	9/16	C24680528
	NPT 1/4		2.23 (56.7)		0.45 (11.5)		11/16	C24680538
	NPT 3/8		2.35 (59.7)		0.57 (14.5)		7/8	C24680548
1/2	NPT 1/8	0.83 (21.0)	2.49 (63.3)	1.61 (40.8)	0.33 (8.5)	0.91 (23.0)	11/16	C24680618
	NPT 1/4		2.57 (65.3)		0.41 (10.5)		11/16	C24680628
	NPT 3/8		2.61 (66.3)		0.45 (11.5)		11/16	C24680638
	NPT 1/2		2.73 (69.3)		0.57 (14.5)		7/8	C24680648
	NPT 1/4		2.26 (57.3)		0.41 (10.5)		3/4	C24680728
	NPT 3/8		2.30 (58.3)		0.45 (11.5)		3/4	C24680738
	NPT 1/2		2.41 (61.3)		0.57 (14.5)		7/8	C24680748


Pneufit C & Pneufit M composite fittings Inch



C2063

Stem Tee

(equal and unequal)




ØA	ØB	A	L	H	B	
5/32	5/32	0.94 (24.0)	1.48 (37.5)	1.46 (37.0)	0.64 (16.3)	C20630200
3/16	3/16	0.94 (24.0)	1.48 (37.5)	1.50 (38.2)	0.66 (16.8)	C20630300
1/4	1/4	0.98 (25.0)	1.61 (41.0)	1.61 (40.8)	0.69 (17.4)	C20630400
5/16	5/16	1.02 (26.0)	1.69 (43.0)	1.72 (43.7)	0.74 (18.7)	C20630500
3/8	3/8	1.13 (28.8)	1.80 (45.8)	1.88 (47.7)	0.80 (20.2)	C20630600
1/2	1/2	1.18 (30.0)	2.03 (51.5)	2.22 (56.5)	0.87 (22.0)	C20630700
1/4	5/32	0.98 (25.0)	1.52 (38.5)	1.46 (37.0)	0.64 (16.3)	C20630402
5/16	1/4	1.02 (26.0)	1.65 (42.0)	1.61 (40.8)	0.69 (17.4)	C20630504
3/8	1/4	1.10 (28.0)	1.74 (44.3)	1.61 (40.8)	0.69 (17.4)	C20630604
3/8	5/16	1.10 (28.0)	1.78 (45.3)	1.72 (43.7)	0.74 (18.7)	C20630605
1/2	3/8	1.18 (30.0)	1.89 (48.0)	1.88 (47.7)	0.80 (20.2)	C20630706

C2082

Union Y

(equal)




ØD	H	L	B	E	C	
5/32	0.83 (21.0)	1.46 (37.1)	0.64 (16.3)	0.41 (10.5)	0.13 (3.3)	C20820200
3/16	0.91 (23.0)	1.46 (37.1)	0.66 (16.8)	0.45 (11.5)	0.13 (3.3)	C20820300
1/4	1.02 (26.0)	1.57 (39.8)	0.69 (17.4)	0.51 (13.0)	0.13 (3.3)	C20820400
5/16	1.14 (29.0)	1.71 (43.4)	0.74 (18.7)	0.57 (14.5)	0.17 (4.3)	C20820500
3/8	1.38 (35.0)	1.88 (47.7)	0.77 (19.6)	0.69 (17.5)	0.17 (4.3)	C20820600
1/2	1.65 (42.0)	2.15 (54.5)	0.87 (22.0)	0.83 (21.0)	0.18 (4.5)	C20820700

C2064

Stem Side Tee

(equal and unequal)




ØA	ØB	A	L	H	B	
5/32	5/32	0.94 (24.0)	2.29 (58.2)	0.98 (25.0)	0.64 (16.3)	C20640200
3/16	3/16	0.94 (24.0)	2.27 (57.6)	0.99 (25.1)	0.66 (16.8)	C20640300
1/4	1/4	0.98 (25.0)	2.46 (62.5)	1.10 (28.0)	0.69 (17.4)	C20640400
5/16	5/16	1.02 (26.0)	2.65 (67.2)	1.22 (30.9)	0.74 (18.7)	C20640500
3/8	3/8	1.10 (28.0)	2.87 (73.0)	1.37 (34.7)	0.80 (20.2)	C20640600
1/2	1/2	1.18 (30.0)	3.22 (81.8)	1.61 (40.8)	0.87 (22.0)	C20640700
1/4	5/32	0.98 (25.0)	2.33 (59.2)	0.98 (25.0)	0.64 (16.3)	C20640402
5/16	1/4	1.02 (26.0)	2.50 (63.5)	1.10 (28.0)	0.69 (17.4)	C20640504
3/8	1/4	1.10 (28.0)	2.59 (65.8)	1.10 (28.0)	0.69 (17.4)	C20640604
3/8	5/16	1.10 (28.0)	2.74 (69.5)	1.22 (30.9)	0.74 (18.7)	C20640605
1/2	3/8	1.18 (30.0)	2.96 (75.2)	1.37 (34.7)	0.80 (20.2)	C20640706

C2082

Union Y

(Unequal)




ØA	ØB	L	H	B1	B2	ØE	ØF	C	
3/16	5/32	1.46 (37.0)	0.83 (21.0)	0.66 (16.8)	0.64 (16.3)	0.45 (11.5)	0.41 (10.5)	0.13 (3.3)	C20820302
1/4	5/32	1.50 (38.1)	0.83 (21.0)	0.69 (17.4)	0.64 (16.3)	0.51 (13.0)	0.41 (10.5)	0.13 (3.3)	C20820402
1/4	3/16	1.52 (38.7)	0.91 (23.0)	0.69 (17.4)	0.66 (16.8)	0.51 (13.0)	0.45 (11.5)	0.13 (3.3)	C20820403
5/16	1/4	1.66 (42.1)	1.02 (26.0)	0.74 (18.7)	0.69 (17.4)	0.57 (14.6)	0.51 (13.0)	0.13 (3.3)	C20820504
3/8	1/4	1.70 (43.2)	1.02 (26.0)	0.77 (19.6)	0.69 (17.4)	0.69 (17.5)	0.51 (13.0)	0.13 (3.3)	C20820604
3/8	5/16	1.70 (43.3)	1.14 (29.0)	0.77 (19.6)	0.74 (18.7)	0.69 (17.5)	0.57 (14.5)	0.17 (4.3)	C20820605
1/2	3/8	2.00 (50.8)	1.38 (35.0)	0.87 (22.0)	0.80 (20.2)	0.83 (21.0)	0.69 (17.5)	0.14 (3.5)	C20820706

C246C

Swivel Tee Adaptor

(Female)




ØD	T	D	L	H	A	B	Hex	
5/32	NPT 1/8	0.41 (10.5)	0.89 (22.5)	1.46 (37)	0.35 (9.0)	0.64 (16.2)	0.55 (14)	C246C0218
3/16	NPT 1/8	0.45	0.89 (22.5)	1.50	0.35 (9.0)	0.66	0.55 (14)	C246C0318
	NPT 1/4	(11.5)	0.89 (22.5)	(38.2)	0.35 (9.0)	(16.8)	0.69 (17.46)	C246C0328
1/4	NPT 1/8	0.51	0.98 (25.0)	1.61	0.35 (9.0)	0.68	0.55 (14)	C246C0418
	UNF 1/4	(13.0)	1.06 (27.0)	(40.8)	0.43 (11.0)	(17.3)	0.69 (17.46)	C246C0428
5/16	NPT 1/8	0.57	1.02 (26.0)	1.72	0.35 (9.0)	0.72	0.55 (14)	C246C0518
	NPT 1/4	(14.5)	1.10 (28.0)	(43.7)	0.43 (11.0)	(18.2)	0.69 (17.46)	C246C0528
	NPT 3/8		1.14 (29.0)		0.47 (12.0)		0.87 (22)	C246C0538
3/8	NPT 1/4	0.69	1.12 (28.5)	1.88	0.43 (11.0)	0.78	0.69 (17.46)	C246C0628
	NPT 3/8	(17.5)	1.16 (29.5)	(47.7)	0.47 (12.0)	(19.9)	0.87 (22)	C246C0638
1/2	NPT 3/8	0.83	1.30 (33.0)	2.22	0.47 (12.0)	0.91	0.87 (22)	C246C0738
	NPT 1/2	(21.0)	1.44 (36.5)	(56.5)	0.57 (14.5)	(23.0)	0.96 (24.5)	C246C0748



Pneufit C & Pneufit M composite fittings Inch

C2488


Swivel Y adaptor



ØD	T	D	L	H	A	B	Hex
5/32	UNF 10/32	0.41	1.50 (38.1)	0.83	0.14 (3.6)	0.64	3/8 C24880210
	NPT 1/8	(10.5)	1.64 (41.7)		0.33 (8.5)		7/16 C24880218
	NPT 1/4		1.76 (44.7)		0.41 (10.5)		9/16 C24880228
3/16	UNF 10/32	0.45	1.65 (41.8)	0.91	0.14 (3.6)	0.66	7/16 C24880310
	NPT 1/8	(11.5)	1.79 (45.4)		0.33 (8.5)		7/16 C24880318
	NPT 1/4		1.91 (48.4)		0.41 (10.5)		9/16 C24880328
1/4	NPT 3/8		1.94 (49.4)	1.02	0.45 (11.5)	0.68	11/16 C24880338
	UNF 10/32	0.51	1.80 (45.8)		0.14 (3.6)		1/2 C24880410
	NPT 1/8	(13.0)	1.88 (47.7)		0.33 (8.5)		1/2 C24880418
5/16	NPT 1/4		1.98 (50.4)	1.14	0.41 (10.5)	0.72	9/16 C24880428
	NPT 3/8		2.02 (51.4)		0.45 (11.5)		11/16 C24880438
	NPT 1/8		1.85 (47.0)		0.33 (8.5)		9/16 C24880518
3/8	NPT 1/4	0.57	1.93 (49.0)	1.38	0.41 (10.5)	0.78	9/16 C24880528
	NPT 3/8	(14.5)	1.97 (50.0)		0.45 (11.5)		11/16 C24880538
	NPT 1/2		2.09 (53.0)		0.57 (14.5)		7/8 C24880548
1/2	NPT 1/8		2.07 (52.7)	1.65	0.33 (8.5)	0.91	11/16 C24880618
	NPT 1/4	0.69	2.15 (54.7)		0.41 (10.5)		11/16 C24880628
	NPT 3/8	(17.5)	2.19 (55.7)		0.45 (11.5)		11/16 C24880638
3/8	NPT 1/2		2.31 (58.7)	1.65	0.57 (14.5)	0.91	7/8 C24880648
	NPT 1/4	0.83	2.54 (64.6)		0.41 (10.5)		3/4 C24880728
	NPT 3/8	(21.0)	2.58 (65.6)		0.45 (11.5)		3/4 C24880738
1/2	NPT 1/2		2.70 (68.6)		0.57 (14.5)		7/8 C24880748

C20D3

Manifold Union




ØA	ØB	C	H	L	B1	B2	
3/16	5/32	0.18 (4.5)	1.04 (26.3)	2.38 (60.5)	0.67 (16.9)	0.64 (16.3)	C20D30302
1/4	5/32	0.18 (4.5)	1.05 (26.6)	2.43 (61.6)	0.69 (17.4)	0.64 (16.3)	C20D30402
5/16	5/32	0.17 (4.3)	1.11 (28.2)	2.58 (65.6)	0.74 (18.7)	0.64 (16.3)	C20D30502
5/16	3/16	0.18 (4.5)	1.14 (28.9)	2.70 (68.7)	0.74 (18.7)	0.67 (16.9)	C20D30503
5/16	1/4	0.18 (4.5)	1.18 (30.0)	2.83 (71.9)	0.74 (18.7)	0.69 (17.4)	C20D30504
3/8	1/4	0.18 (4.5)	1.27 (32.2)	2.92 (74.2)	0.80 (20.2)	0.69 (17.4)	C20D30604
3/8	5/16	0.17 (4.3)	1.36 (34.5)	3.29 (83.6)	0.80 (20.2)	0.74 (18.7)	C20D30605

C2084

Stem Y


(equal and unequal)



ØA	ØD	A	L	H	B	
5/32	5/32	0.94 (24.0)	2.13 (54.2)	0.83 (21.0)	0.64 (16.3)	C20840202
3/16	3/16	0.94 (24.0)	2.28 (57.9)	0.91 (23.0)	0.66 (16.8)	C20840300
1/4	5/32	0.98 (25.0)	2.17 (55.2)	0.83 (21.0)	0.64 (16.3)	C20840402
1/4	1/4	0.98 (25.0)	2.40 (60.9)	1.14 (29.0)	0.69 (17.4)	C20840404
5/16	1/4	1.02 (26.0)	2.44 (61.9)	1.14 (29.0)	0.69 (17.4)	C20840504
5/16	5/16	1.02 (26.0)	2.38 (60.5)	1.14 (29.0)	0.74 (18.7)	C20840505
3/8	1/4	1.10 (28.0)	2.53 (64.2)	1.38 (35.0)	0.69 (17.4)	C20840604
3/8	5/16	1.10 (28.0)	2.47 (62.8)	1.38 (35.0)	0.74 (18.7)	C20840605
3/8	3/8	1.10 (28.0)	2.70 (68.5)	1.38 (35.0)	0.80 (20.2)	C20840600
1/2	1/2	1.18 (30.0)	3.17 (80.6)	1.61 (41.0)	0.87 (22.0)	C20840700

C24D3


Male Manifold



ØA	ØB	C	H	L	B1	B2	A	T	Hex
1/4	5/32	0.13 (3.3)	1.05 (26.6)	2.80 (71.1)	0.69 (17.4)	0.64 (16.3)	0.33 (8.5)	NPT 1/8	1/2 C24D30218
5/16	5/32	0.17 (4.3)	1.11 (28.2)	3.06 (77.7)	0.74 (18.7)	0.64 (16.3)	0.41 (10.5)	NPT 1/4	9/16 C24D30228
5/16	3/16	0.17 (4.3)	1.14 (29.0)	3.19 (80.9)	0.74 (18.7)	0.67 (16.9)	0.41 (10.5)	NPT 1/4	9/16 C24D30328
5/16	1/4	0.17 (4.3)	1.18 (30.0)	3.31 (84.0)	0.74 (18.7)	0.69 (17.4)	0.41 (10.5)	NPT 1/4	9/16 C24D30428
3/8	1/4	0.17 (4.3)	1.27 (32.2)	3.42 (86.9)	0.80 (20.2)	0.69 (17.4)	0.45 (11.5)	NPT 3/8	11/16 C24D30438

C2090


Union Cross



ØD	C	H	L	B	
5/32	0.13 (3.3)	1.44 (36.6)	1.49 (37.9)	0.64 (16.3)	C20900200
3/16	0.13 (3.3)	1.54 (39.2)	1.54 (39.2)	0.66 (16.8)	C20900300
1/4	0.13 (3.3)	1.68 (42.6)	1.68 (42.6)	0.69 (17.4)	C20900400
5/16	0.17 (4.3)	1.77 (44.9)	1.84 (46.8)	0.74 (18.7)	C20900500
3/8	0.17 (4.3)	1.90 (48.2)	1.99 (50.5)	0.79 (20.0)	C20900600
1/2	0.17 (4.3)	2.38 (60.5)	2.38 (60.5)	0.87 (22.0)	C20900700

C20J3

Stem Manifold




ØA	ØB	C	H	L	B1	B2	J	ØJ
3/16	5/32	0.18 (4.5)	1.02 (25.8)	3.24 (82.4)	0.67 (16.9)	0.64 (16.3)	0.94 (24.0)	3/16 C20J30302
1/4	5/32	0.18 (4.5)	1.05 (26.6)	3.32 (84.3)	0.69 (17.4)	0.64 (16.3)	0.98 (25.0)	1/4 C20J30402
5/16	5/32	0.17 (4.3)	1.12 (28.5)	3.52 (89.5)	0.74 (18.7)	0.64 (16.3)	1.02 (26.0)	5/16 C20J30502
5/16	3/16	0.18 (4.5)	1.14 (29.0)	3.62 (91.9)	0.74 (18.7)	0.67 (16.9)	1.02 (26.0)	5/16 C20J30503
5/16	1/4	0.18 (4.5)	1.18 (30.0)	3.58 (91.0)	0.74 (18.7)	0.69 (17.4)	1.02 (26.0)	5/16 C20J30504
3/8	1/4	0.18 (4.5)	1.27 (32.2)	3.93 (99.7)	0.80 (20.2)	0.69 (17.4)	1.10 (28.0)	3/8 C20J30604
3/8	5/16	0.17 (4.3)	1.36 (34.5)	4.32 (109.7)	0.80 (20.2)	0.74 (18.7)	1.10 (28.0)	3/8 C20J30605

Pneufit C & Pneufit M composite fittings Inch



C20GF


Hand Valve Tube to Tube



ØD	ØK	OC	F	E	L	M1	M2	
1/4	0.50 (12.6)	0.65 (16.5)	0.70 (17.7)	0.49 (12.5)	1.04 (26.5)	0.72 (18.3)	0.75 (19.0)	C20GF0400
5/16	0.58 (14.8)	0.65 (16.5)	0.75 (19.1)	0.55 (13.9)	1.10 (27.9)	0.72 (18.3)	0.75 (19.0)	C20GF0500
3/8	0.69 (17.5)	0.76 (19.3)	0.78 (19.7)	0.57 (14.4)	1.22 (30.9)	0.85 (21.5)	0.94 (24.0)	C20GF0600
1/2	0.83 (21.0)	0.76 (19.3)	0.91 (23.2)	0.70 (17.8)	1.35 (34.3)	0.85 (21.5)	0.94 (24.0)	C20GF0700

C24GG


Hand Valve Thread to Thread



ØR	ØH	OC	A	E	L1	L2	M1	M2	
N1/8	9/16	0.65 (16.5)	0.33 (8.5)	0.91 (23.1)	1.46 (37.1)	1.46 (37.1)	0.72 (18.3)	0.75 (19.0)	C24GG1818
N1/4	9/16	0.65 (16.5)	0.41 (10.5)	0.97 (24.6)	1.54 (39.1)	1.54 (39.1)	0.72 (18.3)	0.75 (19.0)	C24GG2828
N3/8	11/16	0.76 (19.3)	0.45 (11.5)	0.96 (24.5)	1.61 (41.0)	1.57 (40.0)	0.85 (21.5)	0.94 (24.0)	C24GG3838
N1/2	7/8	0.76 (19.3)	0.57 (14.5)	1.15 (29.1)	1.80 (45.6)	1.80 (45.6)	0.85 (21.5)	0.94 (24.0)	C24GG4848

C24GH


Hand Valve Tube to Thread



ØD	R	ØK	H	OC	A	F	E1	E2	L1	L2	M1	M2	
1/4	N1/8	0.50 (12.6)	9/16	0.65 (16.5)	0.33 (8.5)	0.70 (17.7)	0.49 (12.5)	0.91 (23.1)	1.04 (26.5)	1.46 (37.1)	0.72 (18.3)	0.75 (19.0)	C24GH0418
1/4	N1/4	0.50 (12.6)	9/16	0.65 (16.5)	0.41 (10.5)	0.70 (17.7)	0.49 (12.5)	0.99 (25.1)	1.04 (26.5)	1.54 (39.1)	0.72 (18.3)	0.75 (19.0)	C24GH0428
1/4	N3/8	0.50 (12.6)	11/16	0.65 (16.5)	0.45 (11.5)	0.70 (17.7)	0.49 (12.5)	1.03 (26.1)	1.04 (26.5)	1.58 (40.1)	0.72 (18.3)	0.75 (19.0)	C24GH0438
5/16	N1/8	0.58 (14.8)	9/16	0.65 (16.5)	0.33 (8.5)	0.75 (19.1)	0.55 (13.9)	0.91 (23.1)	1.10 (27.9)	1.46 (37.1)	0.72 (18.3)	0.75 (19.0)	C24GH0518
5/16	N1/4	0.58 (14.8)	9/16	0.65 (16.5)	0.41 (10.5)	0.75 (19.1)	0.55 (13.9)	0.99 (25.1)	1.10 (27.9)	1.54 (39.1)	0.72 (18.3)	0.75 (19.0)	C24GH0528
5/16	N3/8	0.58 (14.8)	11/16	0.65 (16.5)	0.45 (11.5)	0.75 (19.1)	0.55 (13.9)	1.03 (26.1)	1.10 (27.9)	1.58 (40.1)	0.72 (18.3)	0.75 (19.0)	C24GH0538
3/8	N1/4	0.69 (17.5)	11/16	0.76 (19.3)	0.41 (10.5)	0.78 (19.7)	0.57 (14.4)	0.93 (23.5)	1.22 (30.9)	1.57 (40.0)	0.85 (21.5)	0.94 (24.0)	C24GH0628
3/8	N3/8	0.69 (17.5)	11/16	0.76 (19.3)	0.45 (11.5)	0.78 (19.7)	0.57 (14.4)	0.96 (24.5)	1.22 (30.9)	1.61 (41.0)	0.85 (21.5)	0.94 (24.0)	C24GH0638
3/8	N1/2	0.69 (17.5)	7/8	0.76 (19.3)	0.57 (14.5)	0.78 (19.7)	0.57 (14.4)	1.08 (27.5)	1.22 (30.9)	1.73 (44.0)	0.85 (21.5)	0.94 (24.0)	C24GH0648
1/2	N3/8	0.83 (21.0)	3/4	0.76 (19.3)	0.45 (11.5)	0.91 (23.2)	0.70 (17.8)	1.03 (26.1)	1.35 (34.3)	1.68 (42.6)	0.85 (21.5)	0.94 (24.0)	C24GH0738
1/2	N1/2	0.83 (21.0)	7/8	0.76 (19.3)	0.57 (14.5)	0.91 (23.2)	0.70 (17.8)	1.15 (29.1)	1.35 (34.3)	1.80 (45.6)	0.85 (21.5)	0.94 (24.0)	C24GH0748

C24GJ

Hand Valve Thread to Tube




ØD	R	ØK	H	OC	A	F	E1	E2	L1	L2	M1	M2	
1/4	N1/8	0.50 (12.6)	9/16	0.65 (16.5)	0.33 (8.5)	0.70 (17.7)	0.91 (23.1)	0.49 (12.5)	1.46 (37.1)	1.04 (26.5)	0.72 (18.3)	0.75 (19.0)	C24GJ0418
1/4	N1/4	0.50 (12.6)	9/16	0.65 (16.5)	0.41 (10.5)	0.70 (17.7)	0.99 (25.1)	0.49 (12.5)	1.54 (39.1)	1.04 (26.5)	0.72 (18.3)	0.75 (19.0)	C24GJ0428
1/4	N3/8	0.50 (12.6)	11/16	0.65 (16.5)	0.45 (11.5)	0.70 (17.7)	1.03 (26.1)	0.49 (12.5)	1.58 (40.1)	1.04 (26.5)	0.72 (18.3)	0.75 (19.0)	C24GJ0438
5/16	N1/8	0.58 (14.8)	9/16	0.65 (16.5)	0.33 (8.5)	0.75 (19.1)	0.91 (23.1)	0.55 (13.9)	1.46 (37.1)	1.10 (27.9)	0.72 (18.3)	0.75 (19.0)	C24GJ0518
5/16	N1/4	0.58 (14.8)	9/16	0.65 (16.5)	0.41 (10.5)	0.75 (19.1)	0.99 (25.1)	0.55 (13.9)	1.54 (39.1)	1.10 (27.9)	0.72 (18.3)	0.75 (19.0)	C24GJ0528
5/16	N3/8	0.58 (14.8)	11/16	0.65 (16.5)	0.45 (11.5)	0.75 (19.1)	1.03 (26.1)	0.55 (13.9)	1.58 (40.1)	1.10 (27.9)	0.72 (18.3)	0.75 (19.0)	C24GJ0538
3/8	N1/4	0.69 (17.5)	11/16	0.76 (19.3)	0.41 (10.5)	0.78 (19.7)	0.93 (23.5)	0.57 (14.4)	1.57 (40.0)	1.22 (30.9)	0.85 (21.5)	0.94 (24.0)	C24GJ0628
3/8	N3/8	0.69 (17.5)	11/16	0.76 (19.3)	0.45 (11.5)	0.78 (19.7)	0.96 (24.5)	0.57 (14.4)	1.61 (41.0)	1.22 (30.9)	0.85 (21.5)	0.94 (24.0)	C24GJ0638
3/8	N1/2	0.69 (17.5)	7/8	0.76 (19.3)	0.57 (14.5)	0.78 (19.7)	1.08 (27.5)	0.57 (14.4)	1.73 (44.0)	1.22 (30.9)	0.85 (21.5)	0.94 (24.0)	C24GJ0648
1/2	N3/8	0.83 (21.0)	3/4	0.76 (19.3)	0.45 (11.5)	0.86 (21.9)	1.03 (26.1)	0.70 (17.8)	1.68 (42.6)	1.35 (34.3)	0.85 (21.5)	0.94 (24.0)	C24GJ0738
1/2	N1/2	0.83 (21.0)	7/8	0.76 (19.3)	0.57 (14.5)	0.86 (21.9)	1.15 (29.1)	0.70 (17.8)	1.80 (45.6)	1.35 (34.3)	0.85 (21.5)	0.94 (24.0)	C24GJ0748



Pneufit C & Pneufit M composite fittings Inch

M2020

Straight Union




ØD	D	B	H	
1/8	0.30 (7.6)	0.44 (11.1)	0.91 (23.2)	M20200100
5/32	0.33 (8.5)	0.46 (11.6)	0.96 (24.5)	M20200200
1/4	0.44 (11.2)	0.53 (13.5)	1.13 (28.6)	M20200400

M2020

Straight Union

(Unequal)




ØA	ØB	ØF	ØE	B2	B1	H	
5/32	1/8	0.30 (7.6)	0.33 (8.5)	0.44 (11.1)	0.46 (11.6)	0.94 (23.8)	M20200201
1/4	1/8	0.30 (7.6)	0.44 (11.2)	0.44 (11.1)	0.53 (13.5)	1.04 (26.5)	M20200401
1/4	5/32	0.35 (8.8)	0.44 (11.2)	0.46 (11.8)	0.53 (13.5)	1.11 (28.1)	M20200402

M2425

Straight Adaptor

(external + internal hex)




ØD	T	A	L	B	Hex	
1/8	M3xp=0.5	0.16 (4.0)	0.67 (17.1)	0.44 (11.1)	0.28 (7)	M22250103
1/8	M5xp=0.8	0.18 (4.6)	0.70 (17.7)	0.44 (11.1)	0.31 (8)	M22250105
1/8	M6xp=1.0	0.20 (5.1)	0.72 (18.2)	0.44 (11.1)	0.31 (8)	M22250106
5/32	M3xp=0.5	0.16 (4.0)	0.70 (17.7)	0.46 (11.6)	0.31 (8)	M02250403
5/32	M5xp=0.8	0.18 (4.6)	0.72 (18.2)	0.46 (11.6)	0.31 (8)	M02250405
5/32	M6xp=1.0	0.20 (5.1)	0.74 (18.8)	0.46 (11.6)	0.31 (8)	M02250406
1/4	M5xp=0.8	0.16 (4.0)	0.78 (19.7)	0.53 (13.4)	0.43 (11)	M22250405
1/4	M6xp=1.0	0.16 (4.0)	0.78 (19.7)	0.53 (13.4)	0.43 (11)	M22250406
1/8	UNF 10/32	0.18 (4.6)	0.70 (17.7)	0.44 (11.1)	0.31 (8)	M24250110
1/8	NPT 1/16	0.31 (8.0)	0.65 (16.5)	0.44 (11.1)	0.31 (8)	M24250116
1/8	NPT 1/8	0.33 (8.5)	0.69 (17.5)	0.44 (11.1)	0.44 (11.1)	M24250118
5/32	UNF 10/32	0.18 (4.6)	0.72 (18.2)	0.46 (11.6)	0.31 (8)	M24250210
5/32	NPT 1/16	0.31 (8.0)	0.71 (18.0)	0.46 (11.6)	0.31 (8)	M24250216
5/32	NPT 1/8	0.33 (8.5)	0.73 (18.5)	0.46 (11.6)	0.44 (11.1)	M24250218
1/4	UNF 10/32	0.16 (4.0)	0.76 (19.3)	0.51 (13.0)	0.44 (11.1)	M24250410
1/4	NPT 1/16	0.31 (8.0)	0.87 (22.0)	0.51 (13.0)	0.44 (11.1)	M24250416
1/4	NPT 1/8	0.33 (8.5)	0.77 (19.5)	0.51 (13.0)	0.44 (11.1)	M24250418

M2426

Straight Adaptor

(Female)




ØD	T	A	L	B	D	Hex	
1/8	M3xp=0.5	0.16 (4.0)	0.68 (17.3)	0.44 (11.1)	0.30 (7.5)	0.31 (8.0)	M22260103
1/8	M5xp=0.8	0.24 (6.0)	0.74 (18.8)	0.44 (11.1)	0.30 (7.5)	0.31 (8.0)	M22260105
5/32	M3xp=0.5	0.16 (4.0)	0.72 (18.2)	0.46 (11.6)	0.31 (8.0)	0.31 (8.0)	M02260403
5/32	M5xp=0.8	0.24 (6.0)	0.78 (19.7)	0.46 (11.6)	0.31 (8.0)	0.31 (8.0)	M02260405
1/8	UNF 10/32	0.24 (6.0)	0.74 (18.8)	0.44 (11.1)	0.30 (7.5)	0.31 (8.0)	M24260110
1/8	NPT 1/16	0.31 (8.0)	0.81 (20.5)	0.44 (11.1)	0.30 (7.5)	0.41 (10.3)	M24260116
1/8	NPT 1/8	0.33 (8.5)	0.89 (22.5)	0.44 (11.3)	0.30 (7.5)	0.43 (11.0)	M24260118
1/8	NPT 1/4	0.41 (10.5)	1.00 (25.3)	0.44 (11.3)	0.30 (7.5)	0.67 (17.0)	M24260128
5/32	UNF 10/32	0.24 (6.0)	0.78 (19.7)	0.46 (11.6)	0.31 (8.0)	0.31 (8.0)	M24260210
5/32	NPT 1/16	0.31 (8.0)	0.85 (21.7)	0.46 (11.6)	0.33 (8.5)	0.41 (10.3)	M24260216
1/4	UNF 10/32	0.24 (6.0)	0.81 (20.5)	0.51 (13.0)	0.41 (10.5)	0.43 (11.0)	M24260410
1/4	NPT 1/16	0.31 (8.0)	0.89 (22.5)	0.51 (13.0)	0.41 (10.5)	0.43 (11.0)	M04260416

M242A


Straight Adaptor

(Internal hex only)



ØD	T	A	L	B	H	Hex	
1/8	M3xp=0.5	0.16 (4.0)	0.67 (17.1)	0.44 (11.1)	0.28 (7)	0.06 (1.5)	M222A0103
1/8	M5xp=0.8	0.18 (4.6)	0.70 (17.7)	0.44 (11.1)	0.28 (7)	0.08 (2.0)	M222A0105
1/8	M6xp=1.0	0.20 (5.1)	0.72 (18.2)	0.44 (11.1)	0.31 (8)	0.08 (2.0)	M222A0106
5/32	M3xp=0.5	0.16 (4.0)	0.70 (17.7)	0.46 (11.6)	0.31 (8)	0.06 (1.5)	M022A0403
5/32	M5xp=0.8	0.18 (4.6)	0.72 (18.2)	0.46 (11.6)	0.31 (8)	0.10 (2.5)	M022A0405
5/32	M6xp=1.0	0.20 (5.1)	0.74 (18.8)	0.46 (11.6)	0.31 (8)	0.12 (3.0)	M022A0406
1/4	M5xp=0.8	0.16 (4.0)	0.78 (19.7)	0.53 (13.4)	0.41 (10.5)	0.10 (2.5)	M222A0405
1/4	M6xp=1.0	0.16 (4.0)	0.78 (19.7)	0.53 (13.4)	0.41 (10.5)	0.10 (2.5)	M222A0406
1/8	UNF 10/32	0.18 (4.6)	0.70 (17.7)	0.44 (11.1)	0.28 (7.0)	0.08 (2.0)	M242A0110
1/8	NPT 1/16	0.31 (8.0)	0.71 (18.0)	0.44 (11.1)	0.31 (7.9)	0.09 (2.38)	M242A0116
1/8	NPT 1/8	0.33 (8.5)	0.44 (11.1)	0.44 (11.1)	0.43 (11)	0.09 (2.38)	M242A0118
5/32	NPT 10/32	0.18 (4.6)	0.72 (18.2)	0.46 (11.6)	0.31 (8)	0.10 (2.5)	M242A0210
5/32	NPT 1/16	0.31 (8.0)	0.75 (19.0)	0.46 (11.6)	0.31 (7.9)	0.09 (2.38)	M242A0216
5/32	NPT 1/8	0.33 (8.5)	0.64 (16.3)	0.46 (11.6)	0.43 (11)	0.09 (2.38)	M242A0218
1/4	UNF 10/32	0.16 (4.0)	0.76 (19.3)	0.51 (13.0)	0.41 (10.5)	0.09 (2.38)	M242A0410
1/4	NPT 1/16	0.31 (8.0)	0.87 (22.0)	0.51 (13.0)	0.41 (10.5)	0.16 (4.0)	M242A0416
1/4	NPT 1/8	0.33 (8.5)	0.77 (19.5)	0.51 (13.0)	0.41 (10.5)	0.16 (4.0)	M242A0418

Pneufit C & Pneufit M composite fittings Inch




M2447

90° Swivel Elbow Adapter

ØD	T	A	L1	L	H	B	Hex	
1/8	M3xp=0.5	0.12 (3.0)	0.51 (13.0)	0.78 (19.8)	0.68 (17.2)	0.44 (11.1)	0.31 (8)	M22470103
1/8	M5xp=0.8	0.14 (3.6)	0.51 (13.0)	0.80 (20.4)	0.68 (17.2)	0.44 (11.1)	0.31 (8)	M22470105
1/8	M6xp=1.0	0.16 (4.1)	0.51 (13.0)	0.82 (20.9)	0.68 (17.2)	0.44 (11.1)	0.31 (8)	M22470106
5/32	M3xp=0.5	0.12 (3.0)	0.51 (13.0)	0.80 (20.3)	0.72 (18.2)	0.46 (11.6)	0.31 (8)	M02470403
5/32	M5xp=0.8	0.14 (3.6)	0.51 (13.0)	0.82 (20.9)	0.72 (18.2)	0.46 (11.6)	0.31 (8)	M02470405
5/32	M6xp=1.0	0.16 (4.1)	0.51 (13.0)	0.84 (21.4)	0.72 (18.2)	0.46 (11.6)	0.31 (8)	M02470406
1/4	M6xp=1.0	0.16 (4.1)	0.57 (14.5)	0.95 (24.2)	0.79 (20.1)	0.53 (13.5)	0.31 (8)	M22470406
1/8	UNF 10/32	0.14 (3.6)	0.51 (13.0)	0.80 (20.4)	0.68 (17.2)	0.44 (11.1)	0.31 (8)	M24470110
1/8	NPT 1/16	0.31 (8.0)	0.48 (12.2)	0.86 (21.9)	0.68 (17.2)	0.44 (11.1)	0.31 (8)	M24470116
1/8	NPT 1/8	0.33 (8.5)	0.48 (12.2)	0.91 (23.2)	0.68 (17.2)	0.44 (11.1)	0.43 (11)	M24470118
1/8	NPT 1/4	0.41 (10.5)	0.43 (10.8)	0.99 (25.1)	0.68 (17.2)	0.44 (11.1)	0.55 (14)	M24470128
5/32	UNF 10/32	0.14 (3.6)	0.51 (13.0)	0.82 (20.9)	0.72 (18.2)	0.46 (11.6)	0.31 (8)	M24470210
5/32	NPT 1/6	0.31 (8.0)	0.48 (12.2)	0.88 (22.4)	0.72 (18.2)	0.46 (11.6)	0.31 (8)	M24470216
5/32	NPT 1/8	0.33 (8.5)	0.48 (12.2)	0.93 (23.7)	0.72 (18.2)	0.46 (11.6)	0.43 (11)	M24470218
1/4	UNF 10/32	0.14 (3.6)	0.57 (14.5)	0.93 (23.7)	0.79 (20.1)	0.53 (13.5)	0.31 (8)	M24470410
1/4	NPT 1/6	0.31 (8.0)	0.46 (11.6)	0.99 (25.2)	0.79 (20.1)	0.53 (13.5)	0.31 (8)	M24470416
1/4	NPT 1/8	0.33 (8.5)	0.49 (12.4)	1.04 (26.5)	0.79 (20.1)	0.53 (13.5)	0.43 (11)	M24470418

M2040


Union Elbow



ØD	C	B	H	
1/8	0.13 (3.2)	0.44 (11.1)	0.67 (17.1)	M20400100
5/32	0.13 (3.2)	0.46 (11.6)	0.73 (18.5)	M20400200
1/4	0.13 (3.3)	0.53 (13.5)	0.91 (23.2)	M20400400

M2468


Swivel Side Tee Adapter



ØD	T	A	L1	H	L	B	Hex	
1/8	M3xp=0.5	0.12 (3.0)	0.51 (13.0)	1.16 (29.4)	0.52 (13.3)	0.44 (11.1)	0.31 (8)	M22680103
1/8	M5xp=0.8	0.14 (3.6)	0.51 (13.0)	1.18 (30.0)	0.52 (13.3)	0.44 (11.1)	0.31 (8)	M22680105
1/8	M6xp=1.0	0.16 (4.1)	0.51 (13.0)	1.20 (30.5)	0.52 (13.3)	0.44 (11.1)	0.31 (8)	M22680106
5/32	M3xp=0.5	0.12 (3.0)	0.51 (13.0)	1.20 (30.4)	0.56 (14.2)	0.46 (11.6)	0.31 (8)	M02680403
5/32	M5xp=0.8	0.14 (3.6)	0.51 (13.0)	1.22 (31.0)	0.56 (14.2)	0.46 (11.6)	0.31 (8)	M02680405
5/32	M6xp=1.0	0.16 (4.1)	0.51 (13.0)	1.24 (31.5)	0.56 (14.2)	0.46 (11.6)	0.31 (8)	M02680406
1/4	M5xp=0.8	0.14 (3.6)	0.57 (14.5)	1.41 (35.7)	0.69 (17.6)	0.53 (13.5)	0.31 (8)	M22680405
1/4	M6xp=1.0	0.16 (4.1)	0.57 (14.5)	1.43 (36.2)	0.69 (17.6)	0.53 (13.5)	0.31 (8)	M22680406
1/8	UNF 10/32	0.14 (3.6)	0.51 (13.0)	0.52 (13.3)	1.18 (30.0)	0.44 (11.1)	0.31 (8)	M24680110
1/8	NPT 1/16	0.31 (8.0)	0.48 (12.2)	0.52 (13.3)	1.24 (31.5)	0.44 (11.1)	0.31 (8)	M24680116
1/8	NPT 1/8	0.33 (8.5)	0.48 (12.2)	0.52 (13.3)	1.29 (32.8)	0.44 (11.1)	0.43 (11)	M24680118
5/32	UNF 10/32	0.12 (3.0)	0.51 (13.0)	0.56 (14.2)	1.20 (30.4)	0.46 (11.6)	0.31 (8)	M24680210
5/32	NPT 1/16	0.31 (8.0)	0.48 (12.2)	0.56 (14.2)	1.26 (31.9)	0.46 (11.6)	0.31 (8)	M24680216
5/32	NPT 1/8	0.33 (8.5)	0.48 (12.2)	0.56 (14.2)	1.31 (33.2)	0.46 (11.6)	0.43 (11)	M24680218
1/4	UNF 10/32	0.14 (3.6)	0.57 (14.5)	0.69 (17.6)	1.41 (35.7)	0.53 (13.5)	0.31 (8)	M24680410
1/4	NPT 1/16	0.31 (8.0)	0.46 (11.6)	0.69 (17.6)	1.46 (37.2)	0.53 (13.5)	0.31 (8)	M24680416
1/4	NPT 1/8	0.33 (8.5)	0.49 (12.4)	0.69 (17.6)	1.52 (38.5)	0.53 (13.5)	0.43 (11)	M24680418

M2467


Swivel Tee Adapter



ØD	T	A	L1	L	H	B	Hex	
1/8	M3xp=0.5	0.12 (3.0)	0.51 (13.0)	0.78 (19.8)	1.05 (26.6)	0.44 (11.1)	0.31 (8)	M22670103
1/8	M5xp=0.8	0.14 (3.6)	0.51 (13.0)	0.80 (20.4)	1.05 (26.6)	0.44 (11.1)	0.31 (8)	M22670105
1/8	M6xp=1.0	0.16 (4.1)	0.51 (13.0)	0.82 (20.9)	1.05 (26.6)	0.44 (11.1)	0.31 (8)	M22670106
5/32	M3xp=0.5	0.12 (3.0)	0.51 (13.0)	0.80 (20.3)	1.13 (28.6)	0.46 (11.6)	0.31 (8)	M02670403
5/32	M5xp=0.8	0.14 (3.6)	0.51 (13.0)	0.82 (20.9)	1.13 (28.6)	0.46 (11.6)	0.31 (8)	M02670405
5/32	M6xp=1.0	0.16 (4.1)	0.51 (13.0)	0.84 (21.4)	1.13 (28.6)	0.46 (11.6)	0.31 (8)	M02670406
1/4	M5xp=0.8	0.14 (3.6)	0.57 (14.5)	0.93 (23.7)	1.27 (32.3)	0.53 (13.5)	0.31 (8)	M22670405
1/4	M6xp=1.0	0.16 (4.1)	0.57 (14.5)	0.95 (24.2)	1.27 (32.3)	0.53 (13.5)	0.31 (8)	M22670406
1/8	UNF 10/32	0.14 (3.6)	0.51 (13.0)	0.80 (20.4)	1.05 (26.6)	0.44 (11.1)	0.31 (8)	M24670110
1/8	NPT 1/16	0.31 (8.0)	0.48 (12.2)	0.86 (21.9)	1.05 (26.6)	0.44 (11.1)	0.31 (8)	M24670116
1/8	NPT 1/8	0.33 (8.5)	0.48 (12.2)	0.91 (23.2)	1.05 (26.6)	0.44 (11.1)	0.43 (11)	M24670118
5/32	UNF 10/32	0.14 (3.6)	0.51 (13.0)	0.82 (20.9)	1.13 (28.6)	0.46 (11.6)	0.31 (8)	M24670210
5/32	NPT 1/16	0.31 (8.0)	0.48 (12.2)	0.88 (22.4)	1.13 (28.6)	0.46 (11.6)	0.31 (8)	M24670216
5/32	NPT 1/8	0.33 (8.5)	0.48 (12.2)	0.93 (23.7)	1.13 (28.6)	0.46 (11.6)	0.43 (11)	M24670218
1/4	UNF 10/32	0.14 (3.6)	0.57 (14.5)	0.93 (23.7)	1.27 (32.3)	0.46 (11.6)	0.31 (8)	M24670410
1/4	NPT 1/16	0.31 (8.0)	0.46 (11.6)	0.99 (25.2)	1.27 (32.3)	0.46 (11.6)	0.31 (8)	M24670416
1/4	NPT 1/8	0.33 (8.5)	0.49 (12.4)	1.04 (26.5)	1.27 (32.3)	0.46 (11.6)	0.43 (11)	M24670418

M2060

Union Tee





ØD	C	L	B	H	
1/8	0.13 (3.2)	0.67 (17.1)	0.44 (11.1)	1.05 (26.6)	M20600100
5/32	0.13 (3.2)	0.73 (18.5)	0.46 (11.6)	1.13 (28.6)	M20600200
1/4	0.13 (3.3)	0.91 (23.2)	0.53 (13.5)	1.39 (35.3)	M20600400





Pneufit C & Pneufit M composite fittings Inch

Speed Controllers Flowrate for C2VA0 and C2WA0 Banjo Types



1/8, 5/32 and 1/4" to
10/32 UNF





5/32, 1/4, 5/16 to
1/8 NPT





5/32, 1/4, 5/16, 3/8, 1/2
to 1/4 NPT



1/4, 5/16, 3/8, 1/2 to
3/8 NPT




5/16, 3/8, 1/2 to
1/2 NPT






Speed Controllers Flowrate for C24GE Banjo Types


C24GE0200
5/32 NPT




C24GE0400
1/4 NPT



C24GE0500
5/16 NPT



C24GE0600
3/8 NPT



C24GE0700
1/2 NPT

