


EDP NO. 16-06-00**
ENG. NO. SD-R62-*




注記

1. 推奨プリント基板穴径: $\phi 1.65$

単位: MM DIMENSIONS IN METRIC DO NOT SCALE DRAWING

角度	ANGLE	$\pm 3^\circ$								
30 以上	OVER	± 0.3	16-06-0010	R62-5	$\phi 2.55$	3.68	7.1	11.55	錫メッキ(3 μ MIN.)	
10 以上	OVER	± 0.25	↓ -0011	↓ -4	$\phi 2.28$	3.18	10.15	14.1	錫メッキ(3 μ MIN.)	
10 未満	UNDER	± 0.2	16-06-0004	R62-3	$\phi 2.29$	3.18	7.11	11.05	錫メッキ(3 μ MIN.)	
一般公差			EDP NO.	ENG. NO.	A	B	C	D	メッキ仕様	備考
GENERAL TOLERANCES										
			材料 MATERIAL							
			貴銅							
			仕上 FINISH							
			表参照							
			適用電線範囲 WIRE RANGE							
			被覆外径 INS. RANGE							
D	REVISED	ECN No. 2395	MS	4/1/82	DRAWN BY	CHK'D BY	EDP NO.			
C	REDRAWN	ECN No. 789	MS	9/25/78	APPROVED BY	DATE	16-06-00**			
記号	変更内容	DR.	日付	DATE	APP'D BY	尺 度	ENG. NO.			
LTR	REVISION RECORD	CHK.	DATE			SCALE	SD-R62-*			
TITLE 名称:							REV			
BEAD PIN							D			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX(JAPAN) AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
本図面は日本モレックス社の所有する情報を含むもので当社の許可なく複製を禁止する。



NOTES:

1. MATERIAL: CARTRIDGE BRASS, ALLOY #C26000.
2. FINISH: .000200/(0.00508) MIN. ELECTRO TIN PLATE.

NEW SALES DWG.
ECN U2 0738
5-7-92 RW

MFG.	SH.	REV.	LTR.	REVISIONS

DIMENSIONS SHOWN (METRIC) INCH

UNLESS OTHERWISE SPECIFIED
TOLERANCES: ANGULAR $\pm 1/2^\circ$

	INCH	METRIC
3 PLACE	$\pm .010$	---
2 PLACE	$\pm .014$	± 0.25
1 PLACE	---	± 0.36

DRAFT WHERE APPLICABLE MUST
REMAIN WITHIN DIMENSIONS

DRWG. BY	RW	CHK'D. BY	RW
APP'D. BY	RAS	SCALE	10:1

 $\nabla = 0$ $\blacktriangledown = 0$

REVISE ONLY ON CAD SYSTEM

TITLE

$.062/(1.57)$ DIA. PIN FOR
P.C. BOARD MOUNTING



MOLEX INCORPORATED
LISLE, ILL. 60532 U.S.A.

SHEET NO.

DATE

1 OF 1

5 / 7 / 92

PART NO.

DRWG. NO.

16-06-0010

SDSP-599

FILE NAME
S599X1
DGN

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO
MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

DIV.
CP

SIZE
A