




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



Customer drawing

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1			11/05/08	

D-SUB TECHNICAL DATA

SHELL : Steel 2.5um(100u") min tin over 1.25um(50u") min nickel
BODY : Glass filled thermoplastic.
Flame retardant to UL94 V-0 Color Black
CONTACTS : Machined bronze
0.4um(15u") min gold over 1.25um(50u") min nickel
ELECTRICAL : Voltage rating : 300 V RMS at 50 Hz
Current rating : 7.5A
Withstanding Voltage >1000 V RMS at 50 Hz for one minute
Insulation resistance >5000 M Ohms
CLIMATIC : Temperature range -55 °C up to 155°C
Damp heat 56 days(40 °C-95% HR)
MARKING : Amphenol-...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 77TW A 7W2 S


L: RoHS Compliance

77TW: tin plated shell

Shell Size: A

Contact type:
S:Female
P: Male

Configuration: 7W2

UNLESS OTHERWISE SPECIFIED TOLERANCES U.S. METRIC .X +/- 0.50 .XX +/- 0.30 .XXX +/- 0.20 FRACTIONS +/- ANGLES +/- 5° FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES DIMENSIONS U.S. INCHES METRIC MM		APPROVAL		DATE		Amphenol® TITLE Hybrid connector, TW series			
		DRAWN	Christina.cui	10/31/07					
		CHECKED	Lik.wang	10/31/07					
		CHECKED							
DRAWING FILE :		ANGLE OF PROJECTION		SIZE		DRAWING NO.		REV.	
				A4		C L77TWA7W2S		1	
				SCALE		NONE		SHEET 1 OF 1	