







	1	2	3	4	5	6	7																																																																																		
A	NOTES: MATERIAL 1.Insulator Material:Glass-Filled Thermoplastic PBT,UL 94V-0,Black 2.Contact Material : Copper alloy ,Gold flash selective gold 3.Shell :SPCC 4.Clinch Nut : Brass, Nickle Plated 5.Screwlock : Brass, Nickle Plated ELECTRICAL 1.Current Rating : 1 AMP 2.Voltage Rating : 250 V AC/rms 60 Hz 3.Contact Resistance: 20mΩ max at 1 AMP DC 4.Insulation Resistance: 1000MΩ at 500 VDC 5.Withstand Voltage : 1000V AC/rms 60Hz for 1 minute       With Insulator Support <table><tr><th colspan="6">Dimensions</th></tr><tr><th>Positions</th><th>A</th><th>B</th><th>D</th><th>E</th><th>F</th></tr><tr><td>9</td><td>30.81</td><td>24.99</td><td>16.33</td><td>11.08</td><td>10.16</td></tr><tr><td>15</td><td>39.14</td><td>33.32</td><td>24.66</td><td>19.39</td><td>17.78</td></tr><tr><td>25</td><td>53.04</td><td>47.04</td><td>38.38</td><td>33.24</td><td>30.48</td></tr><tr><td>37</td><td>69.32</td><td>63.50</td><td>54.84</td><td>49.86</td><td>45.72</td></tr></table>							Dimensions						Positions	A	B	D	E	F	9	30.81	24.99	16.33	11.08	10.16	15	39.14	33.32	24.66	19.39	17.78	25	53.04	47.04	38.38	33.24	30.48	37	69.32	63.50	54.84	49.86	45.72	A																																													
Dimensions																																																																																									
Positions								A	B	D	E	F																																																																													
9								30.81	24.99	16.33	11.08	10.16																																																																													
15								39.14	33.32	24.66	19.39	17.78																																																																													
25								53.04	47.04	38.38	33.24	30.48																																																																													
37	69.32	63.50	54.84	49.86	45.72																																																																																				
B								B																																																																																	
C								C																																																																																	
D								D																																																																																	
E								E																																																																																	
F								F																																																																																	
G	RoHS compliant Unit: mm  File No.: E198287 <table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>07.16.2003</td><td>Hellwig</td></tr><tr><td>X.</td><td>±0.38</td><td></td><td></td><td></td><td></td><td>Approved</td><td>23.12.2008</td><td>Hellwig</td></tr><tr><td>X.X</td><td>±0.25</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.13</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.°</td><td>±3°</td><td></td><td></td><td></td><td>23.12.2008</td><td>Dean</td><td></td><td></td></tr><tr><td>X.X°</td><td>±1.0°</td><td>①</td><td>Drawn</td><td></td><td>16.07.2003</td><td>Hellwig</td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td></td><td>Date</td><td>Name</td><td></td><td></td></tr></table> 							Scale	1:1					Date	Name	Customer-No.	TOLERANCE						Drawn	07.16.2003	Hellwig	X.	±0.38					Approved	23.12.2008	Hellwig	X.X	±0.25								X.XX	±0.13								DIM	TOL								X.°	±3°				23.12.2008	Dean			X.X°	±1.0°	①	Drawn		16.07.2003	Hellwig			Angle	TOL	Id.	Modification		Date	Name			G
Scale	1:1					Date	Name	Customer-No.																																																																																	
TOLERANCE						Drawn	07.16.2003	Hellwig																																																																																	
X.	±0.38					Approved	23.12.2008	Hellwig																																																																																	
X.X	±0.25																																																																																								
X.XX	±0.13																																																																																								
DIM	TOL																																																																																								
X.°	±3°				23.12.2008	Dean																																																																																			
X.X°	±1.0°	①	Drawn		16.07.2003	Hellwig																																																																																			
Angle	TOL	Id.	Modification		Date	Name																																																																																			
H	<table><tr><td colspan="2">Drawing-No.</td><td></td></tr><tr><td colspan="2">ASS 0128A CO</td><td>rev02</td></tr><tr><td colspan="2">Replace</td><td>Sheet</td></tr></table>							Drawing-No.			ASS 0128A CO		rev02	Replace		Sheet	H																																																																								
Drawing-No.																																																																																									
ASS 0128A CO		rev02																																																																																							
Replace		Sheet																																																																																							
	1	2	3	4	5	6	7																																																																																		