

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION


© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

, 19

LOC	DIST	P	F	LTR	DESCRIPTION	DATE	APPROVED
G	36			E	REV PER 0G3A-0637-01	030CT02	JR/MS

- 1 CLEANED, UNPLATED
2 PREPRODUCTION - FASR REQ.



325-375 MCM	1 TIN PL PER ASTM B 545 .000150 MIN THK	2 1-324449-0 324449
RANGE	FINISH	PART NO

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN INCHES
TOLERANCES ON:
2 PLC DEC ± -
3 PLC DEC ± -
ANGLES ± -

MATERIAL
COPPER
ASTM-B-75
ANNEALED

FINISH
SEE TABLE

DR 1/16/89
P FORTNEY

CHK 6/20/89
MS FEHER

APPD 6/20/89
WJ VOCKROTH

APPD 6/20/89
R ADAMS

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT .068 LB.

AMP

AMP INCORPORATED
Harrisburg, Pa. 17105

NAME

WIRE SPLICE, PARALLEL,
AMPOWER, WIRE SIZE: 350 MCM

SIZE

A

FSCM NO

00779

DRAWING NO

324449

SCALE

2:1

SHEET

1 OF 1