HM6116LP-2, HM6116LP-3, HM6116LP-4

2048-word×8-bit High Speed Static CMOS RAM

■FEATURES

- Single 5V Supply and High Density 24 Pin Package
- High Speed: Fast Access Time 120ns/150ns/200ns (max.)
- Low Power Standby and Low Power Operation; Standby: 10μW (typ.) Operation: 160mW (typ.)
- Completely Static RAM: No clock nor Timing Strobe Required
- Directly TTL Compatible: All Input and Output
- Pin Out Compatible with Standard 16K EPROM/MASK ROM
- Equal Access and Cycle Time
- Capability of Battery Back up Operation



(DP-24)

■FUNCTIONAL BLOCK DIAGRAM



■PIN ARRANGEMENT



(Top View)

■ABSOLUTE MAXIMUM RATINGS

Item	Symbol	Rating	Unit
Voltage on Any Pin Relative to GND	V_T	−0.5* to +7.0	V
Operating Temperature	T_{opr}	0 to +70	°C
Storage Temperature	T_{stg}	−55 to +125	°C
Temperature Under Bias	T_{bias}	−10 to +85	°C
Power Dissipation	P_T	1.0	W

* Pulse Width 50ns : −3.5V

■TRUTH TABLE

$\overline{CS}$	$\overline{OE}$	$\overline{WE}$	Mode	V_{CC} Current	I/O Pin	Ref. Cycle
H	×	×	Not Selected	I_{SB}, I_{SB1}	High Z	
L	L	H	Read	I_{CC}	Dout	Read Cycle (1)~(3)
L	H	L	Write	I_{CC}	Din	Write Cycle (1)
L	L	L	Write	I_{CC}	Din	Write Cycle (2)

■RECOMMENDED DC OPERATING CONDITIONS (Ta=0 to +70°C)

Item	Symbol	min	typ	max	Unit
Supply Voltage	V_{CC}	4.5	5.0	5.5	V
	GND	0	0	0	V
Input Voltage	V_{IH}	2.2	3.5	6.0	V
	V_{IL}	−3.0*	—	0.8	V

* Pulse Width: 50ns, DC: V_{IL} min = −0.3V

■DC AND OPERATING CHARACTERISTICS (V_{CC}=5V ±10%, GND=0V, Ta=0 to +70°C)

Item	Symbol	Test Conditions	HM6116LP-2			HM6116LP-3/-4			Unit
			min	typ*	max	min	typ*	max	
Input Leakage Current	$\|I_{LI}\|$	V_{CC}=5.5V, V_{in}=GND to V_{CC}	—	—	2	—	—	2	μA
Output Leakage Current	$\|I_{LO}\|$	$\overline{CS}=V_{IH}$ or $\overline{OE}=V_{IH}$, $V_{I/O}$=GND to V_{CC}	—	—	2	—	—	2	μA
Operating Power Supply Current	I_{CC}	$\overline{CS}=V_{IL}$, $I_{I/O}$=0mA	—	35	70	—	30	60	mA
	I_{CC1}**	V_{IH}=3.5V, V_{IL}=0.6V, $I_{I/O}$=0mA	—	30	—	—	25	—	mA
Average Operating Current	I_{CC2}	min. cycle, duty=100%	—	35	70	—	30	60	mA
Standby Power Supply Current	I_{SB}	$\overline{CS}=V_{IH}$	—	4	12	—	4	12	mA
	I_{SB1}	$\overline{CS}\geq V_{CC}-0.2V$, $V_{in}\geq V_{CC}-0.2V$ or $V_{in}\leq 0.2V$	—	2	50	—	2	50	μA
Output Voltage	V_{OL}	I_{OL}=4mA	—	—	0.4	—	—	—	V
		I_{OL}=2.1mA	—	—	—	—	—	0.4	
	V_{OH}	I_{OH}=−1.0mA	2.4	—	—	2.4	—	—	V

* : V_{CC}=5V, Ta=25°C
** : Reference Only

■AC CHARACTERISTICS (V_{CC}=5V ±10%, Ta=0 to +70°C)

●AC TEST CONDITIONS

Input Pulse Levels: 0.8 to 2.4V
Input Rise and Fall Times: 10 ns
Input and Output Timing Reference Levels: 1.5V
Output Load: 1TTL Gate and C_L = 100pF (including scope and jig)

●READ CYCLE

Item	Symbol	HM6116LP-2		HM6116LP-3		HM6116LP-4		Unit
		min	max	min	max	min	max	
Read Cycle Time	t_{RC}	120	—	150	—	200	—	ns
Address Access Time	t_{AA}	—	120	—	150	—	200	ns
Chip Select Access Time	t_{ACS}	—	120	—	150	—	200	ns
Chip Selection to Output in Low Z	t_{CLZ}	10	—	15	—	15	—	ns
Output Enable to Output Valid	t_{OE}	—	80	—	100	—	120	ns
Output Enable to Output in Low Z	t_{OLZ}	10	—	15	—	15	—	ns
Chip Deselection to Output in High Z	t_{CHZ}	0	40	0	50	0	60	ns
Chip Disable to Output in High Z	t_{OHZ}	0	40	0	50	0	60	ns
Output Hold from Address Change	t_{OH}	10	—	15	—	15	—	ns

● WRITE CYCLE

Item	Symbol	HM6116LP-2		HM6116LP-3		HM6116LP-4		Unit
		min	max	min	max	min	max	
Write Cycle Time	t_{WC}	120	—	150	—	200	—	ns
Chip Selection to End of Write	t_{CW}	70	—	90	—	120	—	ns
Address Valid to End of Write	t_{AW}	105	—	120	—	140	—	ns
Address Set Up Time	t_{AS}	20	—	20	—	20	—	ns
Write Pulse Width	t_{WP}	70	—	90	—	120	—	ns
Write Recovery Time	t_{WR}	5	—	10	—	10	—	ns
Output Disable to Output in High Z	t_{OHZ}	0	40	0	50	0	60	ns
Write to Output in High Z	t_{WHZ}	0	50	0	60	0	60	ns
Data to Write Time Overlap	t_{DW}	35	—	40	—	60	—	ns
Data Hold from Write Time	t_{DH}	5	—	10	—	10	—	ns
Output Active from End of Write	t_{OW}	5	—	10	—	10	—	ns

■ CAPACITANCE (f=1MHz, Ta=25°C)

Item	Symbol	Test Conditions	typ	max	Unit
Input Capacitance	C_{in}	V_{in}=0V	3	5	pF
Input/Output Capacitance	$C_{I/O}$	$V_{I/O}$=0V	5	7	pF

Note) This parameter is sampled and not 100% tested.

■ TIMING WAVEFORM

● Read Cycle (1) (1)



● Read Cycle (2) (1), (3), (4)



● Read Cycle (3) (1), (3), (4)



NOTES: 1. $\overline{WE}$ is High for Read Cycle.
2. Device is continuously selected, $\overline{CS}$ = V_{IL}.
3. Address Valid prior to or coincident with $\overline{CS}$ transition Low.
4. $\overline{OE}$ = V_{IL}.

● **Write Cycle (1)**



● **Write Cycle (2)** (5)



NOTES:
1. A write occurs during the overlap (t_{WP}) of a low $\overline{CS}$ and a low $\overline{WE}$.
2. t_{WR} is measured from the earlier of $\overline{CS}$ or $\overline{WE}$ going high to the end of write cycle.
3. During this period, I/O pins are in the output state so that the input signals of opposite phase to the outputs must not be applied.
4. If the $\overline{CS}$ low transition occurs simultaneously with the $\overline{WE}$ low transitions or after the $\overline{WE}$ transition, output remain in a high impedance state.
5. $\overline{OE}$ is continuously low. ($\overline{OE}$ = V_{IL})
6. D_{out} is the same phase of write data of this write cycle.
7. D_{out} is the read data of next address.
8. If $\overline{CS}$ is Low during this period, I/O pins are in the output state. Then the data input signals of opposite phase to the outputs must not be applied to them.

■LOW Vcc DATA RETENTION CHARACTERISTICS (Ta=0 to +70°C)

Item	Symbol	Test Conditions	min	typ	max	Unit
V_{CC} for Data Retention	V_{DR}	$\overline{CS} \geq V_{CC}-0.2V$, $V_{in} \geq V_{CC}-0.2V$ or $V_{in} \leq 0.2V$	2.0	—	—	V
Data Retention Current	I_{CCDR}*	V_{CC}=3.0V, $\overline{CS} \geq 2.8V$, $V_{in} \geq 2.8V$ or $V_{in} \leq 0.2V$	—	—	30	μA
Chip Deselect to Data Retention Time	t_{CDR}	See Retention Waveform	0	—	—	ns
Operation Recovery Time	t_R		t_{RC}**	—	—	ns

* 10 μA max at Ta=0°C to +40°C, V_{IH} min = −0.3V
** t_{RC} = Read Cycle Time.

● **Low Vcc Data Retention Waveform**



SUPPLY CURRENT vs. SUPPLY VOLTAGE



SUPPLY CURRENT vs. AMBIENT TEMPERATURE



ACCESS TIME vs. SUPPLY VOLTAGE



ACCESS TIME vs. AMBIENT TEMPERATURE



ACCESS TIME vs. LOAD CAPACITANCE



SUPPLY CURRENT vs. FREQUENCY



LOW INPUT VOLTAGE vs. SUPPLY VOLTAGE



HIGH INPUT VOLTAGE vs. SUPPLY VOLTAGE



OUTPUT CURRENT vs. OUTPUT VOLTAGE



OUTPUT CURRENT vs. OUTPUT VOLTAGE



STANDBY CURRENT vs. AMBIENT TEMPERATURE



STANDBY CURRENT vs. SUPPLY VOLTAGE



STANDBY CURRENT vs. INPUT VOLTAGE