


MATERIALS	
BODY	PASSIVATED STAINLESS STEEL
CONTACT	GOLD PLATED
INSULATOR	PTFE



SPECIFICATIONS

ELECTRICAL.....(@25°C AMBIENT)
FREQUENCY RANGE.....500 MHz – 2 GHz
ATTENUATION ACURACY..... ±1.0 dB MAX.
IMPEDANCE..... 50 OHMS
VSWR:.....1.35:1 MAX.
VOLTAGE RATING.....100 VOLTS MAX.
DC CURRENT.....2 AMPS MAX.
RF POWER (AVG).....2 WATTS MAX.
OPERATING TEMP. RANGE.....-55°C TO ±125°C



PASTERNAK ENTERPRISES, INC.
P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com
COAXIAL & FIBER OPTICS

DWG TITLE PE7063-10		DES. 50 OHM TNC DC BIAS PASSING ATTENUATORS, 10 dB	
REV. A	FSCM NO. 53919	CAD FILE 030409	SCALE N/A SIZE A 147

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.