

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [15-97-7123](#)  
**Status:** **Active**  
**Overview:** Mini-Fit® TPA Plugs and Receptacles  
**Description:** 4.20mm Pitch Mini-Fit® TPA Header, Dual Row, Vertical, with Snap-in Plastic Peg PCB Lock, 12 Circuits, Tin (Sn) Plating, without Drain Holes

**Documents:**

[3D Model](#) [Packaging Specification PK-30069-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-5556-003 \(PDF\)](#)

**Agency Certification**

CSA	LR19980
TUV	R72081037
UL	E29179

**General**

Product Family	PCB Headers
Series	<a href="#">30069</a>
Application	Power, Wire-to-Board
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with <a href="#">45750</a> Mini-Fit® Plus HCS Crimp Terminal Crimped to 16 AWG wire., See Molex product specification PS-45750-001 for additional current de-rating information.,
Overview	<a href="#">Mini-Fit® TPA Plugs and Receptacles</a>
Product Name	Mini-Fit® TPA
UPC	883906301088

**Physical**

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	3.446/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.80mm
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm



image - Reference only

Series

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[30069Series](#)

**Mates With**

[1597-5041](#) Receptacle

**Use With**

Mini-Fit® TPA Receptacle Housing [30071](#) , [30072](#)

Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

#### Electrical

Current - Maximum per Contact	13A
Voltage - Maximum	600V

#### Solder Process Data

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235

#### Material Info

Old Part Number	30069-12C1
-----------------	------------

#### Reference - Drawing Numbers

Packaging Specification	PK-30069-001
Product Specification	PS-5556-003
Sales Drawing	SDA-30069-****

This document was generated on 11/28/2012

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**