



Leveling Mounts - Space Saving

■ Foot (D dimension) is more compact than that of the conventional leveling mounts.



Part Number		M (Coarse)		A		H	l1	l2	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price
Type	D											
HNFJN	28	8	20	50	100	17.7	5.2	6.5	13	6.5	48	
	38	12	30	80	100	23	7.4	10	19	13	55	
	48	8	20	50	100	20.7	5.2	6.5	13	6.5	77	
		12	30	80	100	23	7.4	10	19	13	90	
	58	8	20	50	100	20.7	5.2	6.5	13	6.5	121	
		12	30	80	100	23	7.4	10	19	13	133	



Part Number		M (Coarse)		A		H	l1	l2	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price
Type	D											
HNFJR	28	8	20	50	100	28.2	5.2	6.5	13	6.5	50	
	38	12	30	80	100	35.4	7.4	10	19	13	59	
	48	8	20	50	100	33.2	5.2	6.5	13	6.5	73	
		12	30	80	100	35.4	7.4	10	19	13	85	
	58	8	20	50	100	33.2	5.2	6.5	13	6.5	115	
		12	30	80	100	35.4	7.4	10	19	13	129	


Ordering Example: Part Number - M - A
HNFJR48 - 12 - 80

Price [Configure Online](#)

Days to Ship [Configure Online](#)

Leveling Mounts

Swivel Type / Tapped Socket Type




Part Number		M-A		D	D1	H	l1	l2	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price
Type												
LEMNT (Steel)		10-75		32	21	22	6	8	17	11.0	342	
		10-100									351	
		12-75		48	23	29	7.5	10	19	16.0	378	
		12-100									390	
LEMNS (Stainless Steel)		16-100		64	27	32	10	13	24	28.3	430	
		16-130									445	

Ordering Example: Part Number
LEMNT16-130

Days to Ship [Configure Online](#)

Price [Configure Online](#)



Part Number		M (Coarse)		A	L	D	B	E	Allowable Vertical Load (kN)	Mass (g)	Unit Price
Type											
FJRP		6	14	31	25	8	9.7	0.59	11		
		8	19	37.5	30	10	11.2	1.08	21		
		10	20	42.5	40	13	13.7	1.57	38		
		12	25	51	50	17	16	3.14	70		

Part Number		M (Coarse)		B	C	D	E	H	Allowable Vertical Load (kN)	Mass (g)	Unit Price
Type											
LEMN (Nylon)		10	9.5	39.0				16			
		12	12.7	41.0	50	18		19	15.9	17.1	
		16	14.2	44.5				22			

Ordering Example: Part Number
LEMN10

Days to Ship [Configure Online](#)

Price [Configure Online](#)

Part Number		M (Coarse)		H	C	D	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price
Type										
LEMT (Steel)		6	10	14	19	4		3.1	17	
		8	13	18	25	8		4.1	34	
		10	17	22	32	10		15.4	65	
		12	19	29	48	11		20.5	167	
LEMS (Stainless Steel)		16	22	32	64	11		24.6	354	

Kgf (Load)=Nx0.101972