

596-00495

Article Number: 596-00495

Pre-Printed Solar Label, "DUAL POWER SOURCE", 4.1" X .75", Vinyl, Orange, 50/RL



 Download spec sheet

Base Data

Local Order Number	596-00495
Type	WDPSLBL
Color	Orange (OG)
Features and Benefits	• Made with UV stable inks and materials for durability and weather resistance. • The labels are supplied with aggressive adhesive to ensure long life. • Solar Installation labels meet NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.
Product Description	HellermannTyton pre-printed Solar Installation labels are designed to meet the requirements of the 2014 National Electrical Code (NEC 2014) and the 2012 International Fire Code (IFC 2012) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.
Technical Description	4.12" X .75" Black text on an Orange background that reads as;" WARNING - DUAL POWER SOURCE SECOND SOURCE IS PV SYSTEM." 50 per roll
Local Order Number 2	Spanish Version: 596-00807
Short Description	Pre-Printed Solar Label, "DUAL POWER SOURCE", 4.1" X .75", Vinyl, Orange, 50/RL

Product Dimensions

Length L (Imperial)	4.125 "
Length L (Metric)	104.6 mm
Width W (Imperial)	4.125 "
Width W (Metric)	104.6 mm
Height H (Imperial)	0.75 "
Height H (Metric)	19.05 mm

Logistics and Packaging

Quantity Per	roll
Package Quantity	50
Package Quantity (Metric)	50
Labels per Column	1
Labels per Row	1

Material and Specifications

Material	Type 443/552, UV Stable Flexible White Vinyl w/Acrylic Laminate
Material Shortcut	443/552

Adhesive Acrylic

Adhesive Shortcut Acrylic

Adhesive Operating Temperature -40°F to +174°F (-40°C to +79°C)

Halogenfree Yes

Operating Temperature -40°F to +174°F (-40°C to +79°C)

ROHS Compliant Yes

Certification/Specification UL969

UL Recognized (US) Yes