

Intel® 815/815E Chipset for Applied Computing

Product Highlights

815/815E Chipset

- Flexible processor support ranging from the Intel® Celeron™ processor at 566 MHz to the Pentium® III processor at 866 MHz and beyond with support for 66, 100, or 133 MHz Processor Side Bus (PSB) speeds
- Increased I/O bus bandwidth through the use of Intel® Hub Architecture which allows better concurrency for next-generation Applied Computing applications
- Support for 100 and 133 MHz SDRAM enabling cost effective high volume memory
- 512 MB maximum memory
- Low power sleep mode for energy savings
- Dual (815) or Quad (815E) USB ports
- Support for ATA/66 (815) or ATA/100 (815E)
- Integrated LAN Support (815E)
- Alert on LAN 1.0
- Intel 3D integrated graphics with Direct AGP expandability for vivid 2D and 3D graphics
- AGP4X upgradeable for increased graphics bandwidth allowing the highest possible graphics performance
- Add-in Graphics Performance Accelerator (GPA) card to provide up to a 30% boost for better 2D and 3D graphics performance over similar systems without a GPA card
- AC '97 Controller for better audio quality
- Digital Video Output which allows for connection of traditional TV or new digital flat-panel displays; compatible with the DVI specification
- Soft DVD MPEG-2 playback with HW motion compensation for life-like audio and video

Product Description

815/815E Chipset


With the Intel® 815 and 815E chipset, Intel has introduced innovative technology to optimize scalability, flexibility, and stability of Applied Computing Platform solutions which utilize the Intel® Pentium® III and Intel Celeron processor. The Intel 815 and 815E chipsets support Pentium III processors (0.18µ process) in a 370-pin Flip-Chip Pin Grid Array (FC-PGA) package and the Intel Celeron processors (0.18µ process) in an FC-PGA package. The chipsets include a processor side bus that automatically scales from 66 to 133 MHz based on the processor used. These chipsets utilize a single driver featuring full backwards compatibility for increased quality and reliability. Intel's 3D with Direct AGP is easily upgraded by adding a Graphics Performance Accelerator (GPA) card, or an AGP4X card for maximum graphics and video performance.

Intel's smart graphics integration makes the Intel 815 chipset an intelligent solution for today's complex Applied Computing applications. Further flexibility can be achieved by taking advantage of the Communication and Network Riser (CNR) card option, which allows for audio, modem, and/or LAN configuration on a single base board design. The smart integration in the Intel 815 chipset design is extended in the Intel 815E with the addition of integrated LAN capability as well as four USB ports. By combining internal graphics, LAN, and support for four USB ports with the ability to take advantage of soft audio/modem technology, the Intel 815E chipset delivers an ideal solution for new innovative form factors.


Built on next generation chipset technology, the Intel 815 and 815E chipsets offer the performance, stability, and reliability customers require for Applied Computing applications. The Intel 815 and 815E chipsets and drivers reduce support costs, validation costs, and offer a variety of sell-up opportunities while still providing flexibility and performance at value pricing.

INTEL® 815 CHIPSET LINECARD

PRODUCT	PRODUCT CODE	PACKAGE	FEATURES
Graphics and AGP Memory Controller Hub (GMCH)	FW82815	544 BGA	<ul style="list-style-type: none"> -Intel Accelerate Hub Architecture -Integrated scalable graphics -Intel 3D graphics with Direct AGP -Overall BOM cost savings
I/O Control Hub (ICH)	FW82801AA	241 BGA	<ul style="list-style-type: none"> -External AGP Port with the option for up to 4 MB of dedicated display cache video memory -Direct connection to the GMCH with Intel's accelerated hub architecture -Supports 32-bit PCI -IDE Controllers with ATA66 -Dual USB ports -AC '97 controller
I/O Control Hub 2 (ICH2)	FW82801BA	360 EBGA	<ul style="list-style-type: none"> -Direct connection to the GMCH with Intel's accelerated hub architecture -Supports 32-bit PCI -IDE Controllers with ATA100 -Four USB ports -AC '97 controller with 6 Channel Sound -Integrated LAN connect interface



815 Chipset Block Diagram



Additional ICH2 Features

Intel Access

Developer's Site	developer.intel.com
Embedded Intel Architecture Home Page	developer.intel.com/design/intarch
Development Kit Web Site	developer.intel.com/design/intarch/devkits
Other Intel Support: Intel Literature Center	developer.intel.com/design/litcentr (800) 548-4725 7 a.m. to 7 p.m. CST (U.S. and Canada) International locations please contact your local sales office.
General Information Hotline	(800) 628-8686 or (916) 356-3104 5 a.m. to 5 p.m. PST

Information in this document is provided in connection with Intel products. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Intel's Terms and Conditions of Sale for such products, Intel assumes no liability whatsoever, and Intel disclaims any express or implied warranty, relating to sale and/or use of Intel products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right. Intel products are not intended for use in medical, life saving, or life sustaining applications. Intel may make changes to specifications and product descriptions at any time, without notice.

Designers must not rely on the absence or characteristics of any features or instructions marked "reserved" or "undefined." Intel reserves these for future definition and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to them.

*Other brands and names are the property of their respective owners.

For more information, visit the Intel Web site at: developer.intel.com



UNITED STATES AND CANADA
Intel Corporation
Robert Noyce Bldg.
2200 Mission College Blvd.
P.O. Box 58119
Santa Clara, CA 95052-8119
USA

EUROPE
Intel Corporation (UK) Ltd.
Pipers Way
Swindon
Wiltshire SN3 1RJ
UK

ASIA-PACIFIC
Intel Semiconductor Ltd.
32/F Two Pacific Place
88 Queensway, Central
Hong Kong, SAR

JAPAN
Intel Kabushiki Kaisha
P.O. Box 115 Tsukuba-gakuen
5-6 Tokodai, Tsukuba-shi
Ibaraki-ken 305
Japan

SOUTH AMERICA
Intel Semicondutores do Brasil
Rue Florida, 1703-2 and CJ22
CEP 04565-001 Sao Paulo-SP
Brazil