

LT Series


Low Pressure Drop and
Low Thermal Resistance Heat Sink

ALPHA




ALPHA

Low Pressure Drop and Low Thermal Resistance Heat Sink

LT70



DIM




HEAT SINK
MATERIAL : A 6063
FINISH : CLEAR ANODIZE

MODEL	HEIGHT [h]	THICKNESS [t]	WEIGHT (grams)
LT70-20W	20.0	3.0	87.6
LT70-25W	25.0	3.5	106.9
LT70-30W	30.0	4.0	126.2
LT70-35W	35.0		140.4
LT70-40W	40.0	5.0	164.8

Dimensions : mm

DATA



- Thermal Resistance (Ducted)
(Solid Line ———)
- Pressure Drop
(Center Line - - -)

- LT70-20B
- LT70-25B
- ▲ LT70-30B
- LT70-35B
- LT70-40B

■ Based on Alpha's Standard Test Procedure. (Refer to page marked Technical Information.)
Dummy Heater Size : 12.7SQ mm

Alpha Company Ltd.

256-1 UEDA, NUMAZU-CITY SHIZUOKA-PREF., JAPAN
PHONE +81(55)966 0789
FAX +81(55)966 9192
E mail : alpha@micforg.co.jp
URL : <http://www.micforg.co.jp>


Alpha Novatech, Inc. - a subsidiary of Alpha Company.

473 Sapena Ct. #12 Santa Clara, CA 95054 USA
PHONE +1(408)567-8082
FAX +1(408)567-8053
E mail : sales@alphanovatech.com
URL : <http://www.alphanovatech.com>


ALPHA

Low Pressure Drop and
Low Thermal Resistance Heat Sink

LT90



DIM




HEAT SINK
MATERIAL : A 6063
FINISH : CLEAR ANODIZE

MODEL	HEIGHT [h]	THICKNESS [t]	WEIGHT (grams)
LT90-25W	25.0	6.0	221.6
LT90-30W	30.0		245.6
LT90-35W	35.0	7.0	286.5
LT90-40W	40.0		310.5

Dimensions : mm

DATA



- Thermal Resistance (Ducted)
(Solid Line —)
- Pressure Drop
(Center Line - -)

- LT90-25W
- ▲ LT90-30W
- LT90-35W
- LT90-40W



■ Based on Alpha's Standard Test Procedure. (Refer to page marked Technical Information.)
Dummy Heater Size : 25.0SQ mm

Alpha Company Ltd.

256-1 UEDA,NUMAZU-CITY SHIZUOKA-PREF.,JAPAN
PHONE +81(55)966 0789
FAX +81(55)966 9192
E mail : alpha@micforg.co.jp
URL : <http://www.micforg.co.jp>

Alpha Novatech, Inc. - a subsidiary of Alpha Company.


473 Sapena Ct. #12 Santa Clara, CA 95054 USA
PHONE +1(408)567-8082
FAX +1(408)567-8053
E mail : sales@alphanovatech.com
URL : <http://www.alphanovatech.com>

ALPHA**Low Pressure Drop and
Low Thermal Resistance Heat Sink****LT13070****DIM**

HEAT SINK
 MATERIAL : A 6063
 FINISH : CLEAR ANODIZE

MODEL	HEIGHT [h]	WEIGHT (grams)
LT13070-30W	30.0	287.1
LT13070-35W	35.0	314.2
LT13070-40W	40.0	341.3
LT13070-45W	45.0	368.4

Dimensions : mm

DATA

● Thermal Resistance (Ducted)
 (Solid Line —)
 ● Pressure Drop
 (Center Line - - -)

▲ LT13070-30W
 ■ LT13070-35W
 ● LT13070-40W
 △ LT13070-45W



■ Based on Alpha's Standard Test Procedure. (Refer to page marked Technical Information.)
 Dummy Heater Size : 25.0SQ mm

Alpha Company Ltd.

256-1 UEDA, NUMAZU-CITY SHIZUOKA-PREF., JAPAN
 PHONE +81(55)966 0789
 FAX +81(55)966 9192
 E mail : alpha@micforg.co.jp
 URL : <http://www.micforg.co.jp>

Alpha Novatech, Inc. - a subsidiary of Alpha Company.


473 Sapena Ct. #12 Santa Clara, CA 95054 USA
 PHONE +1(408)567-8082
 FAX +1(408)567-8053
 E mail : sales@alphanovatech.com
 URL : <http://www.alphanovatech.com>

ALPHA**Low Pressure Drop and
Low Thermal Resistance Heat Sink****LT70130****DIM**

HEAT SINK
 MATERIAL : A 6063
 FINISH : CLEAR ANODIZE

MODEL	HEIGHT [h]	WEIGHT (grams)
LT70130-30W	30.0	297.1
LT70130-35W	35.0	326.3
LT70130-40W	40.0	355.5
LT70130-45W	45.0	384.7

Dimensions : mm

DATA

● Thermal Resistance (Ducted)
 (Solid Line —)
 ● Pressure Drop
 (Center Line - - -)

▲ LT70130-30W
 ■ LT70130-35W
 ● LT70130-40W
 △ LT70130-45W

■ Based on Alpha's Standard Test Procedure. (Refer to page marked Technical Information.)
 Dummy Heater Size : 25.0SQ mm

Alpha Company Ltd.

256-1 UEDA, NUMAZU-CITY SHIZUOKA-PREF., JAPAN
 PHONE +81(55)966 0789
 FAX +81(55)966 9192
 E mail : alpha@micforg.co.jp
 URL : <http://www.micforg.co.jp>

Alpha Novatech, Inc. - a subsidiary of Alpha Company.

473 Sapena Ct. #12 Santa Clara, CA 95054 USA
 PHONE +1(408)567-8082
 FAX +1(408)567-8053
 E mail : sales@alphanovatech.com
 URL : <http://www.alphanovatech.com>