




INSULATION

SERRATIONS

1

6.73 ±0.13 DIA

[.265 ±.005]

FOR 1/4 STUD

11.91 [.469]

11.10 MIN [.437]

21.67 MAX [.853]

27.69 MAX [1.090]

BODY

1

2

3

4

5

6

STAMP AMP 16-14* APPROX AS SHOWN

WIRE INSULATION DIA: 3.00-4.90 [.118-.193]

TONGUE MATERIAL THK: 0.79 ±0.05 [.031 ±.002]

MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - BLUE

MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - BLACK

REPLACED BY 8-34162-1

OBSOLETE

25

100

4000

-

4000

-

QTY

LOOSE PC,BAG

LOOSE PC,BOX

ON TAPE, REEL

LOOSE PIECE

ON TAPE, REEL

LOOSE PIECE

PACKAGE TYPE

8-34162-5

8-34162-1

2-34162-3

2-34162-2

2-34162-1

34162

PART NO.

AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER

1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER

1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

MAX RECOMMENDED OPERATING
TEMPERATURE:

105°C [221° F]

VOLTAGE RATING:

N/A

CIRCULAR MIL AREA:

1.04-2.62mm² [2,050-5,180]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.20 [.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
TIN PER ASTM B545

MATERIAL

SEE NOTES

DWN

DK SCHRUM

08/06/92

CHK

RE HERSEY

11/10/92

APVD

M ELLIS

11/10/92

PRODUCT SPEC

108-1034

APPLICATION SPEC

NOT AVAILABLE

WEIGHT

-

CUSTOMER DRAWING

STE

TE Connectivity

NAME

TERMINAL, RING TONGUE,
PLASTI-GRIP

-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-34162

-

SCALE

4:1

SHEET

1 OF 1

REV

M1

1470-19 (3/11)