



PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .020$	W $\pm .010$	C $\pm .015$	M $\pm .020$	H $\pm .010$
PN18-6LF-3K	#6	.82 (20.82)	.27 (6.9)	.19 (4.82)	.63 (16.00)	.15 (3.81)
PN18-8LF-3K	#8	.89 (22.61)	.29 (7.37)	.23 (5.84)	.68 (17.27)	.16 (4.06)
PN18-10LF-3K	#10	.89 (22.61)	.33 (8.38)	.23 (5.84)	.68 (17.27)	.19 (4.83)

1. UL LISTED AND CSA CERTIFIED FOR:
 - A. 600 V MAX. VOLTAGE RATING
(1000V. MAX. IN SIGNS, FIXTURES & LUMINARIES)
 - B. 221°F (105°C) MAX. TEMP. RATING OF
INSULATION MATERIAL
 - C. #22-18 AWG (0.5-1.5 mm²) SOLID OR STRANDED
COPPER WIRE
2. PACKAGE QTY. : 3K = 3000 PCS.
CONTINUOUS MOLDED CARRIER STRIP
3. MATERIAL:
 - A. STAMPING - .03" THICK COPPER, TIN PLATED
 - B. HOUSING - RED NYLON
 - C. SLEEVE - BRASS, TIN PLATED
4. WIRE STRIP LENGTH: $7/32^{+1/32}_{-0}$ (5.6^{+0.8}₋₀)
5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
6. INSTALLATION TOOLS :
 - A. PRESSES - CP-851, CP-860, CP-861
 - B. APPLICATOR - CA-800
 - C. DIE INSERTS - CD-800-1



								PANDUIT CORP. TINLEY PARK, ILLINOIS			
								TERMO 3PC. CONTINUOUSLY MOLDED NYLON INSULATED, 22-18 BARREL, LOCKING FORKS			
08	3/10	SRB		Changed "W" dimension for PN18-6LF-3K							
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								GRM		NONE	A41103