



SEMITRANS® 2

SKM150GAL12V

Features


- V-IGBT = 6. Generation Trench V-IGBT (Fuji)
- CAL4 = Soft switching 4. Generation CAL-diode
- Isolated copper baseplate using DBC technology (Direct Copper Bonding)
- UL recognized, file no. E63532
- Increased power cycling capability
- With integrated gate resistor
- Low switching losses at high di/dt

Typical Applications*

- DC/DC – converter
- Brake chopper
- Switched reluctance motor
- DC – Motor

Remarks

- Case temperature limited to $T_c = 125^\circ\text{C}$ max, recomm. $T_{op} = -40 \dots +150^\circ\text{C}$, product rel. results valid for $T_j = 150^\circ$



GAL

Absolute Maximum Ratings

Symbol	Conditions		Values	Unit
IGBT				
V _{CES}	T _j = 25 °C		1200	V
I _C	T _j = 175 °C	T _c = 25 °C	231	A
		T _c = 80 °C	176	A
I _{Cnom}			150	A
I _{CRM}	I _{CRM} = 3xI _{Cnom}		450	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 720 V V _{GE} ≤ 20 V V _{CES} ≤ 1200 V	T _j = 125 °C	10	μs
T _j			-40 ... 175	°C
Inverse diode				
I _F	T _j = 175 °C	T _c = 25 °C	189	A
		T _c = 80 °C	141	A
I _{Fnom}			150	A
I _{FRM}	I _{FRM} = 3xI _{Fnom}		450	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 25 °C		900	A
T _j			-40 ... 175	°C
Freewheeling diode				
I _F	T _j = 175 °C	T _c = 25 °C	189	A
		T _c = 80 °C	141	A
I _{Fnom}			150	A
I _{FRM}	I _{FRM} = 3xI _{Fnom}		450	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 25 °C		900	A
T _j			-40 ... 175	°C
Module				
I _{t(RMS)}	T _{terminal} = 80 °C		200	A
T _{stg}			-40 ... 125	°C
V _{isol}	AC sinus 50Hz, t = 1 min		4000	V

Characteristics

Symbol	Conditions	min.	typ.	max.	Unit
IGBT					
$V_{CE(sat)}$	$I_C = 150\text{ A}$ $V_{GE} = 15\text{ V}$ chipelevel	$T_j = 25^\circ\text{C}$	1.75	2.20	V
		$T_j = 150^\circ\text{C}$	2.20	2.50	V
V_{CE0}		$T_j = 25^\circ\text{C}$	0.94	1.04	V
		$T_j = 150^\circ\text{C}$	0.88	0.98	V
r_{CE}	$V_{GE} = 15\text{ V}$	$T_j = 25^\circ\text{C}$	5.40	7.7	$\text{m}\Omega$
		$T_j = 150^\circ\text{C}$	8.80	10.13	$\text{m}\Omega$
$V_{GE(th)}$	$V_{GE} = V_{CE}, I_C = 6\text{ mA}$	5.5	6	6.5	V
I_{CES}	$V_{GE} = 0\text{ V}$ $V_{CE} = 1200\text{ V}$	$T_j = 25^\circ\text{C}$	0.1	0.3	mA
		$T_j = 150^\circ\text{C}$			mA
C_{ies}	$V_{CE} = 25\text{ V}$ $V_{GE} = 0\text{ V}$	$f = 1\text{ MHz}$	9		nF
C_{oes}		$f = 1\text{ MHz}$	0.89		nF
C_{res}		$f = 1\text{ MHz}$	0.884		nF
Q_G	$V_{GE} = -8\text{ V} \dots +15\text{ V}$		1650		nC
R_{Gint}			5.0		Ω



SEMITRANS® 2

SKM150GAL12V

Features

- V-IGBT = 6. Generation Trench V-IGBT (Fuji)
- CAL4 = Soft switching 4. Generation CAL-diode
- Isolated copper baseplate using DBC technology (Direct Copper Bonding)
- UL recognized, file no. E63532
- Increased power cycling capability
- With integrated gate resistor
- Low switching losses at high di/dt


Typical Applications*

- DC/DC – converter
- Brake chopper
- Switched reluctance motor
- DC – Motor

Remarks

- Case temperature limited to $T_c = 125^\circ\text{C}$ max, recomm. $T_{op} = -40 \dots +150^\circ\text{C}$, product rel. results valid for $T_j = 150^\circ$

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
t _{d(on)}	V _{CC} = 600 V	T _j = 150 °C		258		ns
t _r	I _C = 150 A	T _j = 150 °C		32		ns
E _{on}	V _{GE} = ±15 V	T _j = 150 °C		13.5		mJ
t _{d(off)}	R _{G on} = 1.5 Ω	T _j = 150 °C		388		ns
t _f	R _{G off} = 1.5 Ω	T _j = 150 °C		62		ns
E _{off}	di/dt _{on} = 4400 A/μs du/dt _{off} = 1800 A/μs du/dt _{off} = 8100 V/μs	T _j = 150 °C		14.2		mJ
R _{th(j-c)}	per IGBT				0.19	K/W
Inverse diode						
V _F = V _{EC}	I _F = 150 A	T _j = 25 °C		2.14	2.46	V
	V _{GE} = 0 V chip	T _j = 150 °C		2.07	2.38	V
V _{F0}		T _j = 25 °C		1.3	1.5	V
		T _j = 150 °C		0.9	1.1	V
r _F		T _j = 25 °C		5.6	6.4	mΩ
		T _j = 150 °C		7.8	8.5	mΩ
I _{RRM}	I _F = 150 A	T _j = 150 °C		160		A
Q _{rr}	di/dt _{off} = 5500 A/μs	T _j = 150 °C		21.5		μC
E _{rr}	V _{GE} = ±15 V V _{CC} = 600 V	T _j = 150 °C		8.9		mJ
R _{th(j-c)}	per diode				0.31	K/W
Freewheeling diode						
V _F = V _{EC}	I _F = 150 A	T _j = 25 °C		2.14	2.46	V
	V _{GE} = 0 V chip	T _j = 150 °C		2.07	2.38	V
V _{F0}		T _j = 25 °C		1.3	1.5	V
		T _j = 150 °C		0.9	1.1	V
r _F		T _j = 25 °C		5.6	6.4	mΩ
		T _j = 150 °C		7.8	8.5	mΩ
I _{RRM}	I _F = 150 A	T _j = 150 °C		116		A
Q _{rr}	di/dt _{off} = 5900 A/μs	T _j = 150 °C		22		μC
E _{rr}	V _{GE} = ±15 V V _{CC} = 600 V	T _j = 150 °C		8.2		mJ
R _{th(j-c)}	per Diode				0.31	K/W
Module						
L _{CE}					30	nH
R _{CC'+EE'}	terminal-chip	T _C = 25 °C		0.65		mΩ
		T _C = 125 °C		1		mΩ
R _{th(c-s)}	per module			0.04	0.05	K/W
M _s	to heat sink M6		3		5	Nm
M _t		to terminals M5	2.5		5	Nm
						Nm
w					160	g



GAL




Fig. 1: Typ. output characteristic, inclusive $R_{CC'} + E_{E'}$




Fig. 2: Rated current vs. temperature $I_C = f(T_C)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. transfer characteristic




Fig. 6: Typ. gate charge characteristic




Fig. 7: Typ. switching times vs. I_C




Fig. 8: Typ. switching times vs. gate resistor R_G




Fig. 9: Transient thermal impedance




Fig. 10: Typ. CAL diode forward charact., incl. $R_{CC'+EE'}$




Fig. 11: CAL diode peak reverse recovery current






Fig. 12: Typ. CAL diode peak reverse recovery charge



SEMITRANS 2



GAL

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our staff.