

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AA	22		A1	REVISED PER ECO-11-005033	28MAR11	RK HMR

D

C

B


A

D

C


B

A




- 1 MATERIAL: HOUSING – HTN NYLON, BLACK, REFLOW COMPATIBLE, UL 94V-0. TERMINALS—.013[0.33] THICK PHOS BRONZE PLATED WITH .000050[1.27μm] MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND .000150 [3.81μm] MINIMUM THICK MATTE TIN IN SOLDER AREA OVER .000050[1.27μm] MINIMUM THICK NICKEL UNDERPLATE.

- 2 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3. ALL DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
4. ALL DIMENSIONS SHOWN IN BRACKETS [] ARE IN MILLIMETERS.
- 5 USE #30 DRILL BIT OR 3.25mm DRILL BIT WHEN PRODUCING THESE PCB HOLES.



SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE



SUGGESTED PANEL CUTOUT

5557785-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. SLACK/L.A.MAYER 01JUNE2005	TE Connectivity			
DIMENSIONS: INCHES		CHK J.WESTMAN 01JUNE2005				
		APVD S.FLICKINGER 01JUNE2005	NAME MODULAR JACK ASSEMBLY, 8 POSITION,RIGHT ANGLE, LOW PROFILE			
		PRODUCT SPEC 108-1163				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-2048	SIZE A2	CAGE CODE 00779	DRAWING NO C=5557785	RESTRICTED TO -
MATERIAL SEE NOTE 1		WEIGHT -				
FINISH SEE NOTE 1		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 of 1	REV A1	