






Assembly Layout

SPECIFICATIONS

Voltage rating : 250V AC/DC

Current rating : 7A AC/DC

Withstanding voltage : 1500V AC/minute

Contact resistance : 20mΩ max

Temperature range : -40°C to +105°C

Insulation resistance : 1000MΩ min

MATERIAL


Insulator : Nylon66 (UL94V-2)

Insulator color : Transprnt White

Contact : Brass

Plating : Tin Plated

Poles	Dimensions(mm)		
	A	B	C
2	----	5.60	8.60
4	4.20	9.80	12.80
6	8.40	14.00	17.00
8	12.60	18.20	21.20
10	16.80	22.40	25.60
12	21.00	26.60	29.80
14	25.20	30.80	34.00
16	29.40	35.00	38.20
18	33.60	39.20	44.40
20	37.80	43.40	48.60
22	42.00	47.60	52.80
24	46.20	51.80	57.00



TOLERANCE (mm)	APPROVALS	DATE	TITLE		AMPHENOL	
X. ±0.3	DRAWN Stephane	05/Jan/2007	4.2 Power Wafer R/A Dip w/Ear		Amphenol European Design Center	
XX ±0.2	CHECKED Rob	05/Jan/2007				
X.XX ±0.15	APPROVED Rob	05/Jan/2007				
UNLESS OTHERWISE SPECIFIED	UNIT : mm	SIZE : A4	DRAWING N°	MF42-RE-XX		REV. A