



P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REV PER ECO 16-000990	2-19-16	CT	PD

D

C

B

A



- 1 WIRE INSULATION: 10.79[.425] – 11.94[.470] DIA
- △2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.

BODY: COPPER ASTM-B187 ANNEALED
TIN PL MIL-T-10727 0.00457[.000150] MIN THK
INSERT & FUNNEL: BRASS PER ASTM B36
NICKEL PLATE SAE AMS QQ-N-290A,
DATED JULY 2000, 0.00254 [.000100] MIN THK

55837-1

MATERIAL AND FINISH

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 6/15/92	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK WJ VOCKROTH 6/16/92				
		APVD AJ KAUFMAN 6/16/92	NAME			
		PRODUCT SPEC 108-11011	WIRE TERMINAL, COPALUM SEALED, RING TONGUE, WIRE SIZE: 1/0 AL, 2 COPPER			
MATERIAL SEE TABLE		FINISH SEE TABLE	SIZE 114-2134	CAGE CODE A200779	DRAWING NO C=55837	RESTRICTED TO -
		WEIGHT 62 GRAMS	SCALE 2:1	SHEET 1 of 1	REV H	
		CUSTOMER DRAWING				