


SURFACE MOUNT SCHOTTKY BARRIER RECTIFIERS	REVERSE VOLTAGE - 20 to 100 Volts FORWARD CURRENT - 3.0 Amperes
FEATURES ● For surface mounted applications ● Metal-Semiconductor junction with guarding ● Epitaxial construction ● Very low forward voltage drop ● High current capability ● Plastic material has UL flammability classification 94V-0 ● For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications. MECHANICAL DATA ● Case: Molded Plastic ● Polarity: Indicated by cathode band ● Weight: 0.002 ounces, 0.064 grams	SMA  Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS									
Rating at 25°C ambient temperature unless otherwise specified.									
Single phase, half wave ,60Hz, resistive or inductive load.									
For capacitive load, derate current by 20%									

CHARACTERISTICS	SYMBOL	SS32A	SS33A	SS34A	SS35A	SS36A	SS38A	SS310A	UNIT
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	20	30	40	50	60	80	100	V
Maximum RMS Voltage	V _{RMS}	14	21	28	35	42	56	70	V
Maximum DC Blocking Voltage	V _{DC}	20	30	40	50	60	80	100	V
Maximum Average Forward Rectified Current @T _L =100 °C	I _(AV)	3.0							A
Peak Forward Surge Current 8.3ms Single Half Sine-Wave Super Imposed On Rated Load (JEDEC Method)	I _{FSM}	80							A
Maximum Forward Voltage at 3.0A DC	V _F	0.45	0.55	0.6	0.7		0.85		V
Maximum DC Reverse Current @T _J =25°C at Rated DC Blocking Voltage @T _J =100°C	I _R	1.0 20							mA
Typical Junction Capacitance (Note1)	C _J	250							pF
Typical Thermal Resistance (Note2)	R _{θJL}	10							°C/W
Typical Thermal Resistance (Note3)	R _{θJA}	50							°C/W
Operating Temperature Range	T _J	-55 to + 150							°C
Storage Temperature Range	T _{STG}	-55 to + 175							°C

NOTES:1.Measured at 1.0 MHz and applied reverse voltage of 4.0V DC. 2.Thermal resistance junction to lead. 3.Thermal resistance junction to ambient.									
---	--	--	--	--	--	--	--	--	--



FIG. 1 - FORWARD CURRENT DERATING CURVE




FIG.2 - MAXIMUM NON-REPETITIVE
SURGE CURRENT




FIG.3-TYPICAL FORWARD CHARACTERISTICS




FIG.4-TYPICAL JUNCTION CAPACITANCE




FIG.5-TYPICAL REVERSE CHARACTERISTICS

