


▲ LED SPECS	UNITS	YELLOW
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @20mA	V	2.0-2.4
LUMINOUS INTENSITY @ 10mA	MCD	100




T	D
1.0-2.0	8.0-8.2
2.0-2.5	8.2-8.4
2.5-3.0	8.4-8.6



▲ YELLOW LED
CIRCUIT: SPST
OFF (ON)

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: $X.X \pm 0.4$
 $X.XX \pm 0.25$
- RATING: 30VDC @ 100mA
- CONTACT RESISTANCE: 50 Milli-OHMS MAX.
- INSULATION RESISTANCE: 100Mega-OHMS MIN@500VDC.
- OPERATING FORCE: 250 ± 100 gf
- TRAVEL: 1.8 ± 0.3 mm
- OPERATING TEMPERATURE: -40°C TO 85°C
- OPERATING LIFE: 50,000 CYCLES
- LED: YELLOW
- ▲ DENOTES CRITICAL PARAMETERS
- 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC



E-SWITCH™

TITLE LP10A1AY

B	19582	CHANGED DIMS: was 9.6 & 6.1	1/13/11	BGL
A	18727	New Release	12/10/09	BLR

REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	2=1	DATE	12/10/2009	DR	BLR	DWG	B200203	REV	B
-------	-----	------	------------	----	-----	-----	---------	-----	---