






FCIconnect.com

Copyright FCI


PRODUCT NUMBER
SEE NOTE 1




mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC					
ltr				ecn no		dr		date		tolerances unless otherwise specified					
A				V41186		GIP		8/4/94		angles		linear		.XX±.01/.3	
B				V50270		SAR		3/10/95		angles		linear		.XXX±.005/.13	
C				V80922		DLW		10/6/98		angles		linear		0°±2'	
D				V00293		JWS		2/7/00		dr		G. PETERS		8/10/94	
E				M06-0255		AGS		7/7/06		enrg		J. AFTON		8/4/94	
										chr		J. AFTON		8/12/94	
										appd		S. CLARK		8/12/94	
sheet index		revision sheet		E		E		1		2					

form: A3


PRODUCT NUMBER	DIM	LENGTH FORMULAS
SEE NOTE 1	DIM "A"	$.100/2.54 \times \text{NO. OF COLUMNS} + 1.05/26.7$
	DIM "B"	$.100/2.54 \times \text{NO. OF COLUMNS} + .750/19.05$
	DIM "C"	$.100/2.54 \times \text{NO. OF COLUMNS DIVIDED BY 2} - .100/2.54$




SECTION U-U



SECTION W-W



SECTION X-X



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100/2.54 GRID
UNLESS OTHERWISE SPECIFIED)

NOTES:

- PRODUCT NUMBERING CODE:
50783 - X YYY Z
TAIL LENGTH(NOTE 6)
NO. OF POSITIONS(NOTE 2)
PLATING(NOTE 4)
BASE NUMBER
- THIS PRODUCT IS CONFIGURED IN SIZES OF 20 THRU 122 COLUMNS IN INCREMENTS OF TWO.
i.e.: 20,22,24,26,.....118,120,122.
- HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK.
PIN MATERIAL: PHOS. BRONZE
- PLATING OPTIONS:
A = 50u" Ni UNDER ALL WITH 30u" Au ON CONTACT AREA SnPb ON PCB INTERFACE AND Au FLASH ON ALL OTHER AREAS.
- MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.
- TAIL LENGTH OPTIONS
S = .10 / 2.5
- FOR DOCUMENTATION MENU, SEE SPEC. BUS-01-057.

mat'l. code	surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecn no	dr	date	title
E				4 ROW R/A HEADER w/S.T. PINS, 1 G.P., DUPLEX PLTD.
				dwg no
				50783
				sheet 2 of 2 size A3
				type Product Customer Drawing
sheet index	revision sheet			