




- VDC: 12, 24, 48
- RPM: 1150~2800
- CFM: 47.33~124.18
- Impeller: 7 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 24; UL 1007 lead wires
- Mass:250.5g




DC FAN 120x120x38mm


Specification

	Bearing	Voltage	Current	Speed	Input Power	Air Flow	Static Pressure	Noise	Weight
MODEL NO	○ Sleeve ● One ball and one sleeve ○ Hydraulic	(Vdc)	(Amp)	(Rpm)	(Watts)	(CFM)	(mm/H ₂ O)	dB(A)	Gram
B1238B12E	●	12	0.09	1150	1.08	47.33	1.33	22.9	250.5
B1238B12L	●	12	0.26	1800	3.12	76.54	3.09	34.4	250.5
B1238B12M	●	12	0.33	2200	3.96	98.43	5.07	38.7	250.5
B1238B12H	●	12	0.50	2600	6.00	114.79	6.79	45.0	250.5
B1238B12U	●	12	0.65	2800	7.80	124.18	8.20	45.4	250.5
B1238B24E	●	24	0.10	1150	2.40	47.33	1.33	22.9	250.5
B1238B24L	●	24	0.15	1800	3.60	76.54	3.09	34.4	250.5
B1238B24M	●	24	0.25	2200	6.00	98.43	5.07	38.7	250.5
B1238B24H	●	24	0.35	2600	8.40	114.79	6.79	45.0	250.5
B1238B48L	●	48	0.08	1800	3.84	76.54	3.09	34.4	250.5
B1238B48M	●	48	0.15	2200	7.20	98.43	5.07	38.7	250.5
B1238B48H	●	48	0.18	2600	8.64	114.79	6.79	45.0	250.5
E1238B12H	●	12	0.2~0.50	1150~2600	2.4~6.0	47.33~114.79	1.33~6.79	22.9~45.0	250.5
F1238B12E	●	12	0.11	1150	1.32	47.33	1.33	22.9	250.5
F1238B12L	●	12	0.26	1800	3.12	76.54	3.09	34.4	250.5
F1238B12M	●	12	0.40	2200	4.80	98.43	5.07	38.7	250.5
F1238B12H	●	12	0.50	2600	6.00	114.79	6.79	45.0	250.5
F1238B12U	●	12	0.80	2800	9.60	124.18	8.20	45.4	250.5
F1238B24E	●	24	0.10	1150	2.40	47.33	1.33	22.9	250.5
F1238B24L	●	24	0.15	1800	3.60	76.54	3.09	34.4	250.5
F1238B24M	●	24	0.25	2200	6.00	98.43	5.07	38.7	250.5
F1238B24H	●	24	0.45	2600	10.80	114.79	6.79	45.0	250.5
F1238B24U	●	24	0.50	2800	12.00	124.18	8.20	45.4	250.5
F1238B48M	●	48	0.15	2200	7.20	98.43	5.07	38.7	250.5
F1238B48H	●	48	0.20	2600	9.60	114.79	6.79	45.0	250.5
P1238B24H	●	24	0.2~0.32	1400~2800	4.8~7.68	65.07~124.18	2.32~8.20	27.3~45.4	250.5
R1238B12H	●	12	0.2~0.50	1150~2600	2.4~6.0	47.33~114.79	1.33~6.79	22.9~45.0	250.5

Design specifics subject to change without notice.




STATIC PRESSURE





- VDC: 12
- RPM: 2800
- CFM: 142.37
- Impeller: 7 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 24; UL 1007 lead wires
- Mass: 265.5g




DC FAN 120x120x38mm

Specification

MODEL NO	Bearing	Voltage	Current	Speed	Input Power	Air Flow	Static Pressure	Noise	Weight
	○ Sleeve ● One ball and one sleeve ○ Hydraulic	(Vdc)	(Amp)	(Rpm)	(Watts)	(CFM)	(mm/H ₂ O)	dB(A)	Gram
F1238B12UY	●	12	0.85	2800	10.20	142.37	8.79	47.4	265.5

Design specifics subject to change without notice.



STATIC PRESSURE

