






MATED CONDITION (REF.)

NOTE

1. MATED WITH : 104085-0400, 104085-0410 , 101085-0420
2. MATERIALS
 - ① - HEADER : LCP(E130I), GLASS FILLED, UL94V-0,
HALOGEN FREE, COLOR OF NATURAL
 - ② - FITTING NAIL : PHOSPHOR BRONZE, 0.2mm THICKNESS
 - ③ - CONTACT TERMINAL : POSPHOR BRONZE, 0.25mm THICKNESS
3. FINISHES
 - ② - FITTING NAIL : PURE-TIN PLATING ON OVERALL.
THICKNESS 3.0 μ m~5.0 μ m
UNDER PLATING Ni OVERALL.
THICKNESS 1.25 μ m~3.75 μ m
 - ③- CONTACT TERMINAL : PURE-TIN PLATING ON OVERALL.
THICKNESS 3.0 μ m~5.0 μ m
UNDER PLATING Ni OVERALL.
THICKNESS 1.25 μ m~3.75 μ m
4. COPLANALITY OF SOLDER TAILS (PEAK TEMP. : 260°C),
BEFORE & AFTER REFLOW : 0.08MAX





SECTION Z-Z (SCALE 20:1)

NEW RELEASED	2010/12/02	QUALITY SYMBOL 9
EC NO: KOR2011-0057	2010/12/02	▽=0
DRWN:CBCHIN	2010/12/02	▽C=0
CHK'D:SH. CHU	2010/12/02	
APPR: YUNS IKK IM	2010/12/02	
REV		

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± .---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.20	± ---
1 PLACE	± 0.25	± ---
ANGULAR ± ---°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		



DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
JB. JIN	2010/07/01
CHECKED BY	DATE
SH. CHU	2010/07/01
APPROVED BY	DATE
YSOO. KIM	2010/07/01
MATERIAL NO.	
1040860410	
SIZE	THIS DRAWING CONTAINS INCORPORATED AND
A3	

SCALE 10:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
TITLE		
1.25 W-T-B CONN. HEADER ASS'Y-4P		
 MOLEX INCORPORATED		
DOCUMENT NO. SD-104086-001		SHEET NO. 1 OF 01
TAINS INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		




SECTION A-A


PULL OUT DIRECTION



SECTION B-B




PLASTIC BOBBIN




NOTES

1. QUANTITY OF CONNECTORS : 2,000 PCS/REEL

2. LEAD LENGTH



3. PEELING OFF FORCE OF COVER TAPE : 0.1N~0.59N(10.2GF~60GF)
(PEELING DIRECTION AS SHOW IN FOLLOW FIG.)
PEELING OFF SPEED : 300mm/Min.(Ref.)



4. FLASH IN ANY PORTION SHOULD BE LESS THAN 0.20mm MAX.
5. UNLESS OTHERWISE SPECIFIED INNER R0.2 MAX
6. DRAFT ANGLE 3°MAX

3	PLASTIC BOBBIN	HI P.S	WHITE
2	COVER TAPE	PET ANTISTATIC	21.3m
1	CARRIER (EMBOSSD) TAPE	PET ANTISTATIC	
NO.	DESCRIPTION	MATERIAL	REMARK

ORDER NO. 104086-0410

DESIGN UNITS METRIC THIRD ANGLE PROJECTION

SCALE 4:1

TITLE 1.25 W-T-B CONN
HEADER ASS'Y-4P
EMBOSSD PACKAGE

MOLEX MOLEX INCORPORATED

DOCUMENT NO. SD-104086-002 SHEET NO. 1 OF 01

DIMENSION STYLE MM ONLY

DRAWN BY JB. JIN DATE 2010/07/09

CHECKED BY SH. CHU DATE 2010/07/09

APPROVED BY YS00.KIM DATE 2010/07/09

MATERIAL NO. 1040860410


SIZE A3

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.25	± ---
1 PLACE	± 0.25	± ---
ANGULAR	± 3 °	

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

QUALITY SYMBOLS



NEW RELEASED
EC NO: KOR2011-0057
DRWN:CBCHIN 2010/12/02
CHKD:SH. CHU 2010/12/02
APPR:YUNSIKIM 2010/12/02