

# Type 5ST / 5STP

## Time - lag Fuse Series (Low Breaking Capacity)

HF  5ST/5STP Series, 5x20mm Glass Tube Time - lag Fuse

RoHS 6 Compliant

### Description

5x20mm Time lag, low breaking capacity, glass tube body cartridge fuse designed, approved and complied with IEC 60127-2, standard sheet 3.

### Features

- Meet IEC standard 60127-2, sheet 3
- Wide operating temperature range
- Bulk and Tape & Reel packing available
- RoHS 6 compliant
- Halogen Free
- Leadfree

### Applications


Provide individual protection for components or internal circuits.

- Power supplies
- Battery charger
- Monitor
- Adapter

LEAD FREE =   
HALOGEN FREE = 

### Physical Specifications

|           |                                                                                                                                                                                                                                                                                                                                    |
|-----------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Materials | Body : Glass                                                                                                                                                                                                                                                                                                                       |
|           | Cap : Nickel Plated Brass Caps                                                                                                                                                                                                                                                                                                     |
|           | Leads : Matte Tin Plated Copper                                                                                                                                                                                                                                                                                                    |
| Marking   | On Fuse :                                                                                                                                                                                                                                                                                                                          |
|           | "bel", "T", "Current Rating", "L", "250V",                                                                                                                                                                                                                                                                                         |
|           | "Appropriate Safety Logos", "  (RoHS 6 compliant)                                                                                                                                                                                             |
|           | On Label :                                                                                                                                                                                                                                                                                                                         |
|           | "bel", "5ST" or "5STP", "Current Rating", "Voltage Rating", "Interrupting Rating",<br>" Appropriate Safety Logos" and "  ", "  " (China RoHS compliant). |




### Electrical Characteristics(IEC-127-2 STANDARD SHEET 3)

| Rated Current  | 1.5 In |      | 2.1 In |     | 2.75 In |     | 4 In |     | 10 In |     |
|----------------|--------|------|--------|-----|---------|-----|------|-----|-------|-----|
|                | MIN    | MAX  | MIN    | MAX | MIN     | MAX | MIN  | MAX | MIN   | MAX |
| 63mA to 100mA  | 1      | 2    | 200    | 10  | 40      | 3   | 10   | 300 |       |     |
| 125mA to 12.5A | 1      | 2    | 600    | 10  | 150     | 3   | 20   | 300 |       |     |
|                | hr.    | min. | ms     | sec | ms      | sec | ms   | ms  |       |     |

In clause 9.2, the test voltage for 5STP ratings from 63mA to 6.3A is 63VDC.

### Safety Agency Approvals

| SAFETY AGENCY                                                                         | SAFETY AGENCY CERTIFICATE NUMBER | VOLTAGE RATING (V)   | AMPERE RANGE / VOLT @ I.R. ABILITY*                       |
|---------------------------------------------------------------------------------------|----------------------------------|----------------------|-----------------------------------------------------------|
|  | 1021774                          | 63mA - 10A / 250V AC | 63mA - 6.3A / 250V AC @ 35A or 10 In whichever is greater |
|  | 40000507                         |                      |                                                           |
|  | EM231                            |                      | 63mA - 10A / 250V AC @ 35A or 10 In whichever is greater  |
|  | E20624                           |                      |                                                           |
|  | LR39772                          |                      | 63mA - 6.3A / 250V AC @ 35A or 10 In whichever is greater |
|  | 2003010207030316                 |                      |                                                           |

\* I.R. = INTERRUPTING RATING = SHORT CIRCUIT RATING (AMPS)

Specifications subject to change without notice



**bel**

POWER  
SOLUTIONS &  
PROTECTION

a bel group

Bel Fuse Inc.  
206 Van Vorst Street  
Jersey City, NJ 07302 USA

+1 201.432.0463  
techhelp@belf.com  
[belfuse.com](http://belfuse.com)



# Type 5ST / 5STP

## Time - lag Fuse Series (Low Breaking Capacity)

HF  5ST/5STP Series, 5x20mm Glass Tube Time - lag Fuse

RoHS 6 Compliant

### Environmental Specifications

|                           |                                                                                                  |
|---------------------------|--------------------------------------------------------------------------------------------------|
| Shock Resistance          | MIL-STD-202G, Method 213B, Test Condition 1 (100 G's peak for 6 milliseconds; Sawtooth waveform) |
| Vibration Resistance      | MIL-STD-202G, Method 201A(10-55 Hz, 0.06 inch, total excursion).                                 |
| Salt Spray Resistance     | MIL-STD-202G, Method 101E, Test Condition B(48 hrs).                                             |
| Insulation Resistance     | MIL-STD-202G, Method 302, Test Condition B (After Opening) 100, 000 ohms minimum.                |
| Solderability             | MIL-STD-202G, Method 208H                                                                        |
| Resistance to solder Heat | MIL-STD-202G, Method 210F, Test Condition B.(260+/-5 °C,10+/-1 sec)                              |
| Thermal Shock             | MIL-STD-202G, Method 107G, Test Condition B (-65 °C to +125 °C).                                 |
| Operating Temperature     | -55 °C to +125 °C                                                                                |
| Terminal Strength         | IEC-68-2-21                                                                                      |

### Electrical Specifications

| Catalog Number | Ampere Rating | Typical Cold Resistance (ohm) | Volt-drop @100% In (Volt) max. | Voltage and Interrupting Ratings                                                        | Melting I <sup>2</sup> T <10 mSec (A <sup>2</sup> Sec) | Melting I <sup>2</sup> T @10 In (A <sup>2</sup> Sec) | Maximum Power Dissipation (W) | Agency Approvals                                                                      |                                                                                       |                                                                                       |                                                                                       |                                                                                       |                                                                                       |
|----------------|---------------|-------------------------------|--------------------------------|-----------------------------------------------------------------------------------------|--------------------------------------------------------|------------------------------------------------------|-------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                |               |                               |                                |                                                                                         |                                                        |                                                      |                               |  |  |  |  |  |  |
| 5ST(P) 63-R    | 63mA          | 19.5                          | 1.90                           | See Table of Safety Approvals on Page 1 for Voltage and associated Interrupting Ratings | 0.008                                                  | 0.021                                                | 0.28                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 80-R    | 80mA          | 13.2                          | 1.68                           |                                                                                         | 0.015                                                  | 0.036                                                | 0.29                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 100-R   | 100mA         | 11.0                          | 1.63                           |                                                                                         | 0.03                                                   | 0.06                                                 | 0.30                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 125-R   | 125mA         | 7.02                          | 1.29                           |                                                                                         | 0.05                                                   | 0.11                                                 | 0.30                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 160-R   | 160mA         | 4.10                          | 0.92                           |                                                                                         | 0.08                                                   | 0.19                                                 | 0.31                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 200-R   | 200mA         | 2.60                          | 0.77                           |                                                                                         | 0.15                                                   | 0.33                                                 | 0.32                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 250-R   | 250mA         | 1.70                          | 0.64                           |                                                                                         | 0.26                                                   | 0.58                                                 | 0.32                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 315-R   | 315mA         | 1.30                          | 0.57                           |                                                                                         | 0.46                                                   | 1.01                                                 | 0.33                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 400-R   | 400mA         | 0.72                          | 0.41                           |                                                                                         | 0.81                                                   | 1.76                                                 | 0.34                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 500-R   | 500mA         | 0.57                          | 0.47                           |                                                                                         | 1.4                                                    | 3.1                                                  | 0.34                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 630-R   | 630mA         | 0.18                          | 0.14                           |                                                                                         | 0.9                                                    | 1.5                                                  | 0.18                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 800-R   | 800mA         | 0.14                          | 0.14                           |                                                                                         | 1.6                                                    | 2.5                                                  | 0.20                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 1-R     | 1A            | 0.10                          | 0.13                           |                                                                                         | 2.4                                                    | 3.3                                                  | 0.17                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 1.25-R  | 1.25A         | 0.052                         | 0.08                           |                                                                                         | 4.1                                                    | 5.5                                                  | 0.19                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 1.6-R   | 1.6A          | 0.036                         | 0.08                           |                                                                                         | 6.9                                                    | 8.9                                                  | 0.23                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 2-R     | 2A            | 0.028                         | 0.08                           |                                                                                         | 12                                                     | 15                                                   | 0.26                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 2.5-R   | 2.5A          | 0.023                         | 0.08                           |                                                                                         | 20                                                     | 24                                                   | 0.31                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 3.15-R  | 3.15A         | 0.017                         | 0.08                           |                                                                                         | 33                                                     | 39                                                   | 0.36                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 4-R     | 4A            | 0.013                         | 0.07                           |                                                                                         | 56                                                     | 64                                                   | 0.42                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 5-R     | 5A            | 0.0096                        | 0.07                           |                                                                                         | 95                                                     | 105                                                  | 0.49                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 6.3-R   | 6.3A          | 0.0073                        | 0.07                           |                                                                                         | 160                                                    | 173                                                  | 0.57                          | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     | Y                                                                                     |
| 5ST(P) 8-R     | 8A            | 0.0062                        | 0.07                           |                                                                                         | 260                                                    | 282                                                  | 0.80                          | Y                                                                                     | Y                                                                                     |                                                                                       |                                                                                       |                                                                                       |                                                                                       |
| 5ST(P) 10-R    | 10A           | 0.0052                        | 0.07                           |                                                                                         | 439                                                    | 461                                                  | 1.00                          | Y                                                                                     | Y                                                                                     |                                                                                       |                                                                                       |                                                                                       |                                                                                       |
| 5ST(P) 12.5-R  | 12.5A         | 0.0041                        | 0.07                           |                                                                                         | 490                                                    | 679                                                  | 1.70                          |                                                                                       |                                                                                       |                                                                                       |                                                                                       |                                                                                       |                                                                                       |

Consult manufacturer for other ratings

Specifications subject to change without notice



Bel Fuse Inc.  
206 Van Vorst Street  
Jersey City, NJ 07302 USA

+1 201.432.0463  
techhelp@belf.com  
[belfuse.com](http://belfuse.com)




# Type 5ST / 5STP

## Time - lag Fuse Series (Low Breaking Capacity)


HF  5ST/5STP Series, 5x20mm Glass Tube Time - lag Fuse

RoHS 6 Compliant

### Average Time Current Curve




### Temperature Derating Curve



### Soldering Parameters

| Lead-free Wave Soldering Profile                     |                                                |
|------------------------------------------------------|------------------------------------------------|
| Wave Soldering Parameter                             |                                                |
| Average ramp-up rate                                 | 200 °C / second                                |
| Heating rate during preheat                          | typical 1 - 2 °C / second<br>Max 4 °C / second |
| Final preheat temperature                            | within 125 °C of soldering temperature         |
| Peak temperature Tp                                  | 260 °C                                         |
| Time within +0 °C / -5 °C of actual peak temperature | 10 seconds                                     |
| Ramp-down rate                                       | 5 °C / second max.                             |



Specifications subject to change without notice



**bel**

a bel group

**POWER  
SOLUTIONS &  
PROTECTION**

Bel Fuse Inc.  
206 Van Vorst Street  
Jersey City, NJ 07302 USA

+1 201.432.0463  
techhelp@belf.com  
[belfuse.com](http://belfuse.com)



# Type 5ST / 5STP

## Time - lag Fuse Series (Low Breaking Capacity)


HF  5ST/5STP Series, 5x20mm Glass Tube Time - lag Fuse

RoHS 6 Compliant

### Fuse FGNO Explanation 06XX X [XXXX] X XX, [XXXX]=Ampere Rating


| Fraction | Decimal | Milliamps | Bel FGNO[XXXX] | Fraction | Decimal | Amps | Bel FGNO[XXXX] |
|----------|---------|-----------|----------------|----------|---------|------|----------------|
| 1/32     | 0.032   | 32        | 0032           | 1.0      | 1.0     | 1    | 1000           |
| 1/25     | .040    | 40        | 0040           | 1-1/4    | 1.25    | 1.25 | 1250           |
| 1/20     | .050    | 50        | 0050           | 1-1/2    | 1.50    | 1.5  | 1500           |
| 1/16     | .063    | 63        | 0063           |          | 1.60    | 1.6  | 1600           |
| 8/100    | .080    | 80        | 0080           |          | 2.0     | 2    | 2000           |
| 1/10     | .100    | 100       | 0100           | 2-1/4    | 2.25    | 2.25 | 2250           |
| 1/8      | .125    | 125       | 0125           | 2-1/2    | 2.5     | 2.5  | 2500           |
| 15/100   | .150    | 150       | 0150           |          | 3.0     | 3    | 3000           |
|          | .160    | 160       | 0160           |          | 3.15    | 3.15 | 3150           |
| 2/10     | .200    | 200       | 0200           | 3-1/2    | 3.5     | 3.5  | 3500           |
| 1/4      | .250    | 250       | 0250           |          | 4.0     | 4    | 4000           |
| 3/10     | .300    | 300       | 0300           |          | 5.0     | 5    | 5000           |
|          | .315    | 315       | 0315           |          | 6.0     | 6    | 6000           |
| 3/8      | .375    | 375       | 0375           |          | 6.3     | 6.3  | 6300           |
| 4/10     | .400    | 400       | 0400           |          | 7.0     | 7    | 7000           |
| 1/2      | .500    | 500       | 0500           | 7-1/2    | 7.5     | 7.5  | 7500           |
| 6/10     | .600    | 600       | 0600           |          | 8.0     | 8    | 8000           |
|          | .630    | 630       | 0630           |          |         | 10   | 9100           |
| 7/10     | .700    | 700       | 0700           |          |         | 12   | 9120           |
| 3/4      | .750    | 750       | 0750           |          |         | 15   | 9150           |
| 8/10     | .800    | 800       | 0800           |          |         | 20   | 9200           |
|          |         |           |                |          |         | 25   | 9250           |
|          |         |           |                |          |         | 30   | 9300           |

### Mechanical Dimensions



\*Ratings 6.3A and less have 0.032" diameter lead  
\*Ratings 8A and above have 0.040" diameter lead

### Ordering Information



### Packaging

| Packaging Option         | Packaging Specification | Quantity | Packaging Code | Inside Tape Spacing |
|--------------------------|-------------------------|----------|----------------|---------------------|
| Bulk                     | N/A                     | 1000     | 11             | N/A                 |
| Bulk ( Pigtail Type )    | N/A                     | 1000     | 13             | N/A                 |
| Tape & Reel, 10 mm Pitch | EIA-296-F               | 1500     | 16             | 63                  |

Specifications subject to change without notice



Bel Fuse Inc.  
206 Van Vorst Street  
Jersey City, NJ 07302 USA

+1 201.432.0463  
techhelp@belf.com  
[belfuse.com](http://belfuse.com)