



PRODUCT NUMBER
65039-YXX(E)LF

DESIGN CODE _____
0 = STANDARD
2 = OPTIONAL RIB
SEE SHEET 2

PIN STYLE _____
SEE SHEET 2


INDICATES THE PRODUCT IS RoHS
COMPLIANT, SEE NOTE 6

65039-YXXLF OR 65039-YXXELF ARE
EXACTLY THE SAME PRODUCTS.
EXTENSION "E" JUST FOR OLD EUROPEAN
DESIGN AND MANUFACTURING SITE




NOTES:

- MOLDING MATERIAL : MODIFIED POLYPHELYNENE
COLOR BLACK, UL 94 V0
- LATCH MUST WITHSTAND 18N MIN PULL OUT FORCE
- STANDARD PACKAGING IN POLYBAGS
- TERMINALS MUST BE CRIMPED PROPERLY FOR
SATISFACTORY LATCHING :
 - FOR CRIMPING INSTRUCTIONS, SEE TA-75 AND TA-295
 - FOR TERMINAL APPLICATION SEE TA-531.PRODUCT SPECIFICATION: BUS-12-067.
- THIS HOUSING IS INTENDED FOR USE WITH
MINI PV TERMINAL WITH 22-36 GAUGE WIRE
- RoHS COMPLIANT PRODUCT SPECIFICATIONS :
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS
DESCRIBED IN GS-22-008.
 - THE PRODUCT IS NOT INTENDED TO BE EXPOSED
TO A MANUFACTURING SOLDER PROCESS.



mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family BERCONN
ltr	ecn	no	dr	date	tolerances unless otherwise specified	mm	title
BE	V07-0483	HTB		07.07.24	.X ±0.3		MINI LATCH SR
BF	F12-0064	LMU		12.06.08	.xx ±0.13		POLARIZED HSG 2.54mm
BG	B-14321	LMU		13.03.21	.xxx ±0.05	scale 5:1	
BH	B-18693	LMU		14.08.29	dr L.MULIN 12.06.08	FCJ	dwg no
BJ	B-20324	AMA		15.02.27	engr L.MULIN 12.06.08		sheet 1 of 2
					chr		size
					appd JCO 12.06.08		65039 A3
sheet index	revision sheet	BJ	BH				type CUSTOMER Drawing

PIN STYLE	No. OF POS.	DIM J	DIM K
36	1x01	N/A	2.39
35	1x02	2.54	4.93
34	1x03	5.08	7.47
33	1x04	7.62	10.01
32	1x05	10.16	12.55
31	1x06	12.70	15.09
30	1x07	15.24	17.63
29	1x08	17.78	20.17
28	1x09	20.32	22.71
27	1x10	22.86	25.25
26	1x11	25.40	27.79
25	1x12	27.94	30.33
24	1x13	30.48	32.87
23	1x14	33.02	35.41
22	1x15	35.56	37.95
21	1x16	38.10	40.49
20	1x17	40.64	43.03
19	1x18	43.18	45.57
18	1x19	45.72	48.11
17	1x20	48.26	50.65
16	1x21	50.80	53.19
15	1x22	53.34	55.73
14	1x23	55.88	58.27
13	1x24	58.42	60.81
12	1x25	60.96	63.35
11	1x26	63.50	65.89
10	1x27	66.04	68.43
09	1x28	68.58	70.97
08	1x29	71.12	73.51
07	1x30	73.66	76.05
06	1x31	76.20	78.59
05	1x32	78.74	81.13
04	1x33	81.28	83.67
03	1x34	83.82	86.21
02	1x35	86.36	88.75
01	1x36	88.90	91.29



mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		BERCONN
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
BE	V07-0483	HTB		07.07.24			MINI LATCH SR
BF	F12-0064	LMU		12.06.08	linear	mm	POLARIZED HSG 2.54mm
BG	B-18693	LMU		14.08.29		scale 5:1	
BH	B-20324	AMA		15.02.27	dr	L.MULIN	12.06.08
					engr	L.MULIN	12.06.08
					chr		
					appd	JCO	12.06.08
sheet index	revision sheet						



dwg no 65039 sheet 2 of size A3
type CUSTOMER Drawing