

4

3

2

1

HARNESS PRO SERIES H205 MALE						
Contacts number nn	Length without Latches in mm		Contacts reference mark number			
	A	C	D	E	F	G
04	2	7.4	1	2	3	4
06	4	9.4	1	3	4	6
08	6	11.4	1	4	5	8
10	8	13.4	1	5	6	10
12	10	15.4	1	6	7	12
14	12	17.4	1	7	8	14
16	14	19.4	1	8	9	16
18	16	21.4	1	9	10	18
20	18	23.4	1	10	11	20
22	20	25.4	1	11	12	22
24	22	27.4	1	12	13	24
26	24	29.4	1	13	14	26
28	26	31.4	1	14	15	28
30	28	33.4	1	15	16	30
32	30	35.4	1	16	17	32
34	32	37.4	1	17	18	34
36	34	39.4	1	18	19	36
38	36	41.4	1	19	20	38
40	38	43.4	1	20	21	40
42	40	45.4	1	21	22	42
44	42	47.4	1	22	23	44
46	44	49.4	1	23	24	46
48	46	51.4	1	24	25	48
50	48	53.4	1	25	26	50

CABLE COLOR
Black : 0 / Brown : 1
Red : 2 / Orange : 3
Yellow : 4 / Green : 5
Blue : 6 / Violet : 7
Gray : 8 / White : 9

Contacts number
H 2 0 5 S n n D 6 A 5 0 0


« L » = latch with locking
« » = without latch

AWG
24 : E
26 : D
28 : C

NORM
A : MIL-W-22759/11
B : « »

Ce plan est la propriété exclusive de la société NICOMATIC.
Il ne peut être reproduit sans son autorisation. Loi du 11.03.1902.

This document and drawings, sketches, and schematic drawings are the property of the NICOMATIC company, and no parts thereof may be reproduced and used without the written consent of the owner.
Law dated 11.03.1902



WIRES SPECIFICATION
MIL-W-22759/11
AWG26 Blue
Standing : 19 x 38
Finished Ø : 1.02mm max.(0.04 inch)
Conductor : Silver coated copper
Insulation : Extruded PTFE
Temperature Rating : 200°C
Voltage Rating : 600V

TECHNICAL FEATURES

MATERIALS

INSULATOR : Glass filled thermoplastic UL 94-V0

CRIMPING SIGNAL CONTACTS :

Male : Brass / 0.3µ gold plated

FIXING HARDWARE :

Latch : Beryllium copper / Ni 2µ nickel plated

ELECTRICAL


- All contacts: 3 A max. @ 25°C, 2.2 A max. @ 85°C
- Working / Rated voltage (sea level): 300V AC/DC
- Proof / Withstanding voltage: 400V AC/DC
- Contact resistance (initial): max. 20 mΩ
- Contact resistance (after conditioning): max. 25 mΩ
- Insulation resistance (initial): 1000 MΩ min

MECHANICAL

- Mechanical operations: 500 cycles.
- Contact insertion and withdrawal force: 2N max. / 0.2 N min.
- Contact retention in insulator: 10N min.

ENVIRONMENTAL

- Temperature range: From -55°C to +125°C, Peak Reflow Compatible 260°C
- RoHS: Yes




3D example with P/N H205S20LD6A500

Latch separation tool P/N C14790



173, rue des fougères
Z.I. Les Bracots
F-74890 Bons-en-Chablais
Tel. : +33 (0)4.50.36.13.85
Fax : +33 (0)4.50.36.11.33
Web : www.nicomatic.com



Echelle/Scale
3:1

a	19/05/08	H.T.		D.Z.
Ind	Date	Drawn	Checked	Approved

Désignation : Harness CMM200 Pro series
Male AWG26 Blue 500mm

H205Snn(L)D6A500_cl

Réf. catalogue /
Catalogue Reference H205Snn(L)D6A500

Tolérance générale /
General tolerance ±0.2

Page 1/1 A4

4

3

2

1