

**Maximum Ratings**

| Symbol          | Conditions                                  | Values       | Units |
|-----------------|---------------------------------------------|--------------|-------|
| $V_{CEV_{sus}}$ | $I_C = 1\text{ A}$ , $V_{BE} = -2\text{ V}$ | 1000         | V     |
| $V_{CEV}$       | $V_{BE} = -2\text{ V}$                      | 1000         | V     |
| $V_{CBO}$       | $I_E = 0$                                   | 1000         | V     |
| $V_{EBO}$       | $I_C = 0$                                   | 7            | V     |
| $I_C$           | D. C.                                       | 100          | A     |
| $I_{CM}$        | $t_p = 1\text{ ms}$                         | 200          | A     |
| $I_F = -I_C$    |                                             | 100          | A     |
| $I_B$           |                                             | 5            | A     |
| $P_{tot}$       | $T_{case} = 25\text{ °C}$ ; per darlington  | 800          | W     |
| $T_{vj}$        |                                             | -40 ... +150 | °C    |
| $T_{stg}$       |                                             | -40 ... +125 | °C    |
| $V_{isol}$      | a. c. 50 Hz, r.m.s.                         | 2500~        | V     |

**Thermal Characteristics**

|            |                           |             |      |
|------------|---------------------------|-------------|------|
| $R_{thjc}$ | per darlington/per module | 0,155/0,077 | °C/W |
| $R_{thjc}$ | per diode/per module      | 0,65/0,325  | °C/W |
| $R_{thch}$ | per 1/2 module/per module | 0,075/0,038 | °C/W |

**Electrical Characteristics<sup>1)</sup>**

|                  |                                             | min.                    | typ. | max. |    |
|------------------|---------------------------------------------|-------------------------|------|------|----|
| $I_{CEV}$        | $V_{CE} = V_{CEV}$ , $V_{BE} = -2\text{ V}$ |                         |      | 2    | mA |
| $I_{EBO}$        | $I_C = 0$ , $V_{BE} = -7\text{ V}$          |                         |      | 400  | mA |
| $V_{CEsat}^{2)}$ | $I_C = 100\text{ A}$ , $I_B = 2\text{ A}$   |                         |      | 2,5  | V  |
| $V_{BEsat}^{2)}$ | $I_C = 100\text{ A}$ , $I_B = 2\text{ A}$   |                         |      | 3,5  | V  |
| $h_{21E}^{2)}$   | $I_C = 100\text{ A}$                        | $V_{CE} = 2,8\text{ V}$ |      | 75   |    |
|                  |                                             | $V_{CE} = 5\text{ V}$   |      | 100  |    |

**Switching Characteristics for Resistive Load<sup>1)</sup>**




|          |                                                                                    |  |    |    |
|----------|------------------------------------------------------------------------------------|--|----|----|
| $t_{on}$ | $I_C = 100\text{ A}$<br>$I_{B1} = -I_{B2} = 2\text{ A}$<br>$V_{CC} = 600\text{ V}$ |  | 3  | μs |
| $t_s$    |                                                                                    |  | 15 | μs |
| $t_f$    |                                                                                    |  | 3  | μs |

**Inverse Diode Characteristics<sup>1)</sup>**

|                     |                                                                                                                                                    |      |     |    |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|------|-----|----|
| $V_F = -V_{CE}$     | $I_F = -I_C = 100\text{ A}$                                                                                                                        |      | 1,8 | V  |
| $I_{FSM} = -I_{Cp}$ | $\sin 180^\circ$ , 10 ms                                                                                                                           | 1000 |     | A  |
| $I_{RM}$            | $I_F = -I_C = 100\text{ A}$ , $-di_F/dt = 100\text{ A/μs}$<br>$V_{BE} = -3\text{ V}$ , $V_R = V_{CE} = 400\text{ V}$ ,<br>$T_{vj} = 125\text{ °C}$ |      | 38  | A  |
| $Q_{rr}$            |                                                                                                                                                    |      | 19  | μC |

**Mechanical Data**

|       |                      |          |      |    |         |
|-------|----------------------|----------|------|----|---------|
| $M_1$ | Case to heatsink     | SI units | 3    | 6  | Nm      |
|       |                      | US units | 27   | 53 | lb. in. |
| $M_2$ | Busbars to terminals | SI units | 2,5  | 5  | Nm      |
|       |                      | US units | 22   | 44 | lb. in. |
| w     |                      |          | 420  |    | g       |
| Case  | DB                   |          | D 14 |    |         |
|       | DAL                  |          | D 39 |    |         |

**SEMITRANS® 3 NPN**  
**Power Darlington Modules**  
**100 A, 1000 V**
**SK 100 DB 100 D**  
**SK 100 DAL 100 D**
**DB****DAL****Features**

- Isolated baseplate (ease of mounting of one or several modules on one heatsink)
- All electrical connections on top (ease of interconnecting of modules with busbars)
- Large clearances and creepage distances
- Parallel connected fast recovery inverse diode
- UL recognized, file no. 63 532

**Typical Applications**

- Uninterruptible power supplies (UPS)
- DC drives
- AC motor controls
- Brake choppers (DAL)

<sup>1)</sup>  $T_{case} = 25\text{ °C}$  unless otherwise stated

<sup>2)</sup>  $t_p \leq 300\text{ μs}$ ,  $D \leq 1,5\%$

SEMIKRON INC

T-33-35




Fig. 1 Forward biased safe operating area (FBSOA)




Fig. 2 Shifting the limits of the FBSOA with temperature




Fig. 3 Reverse biased safe operating area (RBSOA)




Fig. 4 Forward current transfer ratio vs. coll. current




Fig. 5 Base current/voltage characteristic




Fig. 6 Collector-emitter voltage vs. base current




Fig. 7 Saturation voltages vs. collector current




Fig. 8 Switching times vs. collector current




Fig. 9 Collector current/voltage characteristics




Fig. 10 Turn-off times vs. negative base current




Fig. 11 Inverse diode forward characteristics





Fig. 12 Transient thermal impedance vs. time

**SK 100 DB 100 D**

Case D 14

SEMITRANS® 3

UL recognized, file no. 63 532



Dimensions in mm

**SK 100 DAL 100 D**

Case D 39

SEMITRANS® 3

UL recognized, file no. 63 532

