


- All the data listed in this catalogue are for reference only,TAI-TECH reserves the right to alter or revise the specifications without prior notification.

■ FCI 2520 Series

Part Number	Thickness C size (mm)	Inductance (uH)	Q min.	Test Frequency (MHz)	SRF (MHz) min.	DC Resistance (ohm) max.	Rated Current (mA)
FCI2520-R10□	1.6±0.3	0.10	30	25.2	680	0.21	450
FCI2520-R12□	1.6±0.3	0.12	30	25.2	650	0.22	400
FCI2520-R15□	1.6±0.3	0.15	30	25.2	530	0.25	400
FCI2520-R18□	1.6±0.3	0.18	30	25.2	520	0.29	370
FCI2520-R22□	1.6±0.3	0.22	30	25.2	390	0.30	370
FCI2520-R27□	1.6±0.3	0.27	30	25.2	330	0.33	350
FCI2520-R33□	1.6±0.3	0.33	30	25.2	310	0.39	350
FCI2520-R39□	1.6±0.3	0.39	30	25.2	290	0.40	320
FCI2520-R47□	1.6±0.3	0.47	30	25.2	240	0.44	300
FCI2520-R56□	1.6±0.3	0.56	30	25.2	210	0.49	250
FCI2520-R68□	1.6±0.3	0.68	30	25.2	180	0.52	250
FCI2520-R82□	1.6±0.3	0.82	30	25.2	155	0.61	200
FCI2520-1R0□	1.6±0.3	1.0	30	7.96	140	0.75	150
FCI2520-1R2□	1.6±0.3	1.2	30	7.96	135	0.87	120
FCI2520-1R5□	1.6±0.3	1.5	30	7.96	130	1.00	110
FCI2520-1R8□	1.6±0.3	1.8	30	7.96	120	1.10	100
FCI2520-2R2□	1.6±0.3	2.2	30	7.96	105	1.30	100
FCI2520-2R7□	1.6±0.3	2.7	30	7.96	90	1.40	100
FCI2520-3R3□	1.6±0.3	3.3	30	7.96	80	1.60	80
FCI2520-3R9□	1.6±0.3	3.9	30	7.96	75	1.70	80
FCI2520-4R7□	1.6±0.3	4.7	30	7.96	65	1.90	80
FCI2520-5R6□	1.6±0.3	5.6	30	7.96	60	2.20	80
FCI2520-6R8□	1.6±0.3	6.8	30	7.96	55	2.40	70
FCI2520-8R2□	1.6±0.3	8.2	30	7.96	50	2.60	50
FCI2520-100□	1.6±0.3	10.0	25	2.52	30	2.20	30
FCI2520-120□	1.6±0.3	12.0	25	2.52	27	2.50	20
FCI2520-150□	1.6±0.3	15.0	25	2.52	23	2.80	20
FCI2520-180□	1.6±0.3	18.0	25	2.52	22	3.20	20
FCI2520-220□	1.6±0.3	22.0	25	2.52	21	3.60	20
FCI2520-270□	1.6±0.3	27.0	25	2.52	19	4.30	15
FCI2520-330□	1.6±0.3	33.0	25	2.52	17	4.70	15

NOTE: □ : TOLERANCE J: +/-5% K: +/-10% L: +/-15% M: +/-20%.

■ Q-Frequency Characteristics



■ Inductance-Current Characteristics

