DATASHEET

6 PIN DIP RANDOM-PHASE TRIAC DRIVER PHOTOCOUPLER
EL301X, EL302X, EL305X Series



Schematic



Pin Configuration
1. Anode
2. Cathode
3. No Connection
4. Terminal
5. Substrate
   (do not connect)
6. Terminal

Features:

- Peak breakdown voltage
  - 250V: EL301X
  - 400V: EL302X
  - 600V: EL305X
- High isolation voltage between input and output (Viso=5000 V rms)
- Compact dual-in-line package
- Pb free and RoHS compliant.
- UL approved (No. E214129)
- VDE approved (No.132249)
- SEMKO approved
- NEMKO approved
- DEMKO approved
- FIMKO approved
- CSA approved

Description

The EL301X, EL302X and EL305X series of devices each consist of a GaAs infrared emitting diode optically coupled to a monolithic silicon random phase photo Triac.

They are designed for interfacing between electronic controls and power triacs to control resistive and inductive loads for 115 to 240 VAC operations.

Applications

- Solenoid/valve controls
- Lamp ballasts
- Static AC power switch
- Interfacing microprocessors to 115 to 240Vac peripherals
- Incandescent lamp dimmers
- Temperature controls
- Motor controls

Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No: DPC-0000059 Rev.5

LifecyclePhase: Approved
Expired Period: Forever

Absolute Maximum Ratings (Ta=25℃)

Parameter			Symbol	Rating	Unit
Input	Forward current		I_F	60	mA
	Reverse voltage		V_R	6	V
	Power dissipation		P_D	100	mW
	Derating factor (above T_a = 85℃)			3.8	mW /°C
Output	Off-state Output Terminal Voltage	EL301X	V_{DRM}	250	V
		EL302X		400	
		EL305X		600	
	Peak Repetitive Surge Current (pw=100μs,120pps)		I_{TSM}	1	A
	On-State RMS Current		$I_{T(RMS)}$	100	mA
	Power dissipation		P_C	300	mW
	Derating factor (above T_a = 85℃)			7.4	mW/°C
Total power dissipation			P_{TOT}	330	mW
Isolation voltage *1			V_{ISO}	5000	Vrms
Operating temperature			T_{OPR}	-55 to 100	°C
Storage temperature			T_{STG}	-55 to 125	°C
Soldering Temperature*2			T_{SOL}	260	°C

Notes:
*1 AC for 1 minute, R.H.= 40 ~ 60% R.H. In this test, pins 1, 2&3 are shorted together, and pins 4, 5 & 6 are shorted together.
*2 For 10 seconds

Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

LifecyclePhase: Approved
Expired Period: Forever

Electro-Optical Characteristics (Ta=25℃ unless specified otherwise)

Input

Parameter	Symbol	Min.	Typ.*	Max.	Unit	Condition
Forward Voltage	V_F	-	1.18	1.5	V	I_F = 10mA
Reverse Leakage current	I_R	-	-	10	μA	V_R = 6V

Output

Parameter		Symbol	Min.	Typ.*	Max.	Unit	Condition
Peak Blocking Current		I_{DRM}	-	-	100	nA	V_{DRM} = Rated V_{DRM}, I_F = 0mA
Peak On-state Voltage		V_{TM}	-	-	2.5	V	I_{TM}=100mA peak, I_F=Rated I_{FT}
Critical Rate of Rise off-state Voltage	EL301X EL302X	dv/dt	-	100	-	V/μs	V_{PEAK} =Rated V_{DRM}, I_F=0 (Fig. 8)
	EL305X		1000	-	-		V_{PEAK} =400V, I_F=0 (Fig. 8)

Transfer Characteristics

Parameter		Symbol	Min.	Typ.*	Max.	Unit	Condition
LED Trigger Current	EL3020	I_{FT}			30	mA	Main terminal Voltage=3V
	EL3010 EL3021 EL3051		-	-	15		
	EL3011 EL3022 EL3052		-	-	10		
	EL3012 EL3023 EL3053		-	-	5		
Holding Current		I_H	-	250	-	μA	

* Typical values at T_a = 25°C

Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

LifecyclePhase: Approved
Expired Period: Forever

Typical Electro-Optical Characteristics Curves

Figure 1. Forward Current vs Forward Voltage



Figure 2. On-State Characteristics



Figure 3. Holding Current vs. Ambient Temperature



Figure 4. LED Current Required to Trigger vs. LED Pulse Width



Figure 5. Leakage Current vs. Ambient Temperature



Figure 6. LED Trigger Current vs. Ambient Temperature



Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

LifecyclePhase: Approved
Expired Period: Forever



Figure 8. Static dv/dt Test Circuit & Waveform



Measurement Method

The high voltage pulse is set to the required V_{PEAK} value and applied to the D.U.T. output side through the RC circuit above. LED current is not applied. The waveform V_T is monitored using a x100 scope probe. By varying R_{TEST}, the dv/dt (slope) is increased, until the D.U.T. is observed to trigger (waveform collapses). The dv/dt is then decreased until the D.U.T. stops triggering. At this point, τ_{RC} is recorded and the dv/dt calculated.

$$dv/dt = \frac{0.632 \times V_{PEAK}}{\tau_{RC}}$$

For example, V_{PEAK} = 400V for EL302X series. The dv/dt value is calculated as follows:

$$dv/dt = \frac{0.63 \times 400}{\tau_{RC}} = \frac{252}{\tau_{RC}}$$

Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

LifecyclePhase: Approved
Expired Period: Forever

Order Information

Part Number

EL301XY(Z)-V
or **EL302XY(Z)-V**
or **EL305XY(Z)-V**

Note

X = Part No. for EL301x (0, 1 or 2)
X = Part No. for EL302x, EL305x (1, 2 or 3)
Y = Lead form option (S, S1, M or none)
Z = Tape and reel option (TA, TB or none).
V = VDE safety approved (optional)

Option	Description	Packing quantity
None	Standard DIP-6	65 units per tube
M	Wide lead bend (0.4 inch spacing)	65 units per tube
S (TA)	Surface mount lead form + TA tape & reel option	1000 units per reel
S (TB)	Surface mount lead form + TB tape & reel option	1000 units per reel
S1 (TA)	Surface mount lead form (low profile) + TA tape & reel option	1000 units per reel
S1 (TB)	Surface mount lead form (low profile) + TB tape & reel option	1000 units per reel

EVERLIGHT

Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

R
LifecyclePhase: Approved
Expired Period: Forever

Package Dimension (Dimensions in mm)

Standard DIP Type



Option M Type



Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

LifecyclePhase: Approved
Expired Period: Forever

Option S Type



Option S1 Type



EVERLIGHT

Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

LifecyclePhase: Approved
Expired Period: Forever

Recommended pad layout for surface mount leadform



Device Marking



Notes

EL	denotes EVERLIGHT
3053	denotes Device Number
Y	denotes 1 digit Year code
WW	denotes 2 digit Week code
V	denotes VDE (optional)

EVERLIGHT

Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

LifecyclePhase: Approved
Expired Period: Forever

Tape & Reel Packing Specifications

Option TA



Direction of feed from reel

Option TB



Direction of feed from reel

Tape dimensions



Dimension No.	A	B	Do	D1	E	F
Dimension (mm)	10.4±0.1	7.5±0.1	1.5±0.1	1.5+0.1/-0	1.75±0.1	7.5±0.1

Dimension No.	Po	P1	P2	t	W	K
Dimension (mm)	4.0±0.15	12±0.1	2.0±0.1	0.35±0.03	16.0±0.2	4.5±0.1

Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

LifecyclePhase: Approved
Expired Period: Forever

Precautions for Use

1. Soldering Condition

1.1 (A) Maximum Body Case Temperature Profile for evaluation of Reflow Profile



Note: Reference: IPC/JEDEC J-STD-020D

Preheat	
Temperature min (T_{smin})	150 °C
Temperature max (T_{smax})	200°C
Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds
Average ramp-up rate (T_{smax} to T_p)	3 °C/second max
Other	
Liquidus Temperature (T_L)	217 °C
Time above Liquidus Temperature (t_L)	60-100 sec
Peak Temperature (T_P)	260°C
Time within 5 °C of Actual Peak Temperature: T_P - 5°C	30 s
Ramp- Down Rate from Peak Temperature	6°C /second max.
Time 25°C to peak temperature	8 minutes max.
Reflow times	3 times

.

Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

LifecyclePhase: Approved
Expired Period: Forever

DISCLAIMER

1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.

EVERLIGHT

Copyright © 2010, Everlight All Rights Reserved. Release Date : May 13, 2013. Issue No:DPC-0000059 Rev.5

R
LifecyclePhase: Approved
Expired Period: Forever