


SPECIFICATIONS

Model Number: MC24S3H
Part Number: 032400

SHREV.A
September 7, 2010



Mechanical Drawing:



Motor (full speed):

Nominal Voltage	= 24 vdc
Operating Voltage Range	= 12 - 28 vdc
Nominal Running Current	= 0.280 amps
Locked Rotor Current	= 0.700 amps
Running Power	= 6.7 watts
Average Speed	= 3700 RPM
Bearings	=Ball Bearing
Air Flow	= 102 CFM
Acoustic	= 47.8 dBA

Construction:

Venturi: Lexan 500, Black, UL 94V-0

Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 50,000 hours at 40°C.

Additional Features:

Brushless DC Motor	
Electronic Locked Rotor Protected	
Polarity Protected	
Automatic Restart Capability	
Thermal Speed Control	
Operating Temperature:	-10°C to 70°C
Storage Temperature:	-40°C to 85°C
Thermal Speed Control	

Termination:

PTC on 24" zip cord
12" Lead wires, 22AWG, UL 1061
Red = Fan Power
Black = Fan Ground

Agency Approvals:

UL