








Sin nuestra expresa autorización, queda terminantemente prohibida la reproducción total o parcial de este documento, así como su uso indebido y/o su exhibición o comunicación a terceros. De los infractores se exigirá el correspondiente resarcimiento de daños y perjuicios. Se reserva todos los derechos para el caso de la concesión de patente de invención o el registro de Modelo Industrial.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts ist nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder GM-Eintragung vorbehalten.

Copying of this document, and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of a utility model or design.



- 1 FOR PLASTIC PARTS (POS. 1 AND 2):
 - LENGTHS: DIN 16901/130,
 - ANGLES, FORMS: DIN 7168-m, R,
 FOR METAL PARTS (POS. 3 AND 4): DIN 7168-m,
 FOR SCREWS (POS. 5 AND 6): DIN 7981 F-H.

P/N 9 contacts version: V42254-A6000-G*09

 TE Connectivity		Maßstab
Datum: 30.08.88 Bearb: De Petter Gepr: PD Com P&SE Norm:		D-Sub housing shielded 9 contacts
TOLERANCES UNLESS OTHERWISE SPECIFIED:		V42254-A6000-G***-*-27 customer drawing number: C 1393738-1
D ECO-12-017358 22JAN13 CWR C ECO-12-008266 28AUG12 CWR Zust: Mitteilung Datum: Name:	1	page 1+ of 6

Con questa espresión autolimitada queda formalmente prohibida la reproducción total o parcial de este documento, así como su uso indebido y/o su exhibición o comunicación a terceros. De los infractores se exigirá el correspondiente resarcimiento de daños y perjuicios. Se reserva todos los derechos para el caso de la concesión de patente de invención o el registro de Modelo Industrial.

Weitergabe sowie Verwertung dieses Unterlage, Verwertung und Mitteilung ihres Inhalts ist nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder G.M. Untertage vorbehalten.

Copying of this document and giving it to others and the use or communication of the contents thereof are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of a utility model or design.

A

B

C

D

E









F

A

B

C

D



housing		dimension									
P/N	No. of contacts	A	B	C	D	E	F	G	H	J	K
V42254-A6000-											
G × 15	15					28	39,62		R3	14,5	R4,5
G × 25	25	13	14	1	7,5	41,8	53,52	6,5	R4	16	R5,5
G × 37	37					58,25	69,8				
G × 50	50	16	17,5	1,5	9,5	55,78	67,41	9,5	R5,5	20,6	R7

2) only for the 37 contacts version

1) tape only for the 15 to 37 contacts versions
drawn is the 25 contacts version

				Maßstab	
				TE TE Connectivity	
				D-Sub housing	
				shielded 15 to 50 contacts	
				V42254-A6000-G***-27	
				customer drawing number: C 1393738-1	
				page 2+	
				of 6	

V 4 2 2 5 4 - A 6 0 0 * - G * * *

Housing type

G plastic housing, shielded

Marking and colour of the housing

1 TE-marking, grey

2 without marking, grey


3 TE-marking, black

4 without marking, black

	0	1	2	3	4	No. of contacts - housing size	
wire diameter	4-8	4-6	6-8		4-8	09	9 contact - housing size 1
	5-10	5-8	8-10		5-10	15	15 contacts - housing size 2
	5-11	5-8,5	8,5-1		5-11	25	25 contacts - housing size 3
	6-11	6-8	8-10	10-11	6-11	37	37 contacts - housing size 4
	9-14,5	9-12	12-14,5		9-14,5	50	50 contacts - housing size 5
Packaging	set 1)	200 2)	200 2)	200 2)	200 2)	1) per set, in blister - 9 and 15 contacts : 25 - 25, 37 and 50 contacts : 15 2) loose pieces, in cardboard : 200	



TE Connectivity



LOC DIMENSIONS
GW IN MM

SCALE

WEIGHT

MATERIAL

DATE 30.08.88

NAME De Petter

DEP. PD Com P&SE

EC

TOLERANCE UNLESS
SPECIFIED OTHERWISE

NAME

D-Sub Housing

shielded

DWG NO.

V42254-A6000-G****-*-27

SHT. 3+

D SEE SHEET 1

REV. CHANGE ORDER

DATE

APP.

customer drawing number: C 1393738-1

OF 6

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.

PROPRIETARY:

1	2	3	4																																																																		
A	Active part numbers. Contact Tyco Electronics for other configuration availability																																																																				
B	<table border="1" style="width:100%; border-collapse: collapse;"> <thead> <tr> <th style="width:50%;">Old Part Number</th> <th style="width:50%;">TE Part Number</th> </tr> </thead> <tbody> <tr><td>V42254-A6000-G109</td><td>1393738-1</td></tr> <tr><td>V42254-A6000-G115</td><td>1393738-2</td></tr> <tr><td>V42254-A6000-G125</td><td>1393738-3</td></tr> <tr><td>V42254-A6000-G137</td><td>1393738-4</td></tr> <tr><td>V42254-A6000-G150</td><td>1393738-5</td></tr> <tr><td>V42254-A6000-G209</td><td>1393738-6 OBSOLETE</td></tr> <tr><td>V42254-A6000-G309</td><td>1393738-7 OBSOLETE</td></tr> <tr><td>V42254-A6000-G315</td><td>1393738-8 OBSOLETE</td></tr> <tr><td>V42254-A6000-G325</td><td>1393738-9 SUPERSEDED BY 1393738-1</td></tr> <tr><td>V42254-A6001-G109</td><td>4-1393738-2 OBSOLETE</td></tr> <tr><td>V42254-A6001-G125</td><td>4-1393738-4 SUPERSEDED BY 6-1393738-1</td></tr> <tr><td>V42254-A6001-G309</td><td>4-1393738-5 SUPERSEDED BY 1-1393739-9</td></tr> <tr><td>V42254-A6001-G315</td><td>4-1393738-6 SUPERSEDED BY 6-1393738-7</td></tr> <tr><td>V42254-A6002-G109</td><td>5-1393738-0 OBSOLETE</td></tr> <tr><td>V42254-A6002-G125</td><td>5-1393738-2 SUPERSEDED BY 6-1393738-1</td></tr> <tr><td>V42254-A6003-G137</td><td>5-1393738-7 SUPERSEDED BY 6-1393738-2</td></tr> <tr><td>V42254-A6004-G109</td><td>5-1393738-9</td></tr> <tr><td>V42254-A6004-G115</td><td>6-1393738-0</td></tr> <tr><td>V42254-A6004-G125</td><td>6-1393738-1</td></tr> <tr><td>V42254-A6004-G137</td><td>6-1393738-2</td></tr> <tr><td>V42254-A6004-G150</td><td>6-1393738-3</td></tr> <tr><td>V42254-A6004-G209</td><td>6-1393738-4 SUPERSEDED BY 5-1393738-9</td></tr> <tr><td>V42254-A6004-G215</td><td>6-1393738-5 OBSOLETE</td></tr> <tr><td>V42254-A6004-G225</td><td>6-1393738-6 OBSOLETE</td></tr> <tr><td>V42254-A6004-G309</td><td>1-1393739-9 OBSOLETE</td></tr> <tr><td>V42254-A6004-G315</td><td>6-1393738-7 OBSOLETE</td></tr> <tr><td>V42254-A6004-G325</td><td>2-1393739-0 OBSOLETE</td></tr> <tr><td>V42254-A6004-G337</td><td>2-1393739-1 SUPERSEDED BY 6-1393738-2</td></tr> <tr><td>V42254-A6004-G350</td><td>2-1393739-2 SUPERSEDED BY 6-1393738-3</td></tr> <tr><td>V42254-A6004-G409</td><td>6-1393738-8 OBSOLETE</td></tr> <tr><td>V42254-A6004-G415</td><td>6-1393738-9 OBSOLETE</td></tr> <tr><td>V42254-A6004-G437</td><td>7-1393738-1 OBSOLETE</td></tr> </tbody> </table>			Old Part Number	TE Part Number	V42254-A6000-G109	1393738-1	V42254-A6000-G115	1393738-2	V42254-A6000-G125	1393738-3	V42254-A6000-G137	1393738-4	V42254-A6000-G150	1393738-5	V42254-A6000-G209	1393738-6 OBSOLETE	V42254-A6000-G309	1393738-7 OBSOLETE	V42254-A6000-G315	1393738-8 OBSOLETE	V42254-A6000-G325	1393738-9 SUPERSEDED BY 1393738-1	V42254-A6001-G109	4-1393738-2 OBSOLETE	V42254-A6001-G125	4-1393738-4 SUPERSEDED BY 6-1393738-1	V42254-A6001-G309	4-1393738-5 SUPERSEDED BY 1-1393739-9	V42254-A6001-G315	4-1393738-6 SUPERSEDED BY 6-1393738-7	V42254-A6002-G109	5-1393738-0 OBSOLETE	V42254-A6002-G125	5-1393738-2 SUPERSEDED BY 6-1393738-1	V42254-A6003-G137	5-1393738-7 SUPERSEDED BY 6-1393738-2	V42254-A6004-G109	5-1393738-9	V42254-A6004-G115	6-1393738-0	V42254-A6004-G125	6-1393738-1	V42254-A6004-G137	6-1393738-2	V42254-A6004-G150	6-1393738-3	V42254-A6004-G209	6-1393738-4 SUPERSEDED BY 5-1393738-9	V42254-A6004-G215	6-1393738-5 OBSOLETE	V42254-A6004-G225	6-1393738-6 OBSOLETE	V42254-A6004-G309	1-1393739-9 OBSOLETE	V42254-A6004-G315	6-1393738-7 OBSOLETE	V42254-A6004-G325	2-1393739-0 OBSOLETE	V42254-A6004-G337	2-1393739-1 SUPERSEDED BY 6-1393738-2	V42254-A6004-G350	2-1393739-2 SUPERSEDED BY 6-1393738-3	V42254-A6004-G409	6-1393738-8 OBSOLETE	V42254-A6004-G415	6-1393738-9 OBSOLETE	V42254-A6004-G437	7-1393738-1 OBSOLETE
Old Part Number	TE Part Number																																																																				
V42254-A6000-G109	1393738-1																																																																				
V42254-A6000-G115	1393738-2																																																																				
V42254-A6000-G125	1393738-3																																																																				
V42254-A6000-G137	1393738-4																																																																				
V42254-A6000-G150	1393738-5																																																																				
V42254-A6000-G209	1393738-6 OBSOLETE																																																																				
V42254-A6000-G309	1393738-7 OBSOLETE																																																																				
V42254-A6000-G315	1393738-8 OBSOLETE																																																																				
V42254-A6000-G325	1393738-9 SUPERSEDED BY 1393738-1																																																																				
V42254-A6001-G109	4-1393738-2 OBSOLETE																																																																				
V42254-A6001-G125	4-1393738-4 SUPERSEDED BY 6-1393738-1																																																																				
V42254-A6001-G309	4-1393738-5 SUPERSEDED BY 1-1393739-9																																																																				
V42254-A6001-G315	4-1393738-6 SUPERSEDED BY 6-1393738-7																																																																				
V42254-A6002-G109	5-1393738-0 OBSOLETE																																																																				
V42254-A6002-G125	5-1393738-2 SUPERSEDED BY 6-1393738-1																																																																				
V42254-A6003-G137	5-1393738-7 SUPERSEDED BY 6-1393738-2																																																																				
V42254-A6004-G109	5-1393738-9																																																																				
V42254-A6004-G115	6-1393738-0																																																																				
V42254-A6004-G125	6-1393738-1																																																																				
V42254-A6004-G137	6-1393738-2																																																																				
V42254-A6004-G150	6-1393738-3																																																																				
V42254-A6004-G209	6-1393738-4 SUPERSEDED BY 5-1393738-9																																																																				
V42254-A6004-G215	6-1393738-5 OBSOLETE																																																																				
V42254-A6004-G225	6-1393738-6 OBSOLETE																																																																				
V42254-A6004-G309	1-1393739-9 OBSOLETE																																																																				
V42254-A6004-G315	6-1393738-7 OBSOLETE																																																																				
V42254-A6004-G325	2-1393739-0 OBSOLETE																																																																				
V42254-A6004-G337	2-1393739-1 SUPERSEDED BY 6-1393738-2																																																																				
V42254-A6004-G350	2-1393739-2 SUPERSEDED BY 6-1393738-3																																																																				
V42254-A6004-G409	6-1393738-8 OBSOLETE																																																																				
V42254-A6004-G415	6-1393738-9 OBSOLETE																																																																				
V42254-A6004-G437	7-1393738-1 OBSOLETE																																																																				
C																																																																					
D																																																																					
E																																																																					
F	<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td colspan="2" style="text-align: center;"> TE Connectivity </td> <td style="text-align: center;"> LOC DIMENSIONS IN MM </td> <td style="text-align: center;">SCALE</td> <td style="text-align: center;">WEIGHT</td> </tr> <tr> <td colspan="2" style="text-align: center;"> LOC GW </td> <td colspan="3" style="text-align: center;">MATERIAL</td> </tr> <tr> <td style="width:10%;"></td> <td style="width:10%;"></td> <td style="width:10%;">DATE</td> <td colspan="2" style="width:70%;">NAME</td> </tr> <tr> <td></td> <td></td> <td>30.08.88</td> <td colspan="2" rowspan="3" style="text-align: center; vertical-align: middle;"> D-Sub Housing shielded </td> </tr> <tr> <td></td> <td></td> <td>NAME</td> </tr> <tr> <td></td> <td></td> <td>De Petter</td> </tr> <tr> <td></td> <td></td> <td>DEP.</td> <td colspan="2" rowspan="2" style="text-align: center; vertical-align: middle;"> EC </td> </tr> <tr> <td></td> <td></td> <td>PD Com P&SE</td> </tr> <tr> <td></td> <td></td> <td colspan="2" style="text-align: center;">TOLERANCE UNLESS SPECIFIED OTHERWISE</td> <td style="text-align: center;">DWG NO.</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td style="text-align: center;">SHT. 4+</td> </tr> <tr> <td></td> <td></td> <td></td> <td colspan="2" style="text-align: center;">V42254-A6000-G***-*-27</td> </tr> <tr> <td></td> <td></td> <td></td> <td colspan="2" style="text-align: center;">OF 6</td> </tr> <tr> <td></td> <td></td> <td></td> <td colspan="2" style="text-align: center;">Customer Drawing: C 1393738-1</td> </tr> </table>			TE Connectivity		 LOC DIMENSIONS IN MM	SCALE	WEIGHT	LOC GW		MATERIAL					DATE	NAME				30.08.88	D-Sub Housing shielded				NAME			De Petter			DEP.	EC				PD Com P&SE			TOLERANCE UNLESS SPECIFIED OTHERWISE		DWG NO.					SHT. 4+				V42254-A6000-G***-*-27					OF 6					Customer Drawing: C 1393738-1								
TE Connectivity		 LOC DIMENSIONS IN MM	SCALE	WEIGHT																																																																	
LOC GW		MATERIAL																																																																			
		DATE	NAME																																																																		
		30.08.88	D-Sub Housing shielded																																																																		
		NAME																																																																			
		De Petter																																																																			
		DEP.	EC																																																																		
		PD Com P&SE																																																																			
		TOLERANCE UNLESS SPECIFIED OTHERWISE		DWG NO.																																																																	
				SHT. 4+																																																																	
			V42254-A6000-G***-*-27																																																																		
			OF 6																																																																		
			Customer Drawing: C 1393738-1																																																																		

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.

PROPRIETARY:

V 4 2 2 5 4 - A 6 1 * * - L 1

Technical data		
	contact tube outer diameter ±0.1	for shield braiding outer diameter
04	4	2.0 to 2.7
05	5	2.8 to 3.7
06	6	3.8 to 4.7
07	7	4.8 to 5.7
08	8	5.8 to 6.7
09	9	6.8 to 7.7
10	10	7.8 to 8.7
11	11	8.8 to 9.7
12	12	9.8 to 10.7
13	13	10.8 to 11.7
14	14	11.8 to 12.7
15	15	12.8 to 13.7

Active part numbers. Contact
Tyco Electronics for
other configuration availability

Old Part Number	TE Part Number	
V42254-A6104-L1	3-1393561-2	OBSOLETE
V42254-A6105-L1	3-1393561-3	
V42254-A6106-L1	3-1393561-4	
V42254-A6107-L1	3-1393561-5	
V42254-A6108-L1	3-1393561-6	
V42254-A6109-L1	3-1393561-9	
V42254-A6110-L1	4-1393561-0	
V42254-A6111-L1	4-1393561-1	OBSOLETE
V42254-A6112-L1	4-1393561-2	
V42254-A6113-L1	4-1393561-3	OBSOLETE
V42254-A6114-L1	4-1393561-4	OBSOLETE
V42254-A6115-L1	5-1393502-9	OBSOLETE

APPLICABLE SPEC.:				FINISH					
 TE Connectivity				 DIMENSIONS IN MM		DIMENSIONS APPLY		PLATING	
						SCALE		WEIGHT	
 LOC GW				DATE 30.08.88		NAME			
						D-Sub Housing			
				NAME De Petter		accessories: contact tubes			
				DEP. PD Com P&SE		DWG NO.			
						V42254-A6000-G***-*-27			
				EC		SHT. 5+			
				TOLERANCE UNLESS SPECIFIED OTHERWISE					
D SEE SHEET 1									
REV. CHANGE ORDER		DATE		APP.		customer drawing number: C 1393738-1			
						OF 6			

V 4 2 2 5 4 - A 6 2 * * - L * * *

Technical Data			
		bushing inner diameter ±0.2	cable outer diameter
00	1) 2)	/	/
05	3)	5	4.2 to 4.9
06	3)	6	5.0 to 5.9
07	3)	7	6.0 to 6.9
08	3)	8	7.0 to 7.9
09	3)	9	8.0 to 8.9
10	2)	10	9.0 to 9.9
11	2)	11	10.0 to 10.9
12	4)	12	11.0 to 11.9
13	4)	13	12.0 to 12.9
14	4)	14	13.0 to 13.9
15	4)	15	14.0 to 14.9

	contacts	colour
1	9 to 37	grey
50	50	grey
100	9 to 37	black
150	50	black

Active part numbers. Contact Tyco Electronics for other configuration availability

Old Part Number	TE Part Number	
V42254-A6200-L 1	4-1393561-5	OBSOLETE
V42254-A6200-L 50	4-1393561-6	OBSOLETE
V42254-A6200-L100	5-1393502-1	OBSOLETE
V42254-A6200-L150	5-1393502-2	OBSOLETE
V42254-A6205-L 1	4-1393561-7	
V42254-A6205-L100	4-1393561-8	
V42254-A6206-L 1	4-1393561-9	
V42254-A6206-L100	5-1393561-0	
V42254-A6207-L 1	5-1393561-1	
V42254-A6207-L100	5-1393561-4	OBSOLETE
V42254-A6208-L 1	5-1393561-5	
V42254-A6208-L100	5-1393561-6	OBSOLETE
V42254-A6209-L 1	5-1393561-7	
V42254-A6209-L100	5-1393561-8	
V42254-A6210-L 1	5-1393561-9	
V42254-A6210-L 50	6-1393561-0	OBSOLETE
V42254-A6210-L100	6-1393561-1	OBSOLETE
V42254-A6210-L150	5-1393502-3	OBSOLETE
V42254-A6211-L 1	6-1393561-2	
V42254-A6211-L 50	6-1393561-3	OBSOLETE
V42254-A6211-L100	5-1393502-4	OBSOLETE
V42254-A6211-L150	5-1393502-5	OBSOLETE
V42254-A6212-L 50	6-1393561-4	OBSOLETE
V42254-A6212-L150	5-1393502-6	OBSOLETE
V42254-A6213-L 50	6-1393561-5	OBSOLETE
V42254-A6213-L150	5-1393502-7	OBSOLETE
V42254-A6214-L 50	6-1393561-6	OBSOLETE
V42254-A6214-L150	5-1393502-8	OBSOLETE
V42254-A6215-L 50	8-1393501-5	OBSOLETE
V42254-A6215-L150	6-1393561-7	OBSOLETE

- 4) only for 50 contacts
3) only for 9 to 37 contacts
2) for 9 to 50 contacts
1) Blank bushing

APPLICABLE SPEC.				FINISH			
 TE Connectivity				DIMENSIONS APPLY		PLATING	
				SCALE		WEIGHT	
 DIMENSIONS IN MM				MATERIAL			
DATE 30.08.88 NAME De Petter DEP. PD Com P&SE EC TOLERANCE UNLESS SPECIFIED OTHERWISE				NAME D-Sub Housing accessories: cable bushings			
D SEE SHEET 1 REV. CHANGE ORDER DATE APP.				DWG NO. V42254-A6000-G****-27 SHT. 6 OF 6			
customer drawing number: C 1393738-1							