

TOSHIBA CMOS Linear Integrated Circuit Silicon Monolithic

TC75S60F, TC75S60FU


Single Operational Amplifier

TC75S60F, TC75S60FU are CMOS operational amplifier with low supply voltage, low supply current.

Features


- High slew rate: $SR (V_{DD} = 3 \text{ V}) = 5.1 \text{ V}/\mu\text{s}$ (typ.)
- The power supply operation range is:
 $V_{DD} = \pm 0.9 \sim 3.5 \text{ V}$ or $1.8 \sim 7 \text{ V}$
- Low supply current: $I_{DD} (V_{DD} = 3 \text{ V}) = 330 \mu\text{A}$ (typ.)
- The internally phase compensated operational amplifier.
- Small package

TC75S60F



SSOP5-P-0.95

TC75S60FU



SSOP5-P-0.65A

Weight

SSOP5-P-0.95 : 0.014 g (typ.)

SSOP5-P-0.65A: 0.006 g (typ.)


Maximum Ratings ($T_a = 25^\circ\text{C}$)

Characteristics	Symbol	Rating	Unit
Supply voltage	V_{DD}, V_{SS}	7	V
Differential input voltage	DV_{IN}	± 7	V
Input voltage	V_{IN}	$V_{DD} \sim V_{SS}$	V
Power dissipation	P_D	200	mW
Operating temperature	T_{opr}	$-40 \sim 85$	$^\circ\text{C}$
Storage temperature	T_{stg}	$-55 \sim 150$	$^\circ\text{C}$


000707EBA1

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.

Marking (top view)



Pin Connection (top view)



Electrical Characteristics

DC Characteristics (V_{DD} = 3.0 V, V_{SS} = GND, Ta = 25°C)

Characteristics	Symbol	Test Circuit	Test Condition	Min	Typ.	Max	Unit
Input offset voltage	V _{IO}	1	R _S = 1 kΩ	—	2	7	mV
Input offset current	I _{IO}	—	—	—	1	—	pA
Input bias current	I _I	—	—	—	1	—	pA
Common mode input voltage	CMV _{IN}	2	—	0.0	—	2.1	V
Voltage gain (open loop)	G _V	—	—	60	70	—	dB
Maximum output voltage	V _{OH}	3	R _L = 100 kΩ	2.9	—	—	V
	V _{OL}	4	R _L = 100 kΩ	—	—	0.1	
Common mode rejection ratio	CMRR	2	V _{IN} = 0.0~2.1 V	60	70	—	dB
Supply voltage rejection ratio	SVRR	1	V _{DD} = 1.8~7.0 V	60	70	—	dB
Supply current	I _{DD}	5	—	—	330	500	μA
Source current	I _{source}	6	—	330	700	—	μA
Sink current	I _{sink}	7	—	600	1250	—	μA

DC Characteristics (V_{DD} = 1.8 V, V_{SS} = GND, Ta = 25°C)

Characteristics	Symbol	Test Circuit	Test Condition	Min	Typ.	Max	Unit
Input offset voltage	V _{IO}	1	R _S = 10 kΩ	—	2	7	mV
Input offset current	I _{IO}	—	—	—	1	—	pA
Input bias current	I _I	—	—	—	1	—	pA
Common mode input voltage	CMV _{IN}	2	—	0.3	—	0.9	V
Voltage gain (open loop)	G _V	—	—	—	70	—	dB
maximum output voltage	V _{OH}	3	R _L = 100 kΩ	1.7	—	—	V
	V _{OL}	4	R _L = 100 kΩ	—	—	0.1	
Common mode rejection ratio	CMRR	2	V _{IN} = 0.3~0.9 V	50	60	—	dB
Supply current	I _{DD}	5	—	—	300	450	μA
Source current	I _{source}	6	—	300	600	—	μA
Sink current	I _{sink}	7	—	550	1150	—	μA

AC Characteristics ($V_{DD} = 3.0\text{ V}$, $V_{SS} = \text{GND}$, $T_a = 25^\circ\text{C}$)


Characteristics	Symbol	Test Circuit	Test Condition	Min	Typ.	Max	Unit
Slew rate	SR	—	—	—	5.1	—	V/ μs
Unity gain cross frequency	f_T	—	—	—	3.7	—	MHz

AC Characteristics ($V_{DD} = 1.8\text{ V}$, $V_{SS} = \text{GND}$, $T_a = 25^\circ\text{C}$)

Characteristics	Symbol	Test Circuit	Test Condition	Min	Typ.	Max	Unit
Slew rate	SR	—	—	—	4.0	—	V/ μs
Unity gain cross frequency	f_T	—	—	—	3.0	—	MHz

Test Circuit

1. SVRR, V_{IO}




- SVRR
 $V_{DD} = 1.8\text{ V}$: $V_{DD} = V_{DD1}$, $V_{OUT} = V_{OUT1}$
 $V_{DD} = 7.0\text{ V}$: $V_{DD} = V_{DD2}$, $V_{OUT} = V_{OUT2}$

$$SVRR = 20 \log \left(\left| \frac{V_{OUT1} - V_{OUT2}}{V_{DD1} - V_{DD2}} \right| \times \frac{R_S}{R_F + R_S} \right)$$
- V_{IO}

$$V_{IO} = \left(V_{OUT} - \frac{V_{DD}}{2} \right) \times \frac{R_S}{R_F + R_S}$$


2. CMRR, CMV_{IN}



- CMRR
 $V_{IN} = 0.0\text{ V}$: $V_{IN} = V_{IN1}$, $V_{OUT} = V_{OUT1}$
 $V_{IN} = 2.1\text{ V}$: $V_{IN} = V_{IN2}$, $V_{OUT} = V_{OUT2}$

$$CMRR = 20 \log \left(\left| \frac{V_{OUT1} - V_{OUT2}}{V_{IN1} - V_{IN2}} \right| \times \frac{R_S}{R_F + R_S} \right)$$
- CMV_{IN}

3. V_{OH}




- V_{OH}

$$V_{IN1} = \frac{V_{DD}}{2} - 0.05 \text{ V}$$

$$V_{IN2} = \frac{V_{DD}}{2} + 0.05 \text{ V}$$

4. V_{OL}




- V_{OL}


$$V_{IN1} = \frac{V_{DD}}{2} + 0.05 \text{ V}$$

$$V_{IN2} = \frac{V_{DD}}{2} - 0.05 \text{ V}$$


5. I_{DD}















6. I_{source}











7. I_{sink}












Package Dimensions

SSOP5-P-0.95

Unit : mm




Weight: 0.014 g (typ.)

Package Dimensions

SSOP5-P-0.65A

Unit : mm



Weight: 0.006 g (typ.)