





CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING




ISOMETERIC



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 300mA @ 125 VAC
6. OPERATING FORCE: 800±300 gm-cm
7. OPERATING TEMP: -30°C TO 85°C
- ▲ 8. CIRCUIT SP: 12 POSITION NO STOPS.
9. DIELECTRIC STRENGTH: 500VAC FOR 1 MIN.
- ▲ 10. HARDWARE SUPPLIED ON SWITCH: LOCKWASHER, HEXNUT
11. ▲ DENOTES CRITICAL PARAMETER.



P.C.B MOUNTING LAYOUT



A	15335	RELEASED FOR PRODUCTION	9/28/05	PH
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE KC10A13.001NPS

SCALE 1.5:1

DATE 9/28/2005

DR PH

DWG G510357

REV A