




		0.10–0.41mm ² [202–810CMA]	100	LOOSE PIECE, BOX	M3.5[#6]	3.68[.145]	1.27–2.08[.050–.082]	26–22	--	A				8–326875–1
		0.24mm ² [475CMA]	500	LOOSE PIECE	#10	5.00[.197]	0.79–1.40[.031–.055]	24	BLUE	B				2–326875–5
			500	LOOSE PIECE	M3.5[#6]	3.68[.145]	0.79–1.40[.031–.055]	24	BLUE	B				2–326875–4
		0.10–0.41mm ² [202–810CMA]	4000	326875 ON TAPE, REEL	M3.5[#6]	3.68[.145]	1.27–2.08[.050–.082]	26–22	--	A				2–326875–1
			500	LOOSE PIECE	M3.5[#6]	3.68[.145]	1.27–2.08[.050–.082]	26–22	--	A				326875
CIRCULAR MIL AREA	QTY	PACKAGE TYPE	STUD SIZE "D"	DIM "C"	WIRE INSUL. DIA	WIRE SIZE	COLOR CODE	STYLE	BODY	SLEEVE	MATERIAL	PART NO		
										FINISH				

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS												
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F] MAX										
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: 300V MAX										
FOR ORDER ENTRY	1-800-526-5142	CIRCULAR MIL AREA RANGE: SEE TABLE										

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 14JAN10	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK TOM MICHIELUTTI 14JAN10	NAME			
		APVD MIKE PERCHERKE 14JAN10	TERMINAL, NYLON – PIDG – RING TONGUE			
		PRODUCT SPEC	WIRE SIZE: 26–22			
		APPLICATION SPEC				
MATERIAL	FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE TABLE	SEE TABLE	—	A2	00779	Ⓒ-326875	—
CUSTOMER DRAWING			SCALE	8:1	SHEET	1 of 1
			REV	Y1		