

IDMD-24-D-12.00-G

(2,54 mm) .100"

# SLIM BODY FLAT RIBBON IDC CABLES

## SPECIFICATIONS

For complete specifications see [www.samtec.com?IDSS](http://www.samtec.com?IDSS), [www.samtec.com?IDSD](http://www.samtec.com?IDSD), [www.samtec.com?IDMS](http://www.samtec.com?IDMS) or [www.samtec.com?IDMD](http://www.samtec.com?IDMD)

**Insulator Material:**  
Black Glass Filled Polyester  
**Plating:**  
Au over 50µ" (1,27 µm) Ni or Sn over 100µ" (2,54 µm) Cu or 50µ" (1,27 µm) Ni

**Wire:**  
28 AWG 7/36 stranded  
Tinned Copper

**Temperature Range:**  
-20°C to +105°C (Rainbow Cable)  
-40°C to +105°C (Gray Cable)

**Contact (IDSS/IDSD):**  
BeCu

**Terminal (IDMS/IDMD):**  
Phosphor Bronze

**Current Rating (IDSD/TST):**  
3.4 A per pin

**Current Rating (IDMD):**  
3 A per pin

**Contact Resistance:**  
15 mΩ

**Lead Size Range:**  
(0,56 mm) .022" SQ to (0,71 mm) .028" SQ

**Lead Insertion Depth:**  
(5,59 mm) .220" to (6,22 mm) .245"

**Insertion Force:**  
(Single contact only)  
4 oz (1,11 N) avg.  
(0,64 mm) .025" SQ probe)

**Withdrawal Force:**  
(Single contact only)  
3 oz (0,83 N) avg.  
(0,64 mm) .025" SQ probe)

**RoHS Compliant:**  
Yes

**Mates with:**

TSW, MTSW, TSM, EJH, PHT, HMTSW, HTSW, HW, DW, EW, ZW, MTLW

**IDSD Mates with:**

TST, HTST, ZST, BST, EJH

**IDM**  
= Standard Tail Male Plug

**IDS**  
= Socket

**TYPE STRIP**

**ROW OPTION**


**NO. PINS PER ROW**

**END ASSEMBLY**

**S**  
= Single


**D**  
= Double  
(Color coded cable N/A for 31 thru 36 pins/row. See -G option.)

**-S = Single End**




Socket or Male Plug on one end

**-D = Double End**




Socket or Male Plug on each end

**-T = Transfer End**




Male Plug on one end with socket on other. **Begin part number with IDM.**

## -02 thru -32




(For square or long tail see HCMX Series)


**IDMS (Single)**      **IDMD (Double)**



## -02 thru -36



**IDSS (Single)**      **IDSD (Double)**




## OTHER SOLUTIONS

### Molded-To-Position IDC Assemblies

- Low profile
- Skinny side locks
- Dual beam contacts
- Single and double row
- (3,05 mm) .120" and (5,84 mm) .230" length tail available

Call Samtec for HCXX Series.




## RECOGNITIONS


For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)



**Note:**  
This Series is non-standard, non-returnable.



IDSD-24-S-05.00




IDSD-05-D-04.25-S02

**IDSS, IDSD, IDMS, IDMD SERIES**


**ASSEMBLED LENGTH**

— “XX.XX”  
= Assembled Length



**OPTION**

**POLARIZING KEY**




Optional polarizing key for use with IDSS & IDSD Series. Also polarizes SSW, SSQ, ESW & ESQ Series. Black High Temperature Thermoplastic

Order: Part Number PK-01-06 (Available in wheels of six each)


**EJECTOR HEADERS & LOCKING CLIPS**



- Ejector headers
- Locking clips



See TSW Series.



See EJH Series.

—T = Tin Plating (Both ends)

—C = Tin IDM = 10µm (0.25 µm) Gold IDS (-T End Assembly Required)


—A = 10µm (0.25 µm) Gold IDM = Tin IDS (-T End Assembly Required)

Standard plating is selective gold over BeCu contact for IDS; Selective gold over phosphor bronze for IDM.

1


—ST “X” = Stripped & Tinned

Specify Suffix from table. All dimensions are ± 1/16". Not available in 28 positions and higher.



4


—S “XX” = Daisy Chain Single



When mating double row connector with two single row connectors, the outer most single will be connected to Conductor #1 and the inside single to Conductor #2.


7

—R = Reversed



8

—P “XX” = Polarized




Specify “XX” as position. For Double the same position will be polarized on both ends. (Not available on IDM unless transfer, then only the socket is polarized.)

2

—B “XX” = Breakout


Specify “XX” as number of conductors to be broken out.



Breakout starts with Number 1 lead indicated by brown wire or red stripe. Shown on top side.


5

—D “XX” = Daisy Chain, Double



7

—M = Middle Reversed



Requires -SXX, -WXX or -DXX

8

—G = Gray Cable

Specify -G for Gray cable. Gray cable has one red edge. IDSS and IDMS uses .100" centerline cable. IDSD and IDMD uses .050" centerline cable. Cable is 28 AWG 7/36 copper wire. Standard cable is same as above except color coded.

3

—RW = Reversed Wiring

#1 wire opposite position #1.


6

—W “XX” = Wiring Reversed Daisy Chain, Single

Same as -S “XX” except outer strip connected to Conductor #2 and inside strip connected to Conductor #1.

7

—O = Outside Reversed



Requires -SXX, -WXX or -DXX

8