

SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Terminal body
- (metal housing): Steel
- Terminal screw: Steel Zinc plating "-" slot type.
- Wire guard: PhBz(CuSn), Tin plated.
- Insulator(housing): Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: cULus / TUV 300V / 300V
- Current rating: 20A / 20A
- Wire range: 0.34-2.5mm²
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5 Lb-In / 0.4N.m
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV / 2.5KV
- Operating temperature: -30°C to +105°C
- Safety Approval: 

RoHS Compliant

PART NUMBER:

OSTVMXX7550

No. of Poles

02 2 Poles

03 3 Poles

... ..

24 24 Poles


COLOR

0: Black



5: Green (Standard)

6: Blue

8: Grey



N=Number of poles



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.



ON-SHORE TECHNOLOGY, INC.

TITLE		OSTVM 5.0mm Series						
PART NO.	OSTVMXX7550				DWG NO.	OSTVMXX7550.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	 UNIT: mm SCALE: NONE SHEET: 01/01 REV: D		Tolerance	
Shi Jun 2006.10.25	Shi Jun 2006.10.25	Tony 2006.10.25	Tony 2006.10.25	X. ±0.50				
				X.X ±0.30				
						X.XX ±0.10		
						X° ±1°		