

TD62064APG, TD62064AFG, TD62074APG, TD62074AFG**4ch High-Current Darlington Sink Driver**

The TD62064APG/AFG and TD62074APG/AFG are high-voltage, high-current darlington drivers comprised of four NPN darlington pairs.


All units feature integral clamp diodes for switching inductive loads and all units of TD62074APG/AFG feature uncommitted collectors and emitters for isolated darlington applications.

For proper operation, the substrate (SUB) must be connected to the most negative voltage.

Applications include relay, hammer, lamp and stepping motor drivers.

Features

- Output current (single output) 1.5 A (max)
- High sustaining voltage output
50 V (min) (TD62064APG/AFG, 074APG/AFG)
- Output clamp diodes: TD62064APG/AFG
- Isolated darlington array: TD62074APG/AFG
- Input compatible with TTL and 5 V CMOS
- GND and SUB terminal = Heat sink
- Package type-APG: DIP-16 pin
- Package type-AFG: HSOP-16 pin




Weight

DIP16-P-300-2.54A: 1.11 g (typ.)


HSOP16-P-300-1.00: 0.50 g (typ.)

Pin Assignment (top view)


TD62064APG




TD62074APG



TD62064AFG




TD62074AFG




Schematics (each driver)

TD62064APG/AFG



TD62074APG/AFG



Note: The input and output parasitic diodes cannot be used as clamp diodes.

Precautions for Using

- (1) This IC does not include built-in protection circuits for excess current or overvoltage. If this IC is subjected to excess current or overvoltage, it may be destroyed. Hence, the utmost care must be taken when systems which incorporate this IC are designed. Utmost care is necessary in the design of the output line, COMMON and GND line since IC may be destroyed due to short-circuit between outputs, air contamination fault, or fault by improper grounding.
- (2) If a TD62064APG/AFG is being used to drive an inductive load (such as a motor, solenoid or relay), Toshiba recommends that the diodes (pins 1 and 8) be connected to the secondary power supply pin so as to absorb the counter electromotive force generated by the load. Please adhere to the device's maximum ratings. Toshiba recommends that zener diodes be connected between the diodes (pins 1 and 8) and the secondary power supply pin (as the anode) so as to enable rapid absorption of the counter electromotive force. Again, please adhere to the device's maximum ratings.

If a TD62074APG/AFG is being used to drive an inductive load (such as a motor, solenoid or relay), Toshiba recommends that a diode be connected between the output pin (as the anode) and the secondary power supply pin. Please adhere to the device's maximum ratings.

Maximum Ratings (Ta = 25°C)

Characteristics		Symbol	Rating	Unit
Output sustaining voltage		$V_{CE(SUS)}$	-0.5 to 50	V
Output current		I_{OUT}	1.5	A/ch
Input current		I_{IN}	50	mA
Input voltage		V_{IN}	-0.5 to 17	V
Clamp diode reverse voltage		V_R (Note 1)	50	V
Clamp diode forward current		I_F (Note 1)	1.5	A
Isolated voltage		V_{SUB} (Note 2)	50	V
Power dissipation	APG	P_D	1.47/2.7 (Note 3)	W
	AFG		0.9/1.4 (Note 4)	
Operating temperature		T_{opr}	-40 to 85	°C
Storage temperature		T_{stg}	-55 to 150	°C

Note 1: TD62064APG/AFG

Note 2: TD62074APG/AFG

Note 3: On glass epoxy PCB (50 × 50 × 1.6 mm Cu 50%)

Note 4: On glass epoxy PCB (60 × 30 × 1.6 mm Cu 30%)

Recommended Operating Conditions ($T_a = -40$ to 85°C)


Characteristics		Symbol	Test Condition	Min	Typ.	Max	Unit
Output sustaining voltage		$V_{CE(SUS)}$	—	0	—	50	V
Output current	APG (Note 1) AFG (Note 2)	I_{OUT}	DC1 circuit, $T_a = 25^\circ\text{C}$	0	—	1250	mA/ch
			$T_{pw} = 25\text{ ms}$ 4 circuits	Duty = 10%	0	—	
				Duty = 50%	0	—	
			$T_j = 120^\circ\text{C}$	Duty = 10%	0	—	
			$T_a = 85^\circ\text{C}$	Duty = 50%	0	—	
Input voltage		V_{IN}	—	0	—	8	V
	Output ON	$V_{IN(ON)}$	$I_{OUT} = 1.25\text{ A}$	2.5	—	8	
	Output OFF	$V_{IN(OFF)}$	—	0	—	0.4	
Input current		I_{IN}	—	0	—	20	mA
Clamp diode reverse voltage		V_R	TD62064APG/AFG	0	—	50	V
Clamp diode forward current		I_F	—	—	—	1.25	A
Isolation voltage		V_{SUB}	TD62074APG/AFG	—	—	50	V
Power dissipation	APG	P_D	$T_a = 85^\circ\text{C}$ (Note 1)	—	—	1.4	W
	AFG		$T_a = 85^\circ\text{C}$ (Note 2)	—	—	0.7	

Note 1: On glass epoxy PCB ($50 \times 50 \times 1.6\text{ mm Cu } 50\%$)Note 2: On glass epoxy PCB ($60 \times 30 \times 1.6\text{ mm Cu } 30\%$)Electrical Characteristics ($T_a = 25^\circ\text{C}$)


Characteristics	Symbol	Test Circuit	Test Condition	Min	Typ.	Max	Unit
Output leakage current	I_{CEX}	1	$V_{CE} = 50\text{ V}$, $T_a = 25^\circ\text{C}$	—	—	50	μA
			$V_{CE} = 50\text{ V}$, $T_a = 85^\circ\text{C}$	—	—	500	
Output saturation voltage	$V_{CE(sat)}$	2	$I_{OUT} = 1.25\text{ A}$, $I_{IN} = 2\text{ mA}$	—	—	1.6	V
			$I_{OUT} = 0.75\text{ A}$, $I_{IN} = 935\text{ }\mu\text{A}$	—	—	1.25	
DC current transfer ratio	h_{FE}	2	$V_{CE} = 2\text{ V}$, $I_{OUT} = 1.0\text{ A}$	—	800	—	—
			$I_{OUT} = 0.25\text{ A}$	—	1500	—	
Input voltage (output on)	$V_{IN(ON)}$	3	$I_{OUT} = 1.25\text{ A}$, $I_{IN} = 2\text{ mA}$	—	—	2.4	V
Clamp diode leakage current	I_R	4	$V_R = 50\text{ V}$, $T_a = 25^\circ\text{C}$	—	—	50	μA
			$V_R = 50\text{ V}$, $T_a = 85^\circ\text{C}$	—	—	100	
Clamp diode forward voltage	V_F	5	$I_F = 1.25\text{ A}$	—	—	2.0	V
Input capacitance	C_{IN}	6	$V_{IN} = 0\text{ V}$, $f = 1\text{ MHz}$	—	15	—	pF
Turn-ON delay	t_{ON}	7	$C_L = 15\text{ pF}$, $V_{OUT} = 50\text{ V}$, $R_L = 42\text{ }\Omega$	—	0.1	—	μs
Turn-OFF delay	t_{OFF}	7	$C_L = 15\text{ pF}$, $V_{OUT} = 50\text{ V}$, $R_L = 42\text{ }\Omega$	—	1.0	—	μs

Test Circuit


1. I_{CEX}




2. $V_{CE} (sat)$, h_{FE}




3. $V_{IN} (ON)$




4. I_R





5. V_F



6. C_{IN}











7. t_{ON} , t_{OFF}



Note 1: Pulse Width 50 μ s, Duty Cycle 10%
Output Impedance 50 Ω , $t_r \leq 5$ ns, $t_f \leq 10$ ns

Note 2: C_L includes probe and jig capacitance






Package Dimensions

DIP16-P-300-2.54A

Unit : mm





Weight: 1.11 g (typ.)

Package Dimensions

HSOP16-P-300-1.00

Unit : mm



Weight: 0.50 g (typ.)

About solderability, following conditions were confirmed

- Solderability

- (1) Use of Sn-63Pb solder Bath

- solder bath temperature = 230°C
 - dipping time = 5 seconds
 - the number of times = once
 - use of R-type flux

- (2) Use of Sn-3.0Ag-0.5Cu solder Bath

- solder bath temperature = 245°C
 - dipping time = 5 seconds
 - the number of times = once
 - use of R-type flux

RESTRICTIONS ON PRODUCT USE

030619EBA

- The information contained herein is subject to change without notice.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA for any infringements of patents or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of TOSHIBA or others.
- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- TOSHIBA products should not be embedded to the downstream products which are prohibited to be produced and sold, under any law and regulations.