


HONEYWELL PART NUMBER
111SM2-T2
PRODUCT CODE TYJ0280

REV	DOCUMENT	CHANGED BY	CHECK
8	0038225	PRS 04APR08	BLR



NOTES
1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
2 - TERMINALS ARE PLATED FOR SOLDERING

RELEASE NO.	SR - 10729
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± - ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± ANGLES ± -		DRAWN	VK	25 OCT 07	Honeywell								
OPERATING FORCE — — — 7 OZ MAX		CONTACT ARRANGEMENT SPDT					CHECK	RJ	25 OCT 07					TITLE SWITCH - BASIC				
RELEASE FORCE— — — — 2 OZ MIN		30 VOLTS DC RATING			THIRD ANGLE PROJECTION 		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			SIZE B		TYPE I						DRAWING NAME 111SM2-T2
PRETRAVEL - - - - - .219 MAX		SEA LEVEL 50,000 FT																
DIFFERENTIAL TRAVEL— — — .025 MAX		INDUCTIVE		3 AMP			2.5 AMP	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SCALE -		WEIGHT .008 LB MAX		SHEET 1 OF 1			
OVERTRAVEL — — — — — .030 MIN		RESISTIVE		5 AMP			5 AMP											
		MAXIMUM INRUSH 24 AMP																
		APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4  														
			UL, CSA	5A, 250 VAC ~   BRAND L4														