

DUAL OPERATIONAL AMPLIFIER

■ GENERAL DESCRIPTION

The NJM2141 is a high gain, high output current dual operational amplifier in ultra miniature surface mount package, which drive $\pm 25\text{mA}$ at extremely low operating voltages ($V^+/V^- = \pm 2\text{V}$).

The NJM2141 realize wide bandwidth, low noise, high slew rate and low distortion, which is suitable for audio, telecommunication and instrumentation applications.

■ PACKAGE OUTLINE




NJM2141R

■ FEATURES

- Operating Voltage ($\pm 2\text{V} \sim \pm 10\text{V}$)
- Slew Rate ($3\text{V}/\mu\text{s}$ typ.)
- Bandwidth (8MHz typ.)
- High Output Current ($I_O = 25\text{mA}$)
- Bipolar Technology
- Package Outline VSP8

■ PIN CONFIGURATION




NJM2141R

PIN FUNCTION

- 1.A OUTPUT
- 2.A -INPUT
- 3.A +INPUT
- 4. V^-
- 5.B +INPUT
- 6.B -INPUT
- 7.B OUTPUT
- 8. V^+

■ EQUIVALENT CIRCUIT (1/2 Shown)



NJM2141

■ ABSOLUTE MAXIMUM RATINGS

(Ta=25°C)

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	V^+/V^-	± 10	V
Differential Input Voltage	V_{ID}	± 15	V
Input Voltage	V_{IC}	± 7.5 (note1)	V
Power Dissipation	P_D	320	mW
Operating Temperature Range	T_{opr}	-20~+75	°C
Storage Temperature Range	T_{stg}	-40~+125	°C







(note1) When input voltage is less than $\pm 7.5V$, the absolute maximum control voltage is equal to the input voltage.

■ ELECTRICAL CHARACTERISTICS






($V^+/V^- = 5V, Ta = 25^\circ C$)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Input Offset Voltage	V_{IO}	$R_S = 0\Omega$	-	0.5	6	mV
Input Offset Current	I_{IO}		-	5	200	nA
Input Bias Current	I_B		-	80	500	nA
Input Resistance	R_{IN}		0.3	2.5	-	MΩ
Large Signal Voltage Gain	A_V	$R_L \geq 2k\Omega, V_O = \pm 4V$	86	100	-	dB
Maximum Output Voltage Swing 1	V_{OM1}	$R_L \geq 2k\Omega$	+4.0 -3.5	+5.0 -4.5	-	V
Maximum Output Voltage Swing 2	V_{OM2}	$V^+/V^- = \pm 9V, I_O = 25mA$	+4.0 -4.0	+6.0 -5.0	-	V
Input Common Mode Voltage Range	V_{ICM}		± 4.0	± 4.5	-	V
Common Mode Rejection Ratio	CMR	$R_S \leq 10k\Omega$	70	90	-	dB
Supply Voltage Rejection Ratio	SVR	$R_S \leq 10k\Omega$	76.5	90	-	dB
Operating Current	I_{CC}		-	2.7	5.7	mA
Slew Rate	SR		-	3	-	V/ μs
Gain Bandwidth Product	GB		-	8	-	MHz
Equivalent Input Noise Voltage	V_{NI}	RIAA, $R_S = 2k\Omega$, 39kHz LPF	-	1.2	-	μV_{rms}

■ TYPICAL CHARACTERISTICS



■ TYPICAL CHARACTERISTICS



[CAUTION]

The specifications on this databook are only given for information, without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.