


LOC	DIST	REVISONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			U	REDRAWN PER ECO-12-007497	30MAY2012	CJV	SLB



- ① HOUSING MATERIAL: PBT, GLASS FILLED, UL94V-O RATED, BLACK.
- ② HOUSING MATERIAL: PBT, GLASS FILLED, UL94V-O RATED, GRAY.
- ③ HOUSING MATERIAL: PPS, GLASS FILLED, UL94V-O RATED, BROWN.
4. CONTACT MATERIAL: BRASS.
- ⑤ CONTACT FINISH: 0.76μm MIN GOLD OVER 1.27μm MIN NICKEL ON MATING SURFACES, 3μm MIN BRIGHT TIN OVER 1.27μm MIN NICKEL ON SOLDER TAIL.
- ⑥ CONTACT FINISH: 0.38μm MIN GOLD OVER 1.27μm MIN NICKEL ON MATING SURFACES, 3μm MIN BRIGHT TIN OVER 1.27μm MIN NICKEL ON SOLDER TAIL.
- ⑦ CONTACT FINISH: 0.2μm MIN GOLD OVER 1.27μm MIN NICKEL ON MATING SURFACES, 3μm MIN BRIGHT TIN OVER 1.27μm MIN NICKEL ON SOLDER TAIL.
- ⑧ OBSOLETE.
- ⑨ COMPANY LOGO APPROXIMATELY WHERE SHOWN



THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009			DWN C. VALENTINE 30MAY2012 CHK S. BOLASH 30MAY2012 APVD S. BOLASH 30MAY2012		 TE Connectivity				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.2 1 PLC ±0.2 2 PLC ±0.13 3 PLC ±0.005 4 PLC ±0.0005 ANGLES ±.0005 FINISH		NAME HEADER ASSEMBLY, VERTICAL, LOW PROFILE, AMP-LATCH -					
		PRODUCT SPEC 108-20038 APPLICATION SPEC - WEIGHT -							
MATERIAL SEE TABLE		SEE TABLE		SIZE A2		CAGE CODE 00779	DRAWING NO C-281271	RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 5:1		SHEET 1		OF 2	REV 11

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

GP

00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

10	281271-3	10.16	17.78	20.32	
14	281272-3	15.24	22.86	25.40	
16	281273-3	17.78	25.40	27.94	
20	281274-3	22.86	30.48	33.02	
26	281275-3	30.48	38.10	40.64	
34	281276-3	40.64	48.26	50.80	
40	281277-3	48.26	55.88	58.42	
50	281278-3	60.96	68.58	71.12	
60	281836-3	73.66	81.28	83.82	
NO POS	PART NUMBER	A	B	C	NOTES

10	281271-2	10.16	17.78	20.32	
14	281272-2	15.24	22.86	25.40	
16	281273-2	17.78	25.40	27.94	
20	281274-2	22.86	30.48	33.02	
26	281275-2	30.48	38.10	40.64	
34	281276-2	40.64	48.26	50.80	
40	281277-2	48.26	55.88	58.42	
50	281278-2	60.96	68.58	71.12	
60	281836-2	73.66	81.28	83.82	
NO POS	PART NUMBER	A	B	C	NOTES

10	281271-1	10.16	17.78	20.32	
14	281272-1	15.24	22.86	25.40	
16	281273-1	17.78	25.40	27.94	
20	281274-1	22.86	30.48	33.02	
26	281275-1	30.48	38.10	40.64	
34	281276-1	40.64	48.26	50.80	
40	281277-1	48.26	55.88	58.42	
50	281278-1	60.96	68.58	71.12	
60	281836-1	73.66	81.28	83.82	
NO POS	PART NUMBER	A	B	C	NOTES

10	1-281271-1	10.16	17.78	20.32	
14	1-281272-1	15.24	22.86	25.40	
16	1-281273-1	17.78	25.40	27.94	
20	1-281274-1	22.86	30.48	33.02	
26	1-281275-1	30.48	38.10	40.64	
34	1-281276-1	40.64	48.26	50.80	
40	1-281277-1	48.26	55.88	58.42	
50	1-281278-1	60.96	68.58	71.12	
60	1-281836-1	73.66	81.28	83.82	
NO POS	PART NUMBER	A	B	C	NOTES

10	281271-5	10.16	17.78	20.32	
14	281272-5	15.24	22.86	25.40	
16	281273-5	17.78	25.40	27.94	
20	281274-5	22.86	30.48	33.02	
26	281275-5	30.48	38.10	40.64	
34	281276-5	40.64	48.26	50.80	
40	281277-5	48.26	55.88	58.42	
50	281278-5	60.96	68.58	71.12	
60	281836-5	73.66	81.28	83.82	
NO POS	PART NUMBER	A	B	C	NOTES

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING
PER ASME Y14.5M-2009

DIMENSIONS:
mm

MATERIAL

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.2
2 PLC ±0.13
3 PLC ±0.005
4 PLC ±0.0005
ANGLES ±
FINISH

SEE TABLE

DWN
C. VALENTINE
CHK
S. BOLASH
APVD
S. BOLASH

30MAY2012
30MAY2012
30MAY2012

PRODUCT SPEC
108-20038
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
HEADER ASSEMBLY, VERTICAL,
LOW PROFILE, AMP-LATCH
-

SIZE
A200779

CAGE CODE
C-281271

DRAWING NO

RESTRICTED TO
-

SCALE
5:1

SHEET
2

OF
2

REV
U

1471-9 (3/11)