






CONFIDENTIAL

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	MM
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	ML CHWA	1994-10-24	ANGULAR	LINEAR	0.X	±-
Eng	BSL	1994-10-27			0.XX	±0.25
Chr	KH LEE	2010-01-11	0° ±°		0.XXX	±-
Appr	JOEY NG	2010-01-11	Product family			ECN S10-0205
			MINITEK			Spec ref -
			MINITEK II			Rev. C
			SMT STR HEADER			
			catalog no			
			CUSTOMER			sheet 1 of 2

A

B

C

D

PRODUCT NO	POS	DIM X	DIM Y
94267-X04	2 X 2	2	4
-X06	2 X 3	4	6
-X08	2 X 4	6	8
-X10	2 X 5	8	10
-X12	2 X 6	10	12
-X14	2 X 7	12	14
-X16	2 X 8	14	16
-X18	2 X 9	16	18
-X20	2 X 10	18	20
-X22	2 X 11	20	22
-X24	2 X 12	22	24
-X26	2 X 13	24	26
-X28	2 X 14	26	28
-X30	2 X 15	28	30
-X32	2 X 16	30	32
-X34	2 X 17	32	34
-X36	2 X 18	34	36
-X38	2 X 19	36	38
-X40	2 X 20	38	40
-X42	2 X 21	40	42
-X44	2 X 22	42	44
-X46	2 X 23	44	46
-X48	2 X 24	46	48
-X50	2 X 25	48	50





FIG. 1
NOTE 5(c)

PART NUMBER INFORMATION


XXXXX-XXXLF



NOTES:


- MATERIAL:
BODY : HIGH TEMPERATURE PLASTIC UL 94V-0 BLACK
PIN : COPPER ALLOY
- TOLERANCE UNLESS OTHERWISE NOTED ± 0.25
- DIM 1.0 ± 0.15 APPLIES TO MOLDED SIDE(S) ONLY. IF SIDE(S) ARE BROKEN, DIM 1.5 MAX APPLIES.
- RECESS APPLIES TO MOLDED SIDE(S) ONLY.
- PACKAGING:
a) STANDARD PACKAGING IN PLASTIC BAG.
b) SPECIFY 94267-XXXT FOR TUBE PACKAGING.
c) SPECIFY 94267-XXXTR FOR TAPE AND REEL PACKAGING.
A PICK-UP CAP IS PROVIDED IN THE CENTRE OF THE PRODUCT (SEE FIG. 1) FOR PICK AND PLACE APPLICATION.
- COPLANARITY OF SOLDER LEADS TO BE WITHIN 0.10mm.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- A $\triangle C$ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

PLATING	DESCRIPTION
0	0.2 μ m Au OVER Ni
1	0.76 μ m Au OVER Ni
3	0.38 μ m Au OVER Ni
5	0.38 μ m PdNi W Au FLASH OVER Ni
6	0.76 μ m PdNi W Au FLASH OVER Ni



RECOMMENDED PAD LAYOUT

CONFIDENTIAL

www.fciconnect.com			surface -  ISO 1302		tolerance std ISO 406 ISO 1101		projection 		MM 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	ML CHWA	1994-10-24	ANGULAR	LINEAR	0.X	±-	size A3	Scale 10:1				
Eng	BSL	1994-10-27			0.XX	±0.25						
Chr	KH LEE	2010-01-11			0° ±-°	0.XXX					±-	
Appr	JOEY NG	2010-01-11	Product family				MINITEK		Spec ref			
		title				MINITEK II				dwg no 94267		Rev C
		SMT STR HEADER										
		catalog no				-		CUSTOMER		sheet 2 of 2		