



BOURNS®

Features

- For use with Globespan ADSL chipset
- Excellent Total Harmonic Distortion (THD) Performance
- Exceeds standards for ANSI and ETSI
- Isolation voltages up to 2000 Vrms
- Operating temperature -40 °C to +85 °C

- Designed to meet UL1950 and EN60950 supplementary insulation requirements for operating voltages up to 250 Vrms

Applications

- ADSL - Globespan



PT542-1 to SM547-1 ADSL & RADSL Transformers

Electrical Specifications @ 25 °C



Part Number	Turns Ratio Chip-Line (±2 %)	OCL Primary (1-4) with (2-3) shorted (μH ±10 %)	Leakage Inductance (μH max.)	DCR @ (1-3), (2-4), (10-8), (9-7) (Ω max.)	Isolation Voltage (Vrms)	Insertion Loss (dB max.)	Longitudinal Balance (dB typ.)	Package
PT542-1	1.4:1.4:1:1	940	10	1.2	1500	3	62	THT
PT543-1	1:1:1:1	410	10	0.8	1500	3	62	THT
PT544-1	1.4:1.4:1:1	940	10	1.2	3000	3	62	THT
PT545-1	1:1:1:1	410	10	0.8	3000	3	62	THT
SM546-1	1.4:1.4:1:1	940	10	1.2	3000	3	62	SMT
SM547-1	1:1:1:1	410	10	0.8	3000	3	62	SMT

Product Dimensions


SMT



Recommended PAD layout





THT



DIMENSIONS ARE: $\frac{\text{MM}}{(\text{INCHES})}$


TOLERANCE: $\pm \frac{0.25}{(.010)}$



Packaging Specifications

Tube35 pcs./tube

Electrical Schematic



Reliable Electronic Solutions

Asia-Pacific: TEL +886-2 25624117 • FAX +886-2 25624116
Europe: TEL +41-41 7685555 • FAX +41-41 7685510
N. America: TEL +1-909 781-5500 • FAX +1-909 781-5700
www.bourns.com

04/03

COPYRIGHT© 2003, BOURNS, INC. LITHO IN U.S.A. e 04/03 /SP0207

Specifications are subject to change without notice.