



REV	DOCUMENT	CHANGED BY	CHECK
5	0041567	JA 14JUL08	ASD



CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:		DRAWN	JA	16OCT07	Honeywell						
OPERATING FORCE 3-5 OZ RELEASE FORCE 1 OZ MIN DIFFERENTIAL TRAVEL .004 MAX OVERTRAVEL .010 MIN		CONTACT ARRANGEMENT S P D T					NO PLACES X ± 0.400 ONE PLACE .X ± 0.03 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 ANGLES X ± 3.0°		CHECK						PSR	16OCT07
		30 VOLTS DC RATING			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.											
		SEA LEVEL		50000 FT												
		INDUCTIVE	3 AMP	2.5 AMP												
		RESISTIVE	5 AMP	5 AMP												
		MAXIMUM INRUSH 24AMP			INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY					SIZE	TYPE	CAGE CODE	DRAWING NAME		REV	
		APPROVALS	KEMA,CE	5A,250 V ~ T85 IE4  						THIRD ANGLE PROJECTION 	B	I	-	ISM33-H2		5
UL,CSA	5A,250 VAC  															
						Pro/ENGINEER		2D	SCALE -				SHEET	I	OF	I