


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HG	-		B	ECR-06-019788	24AUG2006	EJH	SB
			BI	REV PER ECR-11-006927	08APR2011	DCH	CT

D


C

B

A



PROTECTIVE COVER




 TE CONNECTIVITY LOGO, ATTENUATION VALUE, PART NUMBER, AND SERIAL NUMBER ARE PRINTED ON THE LABEL.

PERFORMANCE REQUIREMENTS:

OPERATING WAVELENGTH	: 1310/1550 ±25nm
REFLECTANCE	: ≤ -65dB
OPERATING TEMPERATURE	: -40°C TO +75°C
ATTENUATION TOLERANCE, AMBIENT	:
FOR ATTENUATORS ≥ 5dB	: ±10% OF NOMINAL ATTENUATION VALUE
FOR ATTENUATORS < 5dB	: ± 0.50dB
MEASURED WITH REFERENCE QUALITY LAUNCH LEADS	

NOMINAL ATTENUATION VALUE (dB)	PART NUMBER
1	5209597-1
2	5209597-2
3	5209597-3
4	5209597-4
5	5209597-5
6	5209597-6
9	5209597-9
10	1-5209597-0
12	1-5209597-2
15	1-5209597-5
18	1-5209597-8
20	2-5209597-0
25	2-5209597-5
30	3-5209597-0

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. HOPKINS 05DEC2005	 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK E. HOPKINS 05DEC2005				
		APVD S. BUCHTER 05DEC2005	NAME ATTENUATOR, OPTICAL, BUILDOUT SC/APC 8 DEGREE, SM, DUAL WINDOW			
		PRODUCT SPEC -	SIZE A2			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -	CAGE CODE			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH -		WEIGHT -	DRAWING NO C-5209597			
MATERIAL -		CUSTOMER DRAWING	RESTRICTED TO -			
			SCALE 4:1			
			SHEET 1 OF 1			
			REV BI			