


Diac

DO-35 Case




TYPE NO.	V _{BO} (V)		Δ V _{BO} (V) MAX	I _{BO} (μA) MAX	Δ V ± (V)		I _p (A) MAX
	MIN	MAX			MIN	MAX	
CT-32	28	36	3.0	50	5.0		2.0

Programmable UJTs (PUT)



TO-92



TO-92-18R

TYPE NO.	GATE TO ANODE REVERSE VOLTAGE	DC ANODE CURRENT	GATE TO ANODE LEAKAGE CURRENT	PEAK CURRENT		VALLEY CURRENT		CASE
	V _{GAR}	I _T	I _{GAO} V _S =40Vdc	I _p		I _v		
				R _G =10KΩ	R _G =1.0MΩ	R _G =10KΩ	R _G =1.0MΩ	
				(μA)	(μA)	(μA)	(μA)	
				MAX	MAX	MIN	MAX	
2N6027	40	150	10	5.0	2.0	70	50	TO-92
2N6028	40	150	10	1.0	0.15	25	25	TO-92
PN6119-18R	40	300	10	5.0	2.0	70	50	TO-92-18R
PN6120-18R	40	300	10	1.0	0.15	25	25	TO-92-18R